

The display you are connecting must have a HDMI port that can accept a converted HDMI signal. Contact your display manufacturer to confirm that it will work with a VGA + Audio to HDMI converter. If your display does not support this, an alternative solution is Tripp Lite's (Model: Number: U244-001-HDMI-R) USB to HDMI adapter.

VGA with Audio to HDMI Converter, Adapter for Stereo Audio and Video

MODEL NUMBER: **P116-000-HDMI**



Description

Tripp Lite's P116-000-HDMI VGA + Audio to HDMI converter is the perfect solution for using your older laptop or PC with your new HDMI display. Simply connect your computer's VGA and Audio ports to the converter, and the converter to the HDMI port on your display, and you are ready to go. No software or drivers required. If your computer has only a 3.5 mm. Mini Stereo Audio jack, connect it to the converter using a 3.5 mm. to RCA adapter cable such as Tripp Lite's [P314-006](#). You can also convert the RGB Video and Stereo Audio signals on your DVD player, DVR, etc., for use on your HDMI display (Component Video to VGA adapter required) Furthermore, you reduce your equipment costs by eliminating the need to upgrade your computer's video card.

The P116-000-HDMI supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024. Supports 24-bit True Color (8-bits per channel), and HDCP compliant.

Features

- Connect your VGA laptop or PC to a HDMI display to enjoy high definition video and audio
- Convert the RGB Video and Stereo Audio signals from your DVD player, DVR, etc., for use on a HDMI display (Component Video to VGA adapter required)
- Plug-and-Play, no software or drivers required
- Supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024
- Supports 24-bit True Color (8-bits per channel)
- Reduce equipment cost by eliminating the need to update your computer's video card

Highlights

- Connect your VGA laptop or PC to a HDMI display to enjoy high definition video and audio
- Convert the RGB Video and Stereo Audio signals from your DVD player, DVR, etc., for use on a HDMI display (Component Video to VGA adapter required)
- Plug-and-Play, no software or drivers required
- Supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024
- Reduce equipment cost by eliminating the need to update your computer's video card
- HDCP compliant

System Requirements

- The display you are connecting must have a HDMI port that can accept a converted HDMI signal. Contact your display manufacturer to confirm that it will work with a VGA + Audio to HDMI converter. If your display does not support this, an alternative solution is Tripp Lite's U244-001-VGA-R USB to HDMI adapter.
- Computer with a VGA Video and 3.5 mm. or RCA Audio Jacks (If your computer has only a 3.5 mm. Mini Stereo Audio jack, you can use a 3.5 mm. to RCA

- HDCP compliant

adapter cable such as Tripp Lite's P314-006.

- DVD player, DVR, etc. with RGB Video and Stereo Audio jacks (Component video to VGA adapter required)
- Supported PC Video Resolutions - 640 x 480 @ 60Hz, 72Hz, 75Hz, 85Hz, 800 x 600 @ 56Hz, 60Hz, 72Hz, 75Hz, 85Hz, 1024 x 768 @ 60Hz, 70Hz, 75Hz, 80Hz, 85Hz, 1280 x 1024 @ 60Hz, 75Hz
- Supported HD Video Resolutions - 480i @ 60Hz, 480p @ 60Hz, 720p @ 60Hz, 1080i @ 60Hz, 1080p @ 60Hz

Package Includes

- P116-000-HDMI VGA + Audio to HDMI Converter
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 1.2A, 4.9 ft.)
- Owner's Manual

Specifications

MODEL TEXT	
Key Benefit	Converts the VGA and Audio signal from a laptop or PC for use on a HDMI display
OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 1.2A, 4.9 ft.
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.1 x 8.1 x 5.7



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	5.33 x 20.57 x 14.47
Shipping Weight (lbs.)	1.1
Shipping Weight (kg)	0.50
Unit Dimensions (hwd / in.)	1.25 x 3.5 x 2.75
Unit Dimensions (hwd / cm)	3.18 x 8.89 x 6.99
Unit Weight (lbs.)	0.4
Unit Weight (kg)	0.18
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	5 to 131 F (-15 to 55 C)
Relative Humidity	5 to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	(2) RCA (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>