


## 3.8kW Single-Phase Dual-Circuit 120V Basic PDU, 40 NEMA 5-15/20R Outlets, NEMA L5-20P/5-20P Inputs, 10 ft. Cords, 0U

MODEL NUMBER: PDU40TDUAL



### Description

The PDU40TDUAL 3.8kW Single-Phase Dual-Circuit 120V Basic PDU works as two independent PDUs in a single housing, perfect for networking, telecom, security, audio/video and sound reinforcement applications. Ideal for high-density network equipment with dual redundant input cables, it features 40 NEMA 5-15/20R outlets split evenly into two separate power circuits.

Each power circuit, including its input plug, power cord, breaker and outlets, is color-coded black or gray for easy identification. Both 10-foot power cords feature NEMA L5-20P input plugs and come with optional adapters to convert them to NEMA 5-20P plugs, which are not color-coded. Connect the plugs to separate mains input power sources, generators or protected UPS systems to distribute AC power to connected equipment.

The switchless design prevents an accidental shutdown, which could lead to costly downtime. Dual 20A circuit breakers protect connected equipment from dangerous overloads. The 70-inch all-metal housing supports toolless 0U vertical mounting in EIA-standard 19-inch racks, as well as on a wall or workbench or under a counter with user-supplied hardware.

### Features

Dual Single-Phase PDUs in a Single Housing

- Ideal for high-density network equipment with dual redundant input cables
- 40 NEMA 5-15/20R outlets in 2 breakered power circuits
- 70 in. all-metal housing

Dual Input Connectors

### Highlights

- Functions as 2 independent 20A PDUs in one housing
- Dual NEMA L5-20P/5-20P inputs with 10 ft. (3 m) cords
- 40 NEMA 5-15/20R outlets in 2 separate circuits
- Switchless design prevents accidental shutdown
- Supports toolless 0U vertical button-mounting

### Package Includes

- PDU40TDUAL 3.8kW Single-Phase Dual-Circuit 120V Basic PDU
- (2) NEMA L5-20P to NEMA 5-20P Plug Set Adapters
- Mounting Hardware
- Owner's Manual



- NEMA L5-20P input plugs with 10 ft. cords
- Included adapters convert plugs to NEMA 5-20P, if desired
- Plugs connect to separate external AC power sources

#### Dual Independent Power Circuits

- Circuits include input plug, power cord, circuit breaker and outlets
- Color-coded black or gray for easy identification
- 20A circuit breakers protect outlets against overloads

#### Switchless Design

- Prevents accidental shutdowns and costly downtime

#### Versatile Installation Options

- Supports toolless 0U vertical mounting in EIA-standard 19 in. racks
- Also mounts on wall, workbench or under a counter with user-supplied hardware

## Specifications

MODEL TEXT	
Key Benefit	Dual-circuit PDU ideal for delivering 120V single-phase AC power to servers and networking equipment with dual redundant power supplies or any application that requires high capacity in a compact form factor.
OVERVIEW	
PDU Type	Basic
OUTPUT	
Output Capacity Details	3.8kW total - 1.9kW per circuit (120V); 4.0kW total - 2.0kW per circuit (127V); 3.2kW total - 1.6kW per circuit (100V input); 40A maximum total - 20A maximum per circuit (Agency de-rated to 32A continuous total - 16A per circuit)
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(40) 5-15/20R
Output Receptacle Details	20 grey-color outlets are powered via the grey-color input cable; 20 black-color outlets are powered via the black-color input cable
Output Nominal Voltage	100; 120; 127
Overload Protection	2 x 20A circuit breakers; Grey-color circuit breaker protects grey-color outlets; Black-color circuit breaker protects black-color outlets
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	Two 20A 120V circuits



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Maximum Input Amps	40
Maximum Input Amps Details	20A maximum per circuit (Agency de-rated to 16A per circuit continuous)
PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Cord Details	Set of two input power cords; Grey-color input cord powers grey-color outlets; Black-color input cord powers black-color outlets
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	n/a
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	5 x 2.25 x 71.25
Shipping Dimensions (hwd / cm)	12.7 x 5.7 x 181
Shipping Weight (lbs.)	10
Shipping Weight (kg)	4.5
Unit Dimensions (hwd / in.)	70 x 1.5 x 3
Unit Dimensions (hwd / cm)	177.8 x 3.8 x 7.6
Unit Weight (lbs.)	9
Unit Weight (kg)	4.08
Material of Construction	Metal
Form Factors Supported	Zero U vertical rackmount, wallmount, raceway, workbench and more
PDU Form Factor	0U; Vertical
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA), CSA (Canada), RoHS compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>