

## 1.4kW Single-Phase ATS / Metered PDU, 120V (8 5-15R), 2 5-15P, 100-127V Input, 2 12ft Cords, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH15AT



### Description

Tripp Lite Metered ATS / Auto Transfer Switch provides a redundant power option for single-corded network devices. Dual input cords support separate connection to PRIMARY and SECONDARY power sources. The ATS will normally maintain continuous output to all outlets as derived from the primary input cable. If the primary power source becomes unstable or fails altogether, the ATS will switch over to the secondary power source until the primary input is restored and stable. Super-fast switchover between primary and secondary power sources occurs within milliseconds. ATS functionality is supported by any two compatible AC power sources, regardless of phase angle, to support a variety of advanced redundant power networking applications. Enables fault tolerant hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system. In a two-UPS environment, the primary input cable must be supported by a full time sine wave UPS with zero transfer time. Tripp Lite SmartOnline series is highly recommended for use as the primary UPS in a two-UPS application. ATS configurations utilizing separate mains circuits, backup generators and even separate utility power grid feeds are fully supported. On-board ATS processor constantly evaluates power quality on both input sources to prevent transfer to the secondary source when unavailable or of lower quality than the primary source. Front input LED's display primary or secondary power availability.

### Features

- Federal Trade Agreements Act / TAA compliant for GSA schedule purchases
- 120V 15A Automatic Transfer Switch (ATS) / Metered PDU (Agency de-rated to 12A continuous)
- Provides a redundant A/B power option for non-redundant networking equipment with a single input power cord
- Digital display continuously reports total output power consumption in amps
- 1U horizontal rackmount form factor; 14.5 in. / 36.8 cm depth

### Highlights

- Single phase 15A 120V Auto Transfer Switch / ATS PDU
- Enables redundant A/B power option for single-corded network devices
- Separate primary & secondary inputs connect to any two compatible power sources
- 1U horizontal rackmount; 2 NEMA 5-15P inputs; 8 NEMA 5-15R outlets
- Two digit visual current meter reports equipment load in amps; Upgrade options available
- TAA Compliant

### Package Includes

- ATS / Metered PDU with attached 5-15P primary input cord
- Detachable C13 to NEMA 5-15P 12 ft / 3.6m secondary input cord
- 1U rackmount installation brackets
- User manual with warranty information



- 8 built-in NEMA 5-15R outlets
- Set of two 12 ft. / 3.6m NEMA 5-15P input cables support connection to separate PRIMARY and SECONDARY power sources
- ATS circuits normally maintain output sourced from the primary input cable; As primary input power fails or becomes unstable, the ATS will switch to maintain output sourced from the secondary input cable until power on the primary input is restored and stable
- ATS configurations enable fault-tolerant, hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system (in a two-UPS environment, the primary input cable must be supported by an online UPS with zero transfer time similar to Tripp Lite SmartOnline series)
- Advanced ATS configurations utilizing separate mains circuits, backup generators and even separate out of phase utility power grid feeds are fully supported
- On-board ATS processor constantly evaluates power quality on both inputs to prevent transfer to the secondary source when unavailable or of lower quality than the primary source
- Super-fast switchover between primary and secondary power sources occurs in 2-7 milliseconds
- Built-in card slot supports optional SNMPWEBCARD or WEBCARDLX for permanent upgrade to a switched & monitored PDU system
- Outlets are factory programmed for sequential turn-on at 250 millisecond intervals when the PDU is first energized to prevent inrush-related equipment interaction on startup
- Front panel LEDs confirm power availability on both input lines

## Specifications

OVERVIEW	
PDU Type	Auto-Transfer Switch; Metered
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per outlet
Frequency Compatibility	60 Hz
Output Receptacles	(8) 5-15R
Output Nominal Voltage	100; 120; 127
Overload Protection	n/a
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V



Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	(2) NEMA 5-15P
Input Cord Details	Set of 2 inputs enable connection to separate PRIMARY and SECONDARY power sources
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Two digit current meter reports whole PDU output load in amps
Front Panel LEDs	8 front panel LEDs display power on / off status for each outlet, plus 2 additional LEDs to indicate input power status for primary and secondary inputs
Switches	n/a
<b>PHYSICAL</b>	
Minimum Required Rack Depth (inches)	17.5
Minimum Required Rack Depth (cm)	44.45
Shipping Dimensions (hwd / in.)	5.6 x 22.8 x 20
Shipping Dimensions (hwd / cm)	14.2 x 57.9 x 50.8
Shipping Weight (lbs.)	16
Shipping Weight (kg)	7.3
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 14.5
Unit Dimensions (hwd / cm)	4.44 x 44.4 x 36.8
Unit Weight (lbs.)	11
Unit Weight (kg)	4.99
Material of Construction	Metal
Form Factors Supported	1U rackmount
PDU Form Factor	1U; Horizontal
Minimum Required Rack Depth (mm)	444
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000



<b>COMMUNICATIONS</b>	
Network Management Cards	SNMPWEBCARD; WEBCARDLX
SNMP Compatibility	Includes slot for optional <u>SNMPWEBCARD</u> or WEBCARDLX accessory to add built-in network interface and enable remote individual outlet control over IP
<b>SPECIAL FEATURES</b>	
TVSS Grounding	Rear grounding lug
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL 60950-1 (USA), CSA (Canada), Class A (Emissions), NOM (Mexico), RoHS compliant, TAA compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>