

3.2-3.8kW Single-Phase ATS/Switched PDU, 200-240V Outlets (8 C13 & 2 C19), 2 C20, 12ft Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20HVATNET



Description

Tripp Lite Switched ATS / Auto Transfer Switch provides a redundant power option for single-corded network devices. Dual input cords support separate connection to PRIMARY and SECONDARY power sources. The ATS will normally maintain continuous output to all outlets as derived from the primary input cable. If the primary power source becomes unstable or fails altogether, the ATS will switch over to the secondary power source until the primary input is restored and stable. Switched PDU features include individually controllable output receptacles and built-in network interface. Super-fast switchover between primary and secondary power sources occurs within milliseconds. ATS functionality is supported by any two compatible AC power sources, regardless of phase angle, to support a variety of advanced redundant power networking applications. Enables fault tolerant hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system. In a two-UPS environment, the primary input cable must be supported by a full time sine wave UPS with zero transfer time. Tripp Lite SmartOnline series is highly recommended for use as the primary UPS in a two-UPS application. ATS configurations utilizing separate mains circuits, backup generators and even separate utility power grid feeds are fully supported. On-board ATS processor constantly evaluates power quality on both input sources to prevent transfer to the secondary source when unavailable or of lower quality than the primary source. Front input LED's display primary or secondary power availability.

Features

- 200-240V 16/20A Automatic Transfer Switch (ATS) / Switched PDU (Agency de-rated to 16A continuous)
- Enables redundant A/B power option for single-corded network devices
- 2 digit display reports power consumption in amps
- 1U horizontal rackmount form factor

Highlights

- Single phase 16/20A 200-240V Auto Transfer Switch / ATS PDU
- Enables redundant A/B power option for single-corded network devices
- Separate primary & secondary inputs connect to any two compatible power sources
- 1U horizontal rackmount; 10 outlets (8 C13 switched / 2 C19 unswitched)
- Individually switched outlets, network interface and 2 digit visual current meter
- TAA Compliant

Package Includes

- Switch, Metered PDU with ATS Support
- Set of 2 C19 to C20 12 ft. / 3.7m power cables
- User manual with warranty information



- 10 outlets (8 C13 switched / 2 C19 unswitched)
- Two C20 inlets for separate Primary and Secondary inputs; two 12 ft / 3.7m C20 input cables included
- ATS circuits normally maintain output sourced from the primary input cable; As primary input power fails, the ATS will switch to maintain output sourced from the secondary input cable until power on the primary input is restored and stable
- ATS configurations enable hot-swappable UPS protection when used with a single UPS and redundant UPS protection when each cord is connected to a separate UPS system (in a two-UPS environment, the primary input cable must be supported by an online UPS with zero transfer time)
- Advanced ATS configurations utilizing separate mains circuits, backup generators and separate out of phase utility power grid feeds are supported
- On-board ATS processor constantly evaluates power quality on both inputs to prevent transfer to the secondary source when unavailable or of lower quality than the primary source
- 2-7 millisecond transfer time
- Switched outlets and ethernet interface supports individual outlet control on a real-time or programmable basis and user-specified alarm notification thresholds for all reported site power conditions
- DHCP/Manual configuration support
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Outlets are factory programmed for sequential turn-on at 250 millisecond intervals when the PDU is first energized
- LEDs confirm power availability on both input lines and for each output receptacle
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

Specifications

OVERVIEW	
PDU Type	Auto-Transfer Switch; Switched
OUTPUT	
Output Capacity Details	3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V), 3.2kW (200V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C13; (2) C19
Output Nominal Voltage	200; 208; 220; 230; 240
Overload Protection	n/a



Customized Load Management Receptacles	8 individually switched C13 output receptacles
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240
Recommended Electrical Service	20A 208/240V; 16A 230V
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	(2) IEC-320 C20
Input Cord Details	Set of two inputs connect to separate PRIMARY and SECONDARY power sources
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
Input Phase	Single-Phase
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Front Panel LEDs	8 LEDs display power on-off status for each C13 output receptacle, plus 2 additional LEDs to indicate input power status for primary and secondary inputs
Switches	Toggle switch near digital display enables the setting of "HI" for 220, 230 or 240V nominal applications or "LO" for 200 or 208V applications
PHYSICAL	
Minimum Required Rack Depth (inches)	18.3
Minimum Required Rack Depth (cm)	46.48
Shipping Dimensions (hwd / in.)	5.3 x 23.6 x 21
Shipping Dimensions (hwd / cm)	13.5 x 59.9 x 53.3
Shipping Weight (lbs.)	19.98
Shipping Weight (kg)	9.1
Unit Dimensions (hwd / in.)	1.72 x 17.3 x 14.8
Unit Dimensions (hwd / cm)	4.4 x 43.9 x 37.6
Unit Weight (lbs.)	10.3
Unit Weight (kg)	4.67
Material of Construction	Metal
Form Factors Supported	1U rackmount
PDU Form Factor	1U; Horizontal
Minimum Required Rack Depth (mm)	465



ENVIRONMENTAL	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% (non-condensing)
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
COMMUNICATIONS	
SNMP Compatibility	Yes, via pre-installed <u>SNMPWEBCARD</u> . Provides remote monitoring, outlet control, and automatic power management configurations.
CERTIFICATIONS	
Certifications	Tested to UL 60950 (USA, Canada), CE (Europe), Class A (Emissions), NOM (Mexico), RoHS Complaint, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>