

## AVR750U PRODUCT TRANSITION

Tripp Lite's AVR750U UPS is transitioning to an updated version with a NEW look and performance updates. This page contains information on the NEW version of AVR750U. The NEW version is still in a similar desktop / wall-mount form factor as the previous version. During the transition period, your reseller may still have remaining stock on the previous version. Click [HERE](#) for specifications on the previous version of AVR750U.

## 750VA 450W Line-Interactive UPS - 12 NEMA 5-15R Outlets, AVR, 120V, 50/60 Hz, USB, Desktop/Wall Mount

MODEL NUMBER: AVR750U



Desktop UPS provides battery backup support with automatic voltage regulation (AVR) for your home/office network system or home theater.

### Features

#### 750VA/450W/120V Battery Backup for PCs, Home Theater or Digital Signage

The line-interactive AVR750U UPS system with AVR protection provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The 12-outlet 120V battery backup is ideal protection for your home office, media center or commerce components, including computers, routers, printers, HDTVs, Blu-ray players, game consoles, ATMs, security systems and digital signage equipment.

#### Allows Time to Back Up Critical Files During a Blackout

Backup support allows you to work through short power failures and gives you enough time to safely save files and shut down your system in case of a prolonged blackout. Backup time varies according to load, but the line-interactive UPS system should keep an energy-efficient desktop computer with small LCD monitor powered as long as 42 minutes. During normal operation, incoming utility power keeps the replaceable internal battery fully charged, so backup power will always be available.

#### 12 NEMA 5-15R Outlets Protect Your Connected Components

Six 5-15R outlets provide battery backup, surge protection and voltage regulation for your computer, monitor and other crucial components. The other six 5-15R outlets provide surge suppression only for printers, speakers and other desktop equipment regarded as non-essential during a blackout. A high >96% line mode efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

#### Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

### Highlights

- Protects equipment against blackouts, brownouts, overvoltages, surges and line noise
- Keeps AC power running during blackouts to allow time for file saves and safe shutdown
- 12 NEMA 5-15R outlets power and protect PC, home theater or digital signage equipment
- Home-friendly alarm remains silent in backup mode, sounding only when imperative
- High >96% efficiency with low BTU ratings saves electricity and lowers your energy costs

### Applications

- Protect your PC and other sensitive electronics against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Extend runtime for DVRs, wireless routers and other low-power home network equipment

### Package Includes

- AVR750U 750VA 450W 120V Line-Interactive UPS with 12 Outlets

AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts and overvoltages. The AVR750U can correct brownouts as low as 89V and overvoltages as high as 145V back to nominal 120V power continuously, all while keeping the battery fully charged and ready to take over in case of power failure.

- USB cable
- Owner's manual

**316 Joules Fight Back Against Unexpected Power Surges**

A 316-joule surge suppression rating protects connected components from the harmful effects of power surges.

**Combats Electromagnetic Interference That Can Harm Equipment**

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems and can lead to incremental hardware damage, data corruption and audio/video transmission problems. The AVR750U incorporates technology that filters out disruptive line noise so that it won't affect your equipment.

**Home-Friendly Alarm and Diagnostic LEDs Keep You Informed 24/7**

The UPS remains silent in both line and battery backup modes. The alarm sounds only to report low battery, battery replace, overload and fault condition. Dual front-panel LEDs report line and battery mode operation.

**HID-Compliant USB Port Allows for Automatic Saves and Shutdowns**

This USB port connects the AVR750U to a computer running Tripp Lite's free downloadable PowerAlert® software to enable safe unattended file saves and system shutdown in case of a prolonged power failure. USB cable is included. Battery independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even when batteries are expired and require replacement.

**Compact Housing Compatible with Easy Desktop or Wall-Mount Installation**

The space-saving ABS housing fits on a desktop, shelf or anywhere else convenient to your workstation or home theater. Keyhole mounting tabs on the rear allow easy wall-mount installation. The five-foot power cord with NEMA 5-15P plug connects to any compatible AC outlet.

## Specifications

| OVERVIEW  |                                     |
|---|-------------------------------------|
| UPC Code  | 037332211484                        |
| UPS Type  | Line-Interactive                    |
| OUTPUT  |                                     |
| Output Volt Amp Capacity (VA)                   | 750                                 |
| Output Watt Capacity (Watts)                    | 450                                 |
| Nominal Voltage Details                         | 120v nominal output in battery mode |
| Frequency Compatibility                         | 50 / 60 Hz                          |
| Output Voltage Regulation (Line Mode)           | 120V (+6%/-12%)                     |
| Output Voltage Regulation (Battery Mode)        | 120V (±10%)                         |
| UPS Output Receptacles (Surge Suppression Only) | 6 UPS outlets, 6 surge-only outlets |
| Output AC Waveform (AC Mode)                    | Pure sine wave                      |



|  |  |
|--|--|
| Output AC Waveform (Battery Mode)            | PWM sine wave  |
| Nominal Output Voltage(s) Supported          | 110V; 115V; 120V   |
| Output Receptacles                           | (12) 5-15R   |
| Individually Controllable Load Banks         | No   |
| <b>INPUT</b>                                 |  |
| Rated input current (Maximum Load)           | 10A  |
| Nominal Input Voltage(s) Supported           | 120V AC  |
| UPS Input Connection Type                    | 5-15P  |
| Input Circuit Breakers                       | 10A  |
| UPS Input Cord Length (ft.)                  | 5  |
| UPS Input Cord Length (m)                    | 1.5  |
| Recommended Electrical Service               | 15A 120V   |
| Input Phase                                  | Single-Phase   |
| <b>BATTERY</b>                               |  |
| Full Load Runtime (min.)                     | 3 min. (450w)  |
| Half Load Runtime (min.)                     | 11 min. (225w)   |
| DC System Voltage (VDC)                      | 12   |
| Battery Recharge Rate (Included Batteries)   | 8 hours (10% to 90%)   |
| Internal UPS Replacement Battery Cartridge   | &nbsp;<a class="productLink" href="//www.tripplite.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>&nbsp; |
| Battery Access                               | Battery access door  |
| Battery Replacement Description              | Replaceable internal batteries (see manual)  |
| Expandable Runtime                           | No   |
| <b>VOLTAGE REGULATION</b>                    |  |
| Voltage Regulation Description               | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 89 to 145   |
| Overvoltage Correction                       | Input voltages between 128 and 149 are reduced by 15%  |
| Undervoltage Correction                      | Input voltages between 89 and 108 are boosted by 18%   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| Switches                                     | Power off/on switch  |
| Audible Alarm                                | UPS remains silent in battery backup mode; Alarm sounds only to report low-battery, fault, overload and replace-battery conditions                                     |
| LED Indicators                               | 2 Status LEDs; GREEN indicates power status and operating mode / RED indicates battery-low, overload, replace-battery and fault conditions                             |



| <b>SURGE / NOISE SUPPRESSION</b>                              |  |
|---|--|
| UPS AC Suppression Joule Rating                               | 316  |
| UPS AC Suppression Response Time                              | Instantaneous  |
| UPS Dataline Suppression                                      | 1 line TEL/DSL or Ethernet                                 |
| EMI / RFI AC Noise Suppression                                | Yes  |
| <b>PHYSICAL</b>   |  |
| Installation Form Factors Supported with Included Accessories | Tower; Ultra-compact desktop; Wallmount                    |
| Primary Form Factor   | Desktop  |
| Primary UPS Depth (mm)  | 305  |
| Primary UPS Height (mm)                                       | 105  |
| Primary UPS Width (mm)  | 190  |
| Shipping Dimensions (hwd / cm)                                | 27.20 x 16.00 x 38.10                                      |
| Shipping Dimensions (hwd / in.)                               | 10.71 x 6.30 x 15.00                                       |
| Shipping Weight (kg)  | 7.58   |
| Shipping Weight (lbs.)  | 16.72  |
| UPS Housing Material  | ABS  |
| UPS Power Module Dimensions (hwd, cm)                         | 10.52 x 19.00 x 30.48                                      |
| UPS Power Module Dimensions (hwd, in.)                        | 4.14 x 7.48 x 12   |
| UPS Power Module Weight (kg)                                  | 7.18   |
| UPS Power Module Weight (lbs.)                                | 15.84  |
| <b>ENVIRONMENTAL</b>  |  |
| Operating Temperature Range                                   | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius  |
| Storage Temperature Range                                     | +5 to +113 degrees Fahrenheit / -15 to +45 degrees Celsius |
| Relative Humidity   | 0 to 90%, non-condensing                                   |
| AC Mode BTU / Hr. (Full Load)                                 | 41   |
| AC Mode Efficiency Rating (100% Load)                         | >96%   |
| Operating Elevation (ft.)                                     | Up to 10,000 ft.   |
| Operating Elevation (m)                                       | Up to 3000m  |
| <b>COMMUNICATIONS</b>   |  |
| Communications Interface                                      | USB (HID enabled)  |



|   |  |
|---|--|
| PowerAlert Software   | For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a> |
| Communications Cable  | USB interface cable included   |
| WatchDog Compatibility                                      | Supports Watchdog application, OS and hard-reboot restart options for remote applications  |
| Network UPS Tools Compatibility                             |  |
| <b>LINE / BATTERY TRANSFER</b>                              |  |
| Transfer Time   | 6 milliseconds typical (10 milliseconds max)   |
| Low Voltage Transfer to Battery Power (Setpoint)            | 89   |
| High Voltage Transfer to Battery Power (Setpoint)           | 145  |
| <b>SPECIAL FEATURES</b>                                     |  |
| Grounding Lug   | Includes side panel grounding lug  |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported   |
| High Availability UPS Features                              | Battery Independent Restart  |
| Green Energy-Saving Features                                | Greater than 95% efficiency - GREEN UPS  |
| <b>CERTIFICATIONS</b>                                       |  |
| UPS Certifications  | Meets FCC Part 15 Category A (EMI); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)   |
| UPS Certification Details                                   | UL1778: 2014 5th EDITION; CAN/CSA-C22.2 NO. 107.3:2014 3rd EDITION; FCC CLASS A; FCC Part 68 Approved (#5WSWP01B005); Industry Canada Approved (#3449A-005, RENO.1B); RETIE (Colombia)       |
| <b>WARRANTY</b>   |  |
| Product Warranty Period (U.S. & Canada)                     | 3-year limited warranty  |
| Product Warranty Period (Latin America)                     | 3-year limited warranty  |
| Product Warranty Period (International)                     | 2-year limited warranty  |
| Product Warranty Period (Mexico)                            | 3-year limited warranty  |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico)  | \$100,000 &nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &nbsp;  |

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>