

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com



USB C to VGA External Video Adapter (M/F), Displayport Alternate Mode, 1920 x 1200 (1080p)

MODEL NUMBER: U444-06N-VGA-AM









Description

The <u>U444-06N-VGA</u>-AM USB 3.1 Gen 1 to VGA Alternate Mode Dual/Multi-Monitor External Video Graphics Card Adapter supports USB DisplayPort Alternate Mode for displaying video on a VGA monitor or projector via your computer, tablet, laptop or smartphone's USB-C[™] port. It's an ideal tool for multitasking, viewing large spreadsheets, editing documents, giving presentations at trade shows and conferences, or playing games and watching movies on large screens.

You can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary display. No external power supply is needed. Connect the adapter's USB-C male plug to the USB-C port on your smartphone, tablet, Ultrabook or computer. Then, connect the adapter's VGA female port to a monitor using a VGA cable (such as Tripp Lite's P502-Series) to see and hear full DisplayPort audio and video.

The <u>U444-06N-VGA</u>-AM supports high-definition (HD) video resolutions up to 1920 x 1200 (@ 60 Hz), including 1080p, and data transfer rates up to 5 Gbps. It also supports 36-bit Deep Color (12 bits per channel). Compatible with USB-C devices that support USB DisplayPort Alternate Mode.

Features

Easy to Add a Display

- Supports USB DisplayPort Alternate Mode for transmitting video to a VGA display via your computer, tablet, laptop or smartphone's USB-C port
- Extend video to a second monitor, duplicate the same video on both monitors, or make the second monitor your primary display
- Ideal for multitasking, viewing spreadsheet data, editing documents, giving presentations, watching movies and playing video games

Highlights

- Supports USB DisplayPort
 Alternate Mode for transmitting
 video
- Extend video to a second display or duplicate one video on both
- Supports HD video resolutions up to 1080p (@ 60 Hz)
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- No external power supply or drivers required

System Requirements

- USB-C device that supports
 USB DisplayPort Alternate
 Mode
- VGA-enabled monitor

Package Includes

- <u>U444-06N-VGA</u>-AM USB 3.1
 Gen 1 to VGA Alternate Mode
 Dual/Multi-Monitor External
 Video Graphics Card Adapter
- Quick Start Guide



- No external power supply or drivers required
- Compatible with USB-C devices that support USB DisplayPort Alternate Mode

Vibrant, Superior Video Quality

- Supports high-definition video resolutions up to 1920 x 1200 (@ 60 Hz), including 1080p
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Supports 36-bit Deep Color (12 bits per channel)

Specifications

| MODEL TEXT | |
|--|---|
| Key Benefit | Connect a VGA monitor or projector to the USB Type-C [™] port on your computer or laptop. Ideal for multitasking, presenting at trade shows and conferences, editing documents, playing games and watching movies. |
| CONNECTIONS | |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | HD15 (FEMALE) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies