

Ultra Thin Toslink to Mini Toslink Digital Optical SPDIF Audio Cable, 2M (6.56 ft.)

MODEL NUMBER: A104-02M



Features

- Connect your digital audio equipment to your home theater system
- Ultra Thin cable is ideal for situations where space is at a premium
- Digital Optical Fiber offers the best in Audio clarity
- Precision polished optical termination minimizes loss for better high frequencies, and a more realistic stereo image
- Immune to all Electromagnetic and Radio-Frequency interference
- Eliminates distortion caused by inductance, capacitance, and resistance found in copper cables

Specifications

| OVERVIEW | |
|---------------------------------|--------------------|
| UPC Code | 037332189080 |
| Product Type | Passive |
| Technology | Toslink/SPDIF |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 6.6 |
| Cable Length (m) | 2.01 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |

Highlights

- Connect your digital audio equipment to your home theater system
- Ultra Thin cable is ideal for situations where space is at a premium
- Superior-grade optical fiber and precision polished optical terminations
- Best possible sound quality through digital fiber optic signals
- Immune to all forms of EMI/RFI

System Requirements

- Home Theater or Stereo equipment with Toslink/Mini Toslink capabilities

Package Includes

- 2M (6.6-ft.) Ultra Thin Toslink to Mini Toslink Digital Optical Audio Cable

| | |
|--------------------------------------|---------------------------|
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.04 |
| Shipping Weight (kg) | 0.02 |
| CONNECTIONS | |
| Side A - Connector 1 | TOSLINK (MALE) |
| Side B - Connector 1 | MINI TOSLINK (MALE) |
| Latching or Gripping Connector | No |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| IP20 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |