

Rigid Industrial F-Type Adapter (M/F) - IP68, Black

MODEL NUMBER: A200-FF-IND



Panel-mount adapter changes a male F-type connector to female, allowing a secure link between two male F-type connectors.

Features

Connects Coaxial Cabling on Plant Floors and Harsh Outdoor Environments

This rigid industrial adapter (M/F) fastens tightly to a male F-type connector and changes it to female. The A200-FF-IND is designed for coaxial cables' indoor or outdoor use wherever heavy vibrations, water and dust are present, including industrial plants, warehouses and other manufacturing settings.

IP68 Rating Denotes Resistance to Dust and Water

The IP68 rating means the A200-FF-IND is not only 100% protected against dust, but also able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance, keeping the cable safe in storms and other foul weather. The F-type connector locks into place to ensure your AV connection remains stable and secure.

High-Quality Components

The A200-FF-IND is recommended for transmitting high-definition television signals from cable/satellite boxes. Molded nickel-plated connectors with gold-plated contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission. An included dust cap keeps the adapter free of debris when not in use.

Highlights

- IP68 adapter endures immersion in water during harsh weather/industrial conditions
- Nickel connectors with gold contacts resist corrosion that can weaken the signal
- Polarized interface ensures proper mating of locking F-type connectors

Package Includes

A200-FF-IND Rigid Industrial F-Type Adapter (M/F), Black

Specifications

OVERVIEW	
UPC Code	037332287069
Technology	Coax
VIDEO	
HDR Support	No
3D Video Supported	No



Powering Business Worldwide

TRIPP LITE
SERIES

DisplayPort Alt Mode	No
CONNECTIONS	
Side A - Connector 1	F-TYPE (MALE) THREADED COAX
Side B - Connector 1	F-TYPE (MALE) THREADED COAX
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Material of Construction	MAIN BODY&DUST CAP: PBT+GF,UL94V-0; ALL HOOD: PVC; CHAIN: BRONZE, NICKEL PLATED
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.04
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154.4°F (-40° to 68°C)
Relative Humidity	10% TO 90% RH, NON-CONDENSING
COMMUNICATIONS	
EDID Compatible	No
Consumer Electronics Control (CEC) Supported	No
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
IP68 Rated	Yes
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Armored Cable	No
Driver Required	No



Powering Business Worldwide

TRIPP LITE
SERIES

DIN Mountable	No
Outdoor Use	Yes
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed
Product Compliance	REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.