

Position a 200A fuse link less than 18 in. from the battery in the positive line to protect against high-current draw that may occur during inverter failure.

## 1250W PowerVerter APS 12VDC 120V Inverter/Charger with Auto Transfer Switching, 2 Outlets

MODEL NUMBER: **APS1250**



Portable dual-outlet power source for power applications, such as power tools and computers, as a vehicle inverter, standalone AC power source or extended-run UPS. Ideal for RVs, fleet vehicles and emergency vehicles.

### Features

#### Reliable Power for Mobile, Emergency and Remote Sites

- Generates safe, stable, computer-grade 120V AC power from 12V battery bank
- Ideal for powering tools, saws, motors, pumps, portable lighting, appliances and computer equipment in heavy-load conditions
- Designed for easy installation in RVs, over-the-road trucks, fleet vehicles and emergency vehicles
- Functions as a vehicle inverter, standalone AC power source or extended-run UPS
- Features 2 front NEMA 5-15R outlets
- Unlimited runtime with variety of user-supplied batteries

#### Meets Normal and Peak Power Demands

- 1250W of continuous power
- 1850W of reserve power up to 1 hr.
- 2500W of peak power up to 10 sec. to accommodate surge power demands during equipment startup and cycling
- Automatic overload detector, built-in cooling fan and resettable AC circuit breaker protect unit from damage

### Highlights

- Delivers clean 120V AC power from AC or DC power source
- 1250W continuous output power; 2500W peak power
- Auto-transfer switching option for UPS operation
- Protects against blackouts, surges and EMI/RFI line noise
- Rugged polycarbonate housing resists moisture and impact

### Package Includes

- APS1250 1250W PowerVerter APS 12V DC 120V AC Inverter/Charger
- Owner's manual



#### Automatic Transfer Switching

- Transfer relay switches to inverter power during blackout in 16.6 ms
- 3-position switch enables Auto, Charge Only or System Off mode
- DIP switches configure high and low voltage auto-transfer

#### 3-Stage 30A Battery Charger

- Serves as battery charger when external 120V AC power is supplied and powering connected equipment
- Protects battery from overcharging and overdischarging
- Low-battery protection prevents excessive battery depletion
- DIP switches configure wet/gel charging profiles

#### Optional Remote Control Capability

- RJ45 communication port allows connection of optional remote control module, such as Tripp Lite's APSRM4

#### Front-Panel LEDs

- Indicate load level, battery charge level, shutdown status and system fault status

#### Rugged Polycarbonate Housing

- Resists moisture, vibration and impact
- Built-in mounting feet for installation on any rigid horizontal surface
- Grounding lug connects unit to earth ground or vehicle grounding system
- Built-in 6-ft. (1.83 m) AC power cord with NEMA 5-15P plug connects to AC power source

## Specifications

OVERVIEW	
UPC Code	037332121653
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	DC INPUT: Requires 12VDC input source capable of delivering 125A for the required duration (when used at full continuous capacity - DC requirements increase during OverPower and DoubleBoost operation). For automotive applications, professional hardwire installation with 225A minimum battery system fusing is recommended. AC INPUT: 120VAC
Maximum Input Amps / Watts	DC INPUT: Full continuous load - 127A at 12V DC. AC INPUT: 12 amps at 120VAC with full inverter and charger load (6.3A max charger-only)
Input Connection Type	DC INPUT: Set of 2 DC bolt-down terminals. AC INPUT: NEMA 5-15P input plug
Voltage Compatibility (VAC)	120
Voltage Compatibility (VDC)	12





**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Dimensions (hwd / in.)	12.60 x 10.60 x 10.20
Shipping Weight (kg)	11.02
Shipping Weight (lbs.)	24.30
Unit Dimensions (hwd / cm)	17.78 x 22.23 x 22.86
Unit Dimensions (hwd / in.)	7 x 8.75 x 9
Unit Weight (kg)	10.52
Unit Weight (lbs.)	23.2
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time (Line Power to Battery Mode)	16.6 milliseconds (typical - compatible with many computers, servers and networking equipment - verify transfer time compatibility of loads for UPS applications)
Low Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage drops to 75V (user adjustable to 85, 95, 105V - see manual)
High Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage increases to 135V (user adjustable to 145 - see manual)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>