

## 4-Port DisplayPort/USB KVM Switch - 4K 60 Hz, HDR, HDCP 2.2, IR, DP 1.4, USB Sharing

MODEL NUMBER: B005-DPUA4



Controls 4 DisplayPort-enabled desktop or notebook computers using one centralized DisplayPort or HDMI monitor and USB keyboard/mouse.

### Features

**Connects 4 DisplayPort-Enabled Devices to a Single Monitor, Keyboard and Mouse** This KVM switch lets you access, control, boot and reboot four computers with DisplayPort connectors and switch between them. In addition to desktop and notebook computers, the switch also connects up to four media centers, video game systems, Blu-ray and DVD players, cable and satellite boxes, DVRs and other DisplayPort-enabled devices. All computers share one monitor, USB keyboard and USB mouse, which saves space on your desk or workspace.

**Supports DisplayPort++ for Connecting an HDMI or DisplayPort Monitor** The B005-DPUA4 supports DP++, allowing incoming DisplayPort signals to be converted to HDMI. It features one DisplayPort output and one HDMI output, though only one monitor may be used at a time.

**Switching Between Computers Is Fast and Easy** Use the front-panel push buttons, hotkey commands, mouse movement or the included IR remote control for quick and easy toggling between computers. You can also use the Auto Scan feature to scan all connected computers in five-second intervals automatically. LEDs indicate which computer is currently selected.

**USB Hub Lets You Share Peripherals between Computers** Two USB 3.0 hub ports allow you to share USB peripherals, such as printers, hard drives, scanners, webcams and flash drives, between both connected computers. The ports support USB 3.0 data transfer speeds up to 5 Gbps and are backward compatible with earlier USB generations.

**Transmits Crystal-Clear True 4K Video with HDR and 4:4:4 Color** The B005-DPUA4 supports Ultra HD resolutions up to 4096 x 2160 (4K x 2K) at 60 Hz, as well as HDR video, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This KVM switch also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

**Designed for Convenient Mounting with Included Brackets** The heavy-duty metal housing comes with mounting brackets for permanent installation on a wall or beneath a desk with user-supplied hardware. The included DC power supply connects to any standard AC power source.

### Highlights

- Supports 4K @ 60 Hz video resolutions as specified in HDMI 2.0
- Carries High Dynamic Range (HDR) signals for expanded color accuracy
- Dual-mode DisplayPort (DP++) support allows connection of a local HDMI display
- Dual USB 3.0 hub ports let you share USB peripherals among connected computers
- Push buttons, hotkeys and included IR remote allow easy toggling between computers

### Applications

- Share a keyboard, mouse and screen with up to 4 computers
- Connect up to 4 gaming consoles, media centers or other A/V devices for a home theater system with 4K resolution
- Save money and space by sharing USB peripherals, such as a printer and external hard drive, among 4 connected computers

### System Requirements

- Console with DisplayPort or HDMI monitor, USB keyboard/mouse and (optional) speakers with 3.5 mm connectors
- Computers with DisplayPort connector, USB-A port and



- (optional) 3.5 mm audio jack
- Windows, macOS or Linux operating system

**Package Includes**

- B005-DPUA4 4-Port DisplayPort/USB KVM Switch
- IR extender
- IR remote control
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 3A)
- Mounting brackets
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332255020
Technology	DisplayPort; HDMI; Stereo Audio; USB; USB 3.0 (SuperSpeed)
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 5-15P North America
Bus Powered	No
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V; 50/60Hz; 0.6A
External Power Supply Output Specs (V / A)	5.0V, 3.0A
External Power Supply Cord Length (ft.)	3.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 16.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CCC; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White (KVM Port LED's) = Port in use; White (Power LED) = Power On; Green = Online



<b>PHYSICAL</b>	
Color	Black
Material of Construction	Metal
Rackmountable	No
Unit Dimensions (hwd / in.)	1.02 x 9.57 x 2.95
Unit Dimensions (hwd / mm)	26 x 243 x 75
Unit Packaging Type	Box
Unit Weight (kg)	0.50
Unit Weight (lbs.)	1.11
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113°F (0 to 45°C)
Storage Temperature Range	14 to 176°F (-10 to 80°C)
Power Consumption (Watts)	11.75
Operating Humidity Range	10% to 85% RH (No Condensation)
Storage Humidity Range	5% to 90% RH (No Condensation)
ESD Protection	+/- 8kV (air-gap discharge); +/- 4kV (contact discharge)
<b>COMMUNICATIONS</b>	
Hotkey	Yes
IP Remote Access	No
<b>CONNECTIONS</b>	
Ports	4
PC/Server Connections	DisplayPort; HDMI
Side A - Connector 1	(3) 3.5MM (FEMALE)
Side A - Connector 2	(2) USB 3.0 A (FEMALE)
Side B - Connector 1	(2) USB A (FEMALE)
Side B - Connector 2	HDMI (FEMALE)
Side B - Connector 3	(4) USB 3.0 B (FEMALE)
Side B - Connector 4	(5) DISPLAYPORT (FEMALE)
Side B - Connector 5	(10) 3.5MM (FEMALE)
Side B - Connector 6	3.5mm x 1.35mm (5V DC Barrel)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	Displayport; HDMI



Console Keyboard and Mouse Interface	USB
Console Monitor Interface	Displayport
<b>FEATURES &amp; SPECIFICATIONS</b>	
Autoscan (Y,N)	Y
Autoscan Duration	5 to 999 seconds
Number of Users	1
NIAP-Certified Secure	No
On-Screen Display (OSD)	No
Port Selection	Hotkey; Mouse; Pushbutton; Remote Selector
Max Supported Video Resolution	4K x 2K (4096 x 2160) @ 60 Hz (HDMI and DisplayPort)
Displayport Specification	1.4
HDMI Specification	2.0
HDCP Specification	1.4; 2.2
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	7.1 Surround Sound
Driver Required	No
Common Access Card (CAC) Support	No
Cat5 KVM Switch	No
Max Supported Color Depth	36-bit Deep Color
IR Remote Extension Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4
<b>SPECIAL FEATURES</b>	
HDR Support	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>