

Cat5e KVM Console Extender Kit

MODEL NUMBER: **B013-330**



Highlights

- Manage a PS/2 or USB computer/KVM switch from a remote location up to 330ft (100m) away
- Use readily available Cat5e cable for interconnection

Package Includes

- Transmitter and Receiver Unit (1 each)
- 3-ft. PC/KVM Cable Kit (1)
- Power Adapter (DC9V, 1A) for Receiver Unit (1)
- 4-ft. (1.22 m) USB A-B Cable (1)
- Quick Start Guide

Features

- Enables you to control a PS/2 or USB computer/KVM switch from a distance of up to 330ft (100m) away.
- Can control the computer or KVM switch via both Local and Remote Consoles.
- The remote connection is made using standard Cat5e cable
- Display mode of 1600 x 1200 @ 60Hz
- Shielded Cat5e cables provide better transmission integrity

Specifications

OVERVIEW	
UPC Code	037332143419
Accessory Type	Extender Kit
Technology	PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories
PRODUCT OVERVIEW	
Product Overview	Cat5e KVM Console Extender Kit
VIDEO	
Max Supported Video Resolution	1600 x 1200 @60Hz
HDR Support	No
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1A
AC Power Adapter Output Specs (V / A)	9V / 1.33A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
POWER	
Power Source Type	AC Adapter
Power Over Cable (PoC) Support	No
DC Barrel Plug	OD: 5.5 x 2.1 x 9.5mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	3.5
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	(2) HD15 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	USB B (FEMALE)
Side A - Connector 4	(2) MINI DIN-6 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	(2) MINI DIN-6 (FEMALE)
Computer Keyboard and Mouse Interface	PS/2; USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	PS/2
Console Monitor Interface	VGA
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Power); Green (Link)
PHYSICAL	
Color	Silver
Material of Construction	Steel
Rackmountable	No
Receiver Unit Dimensions (hwd / in.)	1 x 5.2 x 2.6
Receiver Unit Weight (lbs.)	1.3



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	5.40 x 6.90 x 8.00
Shipping Dimensions (hwd / cm)	13.72 x 17.53 x 20.32
Shipping Weight (lbs.)	2.60
Shipping Weight (kg)	1.18
Transmitter Unit Dimensions (hwd / in.)	1 x 5.2 x 2.6
Transmitter Unit Weight (lbs.)	1.3
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0%-90% RH, Non-Condensing
BTUs	11.9 BTU/Hr
COMMUNICATIONS	
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
USB Extension Support	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Recommended Category Cable	Cat5/Cat5e Cables
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; UL; cUL; TUV; CB
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.