



KVM Extender with VGA and USB Connections, Up to 330 ft.

MODEL NUMBER: B013-330-USB











Extends keyboard, mouse and monitor up to 330 ft. from your computer via Cat5 UTP cabling.

Features

Extends Console up to 330 ft. from Computer, KVM or Server

This KVM extender lets you control a computer, server or KVM switch from up to 330 feet (100 meters) away. Just connect the included transmitter and receiver with a Cat5 UTP cable (sold separately). Console ports on both the transmitter and receiver allow local or remote control of the connected device. Plus, the receiver doubles as a two-port KVM, allowing the connection of a local computer.

Recommended for Small to Medium-Sized Businesses (SMBs)

Being able to extend VGA video and USB signals up to 330 feet is ideal in commercial office spaces where the computers are not close to your workstation, as well as SMB applications needed KVM switches without requiring an IP network for long-distance control. The B013-330-USB supports VGA video resolutions up to 1920 x 1200.

Pure Hardware Solution Is Easy to Install and Operate

The B013-330-USB supports all major operating systems, including Windows and macOS. All necessary cables are included as a convenient off-the-shelf package, making the KVM Extender simple to maintain. As a pure hardware solution, you don't have to worry about software/network conflicts. This KVM Extender is compatible with any computers using VGA and USB connections.

Specifications

OVERVIEW		
-		
UPC Code	037332288875	
Console	No	
Accessory Type	Extender Kit	
Technology	USB 2.0 (High Speed)	
Accessory Class	KVM Switch Accessories	

Highlights

- Extends VGA video + USB keyboard/mouse from your computer up to 330 ft.
- Console ports on each end allow for local or remote control of connected computer
- Receiver doubles as 2-port KVM, allowing for connection of a local computer
- Supports VGA video resolutions up to 1920 x 1200, including 1080p
- Easy to install and operate with all necessary cables included

Package Includes

- Transmitter
- Receiver
- (2) USB KVM combo cables
- USB-A to USB-B upgrade cable (M/M)
- (2) External power supplies (Input: 100–240V, 50/60 Hz, 0.6A; Output: 5V 2A) with 6 ft. (1.8 m) cord
- (8) International plug adapters
- · Quick Start Guide





VIDEO		
Number of Monitors Supported	1	
Video Ports	HD15 (FEMALE)	
Max Supported Video Resolution	1920 x 1200 @60Hz	
Max. Distance (Between any 2 Units)	330FT (100M)	
Max Number of Ports (Entire Chain)	2	
Transmitter Video Input	VGA	
HDR Support	No	
3D Video Supported	No	
EDID Support	Yes	
INPUT		
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America	
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A	
AC Power Adapter Output Specs (V / A)	DC 5V/2A	
AC Power Adapter Cord Length (ft.)	6	
AC Power Adapter Cord Length (m)	1.8	
Nominal Input Voltage(s) Supported	100V AC; 240V AC	
Maximum Input Amps	1	
Voltage Compatibility (VAC)	100-240	
Input Frequency	50/60 HZ	
Redundancy - Dual Power Inputs	No	
Bus Powered	No	
POWER		
Power Source Type	AC Adapter with detachable power cord	
AC Plug Type	AS/NZS 3112; BS1363; CEE 7/16 Schuko; NEMA 1-15P	
Power Over Cable (PoC) Support	Yes	
AC Adapter	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America	
DC Barrel Plug	OD: 3.5 x 1.35 x 7.5mm, Positive Pin, Negative Sleeve	
CONNECTIONS		
Number of Ports	2	
Computer/Server Ports	(2) HD15 (FEMALE)	
Firmware Upgrade Port	(x2) USB-B	





PC/Server Connections	USB; VGA	
Side A - Connector 1	(2) HD15 (FEMALE); RJ45 (MALE); (2) USB A (FEMALE); (1) USB B (FEMALE)	
Side B - Connector 1	(2) HD15 (FEMALE); RJ45 (MALE); (2) USB A (FEMALE); (1) USB B (FEMALE)	
Included Cable (Side A) - Connector 1	(1) USB A (FEMALE)	
Included Cable (Side B) - Connector 2	(1) USB B (FEMALE)	
Included KVM Cable (Equipment Side) - Connector 1	(1) HD15 (FEMALE)	
Included KVM Cable (Equipment Side) - Connector 2	(1) HD15 (FEMALE), (1) USB A (FEMALE), (1) PS/2	
Computer Keyboard and Mouse Interface	USB	
Computer Monitor Interface	HD15; VGA	
Console Keyboard and Mouse Interface	PS/2; USB	
Console Monitor Interface	HD15; VGA	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	Receiver- 1X (Red) Power; 3X (Green) Link RX & TX; Transmitter- 1X (Red) Power; 3X (Green) Link, Video & Control	
PHYSICAL		
Color	Black	
Material of Construction	Metal	
Rackmountable	No	
Receiver Unit Dimensions (hwd / in.)	1.02 x 5.15 x 2.55	
Receiver Unit Weight (lbs.)	0.639	
Shipping Dimensions (hwd / in.)	7.95 x 5.47 x 6.92	
Shipping Weight (lbs.)	0.24	
Transmitter Unit Dimensions (hwd / in.)	1.02 x 5.15 x 2.55	
Transmitter Unit Weight (lbs.)	0.639	
Unit Dimensions (hwd / in.)	1.020 x 5.150 x 2.550	
Unit Packaging Type	Вох	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Relative Humidity	0 to 90%, Non-Condensing	
COMMUNICATIONS		





Hotkey	YES	
Port Control	Push Buttons, Hotkeys, OSD	
IP Remote Access	No	
Transmission Distance	330 ft.	
EDID Compatible	Yes	
IR Remote Extension Support	No	
Consumer Electronics Control (CEC) Supported	No	
Latency	Zero	
USB Extension Support	Yes	
FEATURES & SPECIFICATIONS		
USB Specification	USB 1.1 (up to 12 Mbps)	
NIAP-Certified Secure	No	
Number of Users	1	
Autoscan (Y,N)	N	
On-Screen Display (OSD)	Yes	
Port Selection	Hotkey; OSD; Pushbutton	
Driver Required	No	
Recommended Category Cable	Cat5,Cat5e	
REMOTE ACCESS		
Modem Port	No	
STANDARDS & COMPLIANCE		
External Power Supply Certifications	CE; FCC; GS; NOM; TUV; UKCA; UL; WEEE; cUL	
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); EN 55032; EN 55035; IEC 62368-1; NOM (Mexico); TUVus; UL 62368-1	
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS; UKCA; WEEE	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.