

## 750W APS X Series 12VDC 230V Inverter/Charger with Auto-Transfer Switching, 2 C13 Outlets

MODEL NUMBER: **APSX750**



Portable dual-outlet power source for small power applications as a vehicle inverter, standalone AC power source or extended-run UPS. Ideal for RVs, commercial and fleet vehicles and emergency vehicles.

### Description

The APSX750 750W APS X Series 12V DC 230V AC Inverter/Charger is a reliable power source for a wide variety of equipment ranging from power tools and portable lighting to laptop computers and sensitive monitoring equipment. With no fumes, fuel or excess noise, it's an excellent alternative to generator power.

The DC-to-AC inverter features an automatic line-to-battery transfer switch and integrated charging system that allow it to work as a vehicle inverter, standalone AC power source or extended-run UPS. It delivers 750W of continuous power, 1125W up to one hour, or 1500W of peak power up to 10 seconds during equipment startup or cycling. An automatic overload detector, cooling fan and resettable AC circuit breakers protect the unit from damage.

Designed for easy installation in RVs, over-the-road trucks, fleet vehicles and conversion vans, the APSX750 converts stored power from any 12V battery or automotive DC source to safe, stable, computer-grade AC power for unlimited runtime. When hardwired to an external 230V AC source, the unit keeps the user-supplied battery charged via a three-stage 5/20A selectable charging system while simultaneously delivering AC power to connected equipment.

When used as a UPS, the APSX750 responds to blackouts and brownouts with an automatic, instantaneous transfer to battery-derived AC output. LEDs on the unit indicate load percentage and battery charge level.

### Features

#### Reliable Power for Mobile, Emergency and Remote Sites

- Generates safe, stable, computer-grade 230V AC power from 12V battery bank
- Ideal for powering tools, saws, motors, pumps, portable lighting, appliances and computer equipment in heavy-load conditions
- Designed for easy installation in RVs, commercial and fleet vehicles, emergency vehicles and construction equipment
- Functions as a vehicle inverter, standalone AC power source or extended-run UPS
- Features dual C13 outlets
- Unlimited runtime with variety of user-supplied batteries

### Highlights

- Delivers clean 230V AC power from AC or DC source
- 750W continuous output power; 1500W peak power
- Auto-transfer switching option for UPS operation
- Protects against blackouts, surges and EMI/RFI line noise
- Rugged polycarbonate housing resists moisture and impact

### Package Includes

- APSX750 750W APS X Series 12V DC 230V AC Inverter/Charger
- Owner's manual

**Meets Normal and Peak Power Demands**

- 750W of continuous power
- 1125W of reserve power up to 1 hr.
- 1500W of peak power up to 10 sec. to accommodate surge power demands during equipment startup and cycling
- Automatic overload detector, built-in cooling fan and resettable AC circuit breakers protect unit from damage
- High-current DC input terminals for simple hardwired installation

**Automatic Transfer Switching**

- Transfer relay switches to inverter power during blackout in 10 ms
- 3-position switch enables Auto, Charge Only or System Off mode
- DIP switches configure high and low voltage auto-transfer

**3-Stage 5/20A Selectable Battery Charger**

- Serves as battery charger when external 230V AC power is supplied and powering connected equipment
- Protects battery from overcharging and overdischarging
- Low-battery protection prevents excessive battery depletion
- DIP switches configure wet/gel charging profiles

**Optional Remote Control Capability**

- RJ45 port allows connection of optional remote control module, such as APSRM4

**Front-Panel LEDs**

- Indicate load percentage and battery charge level

**Rugged Polycarbonate Housing**

- Resists moisture, vibration and impact
- Built-in mounting feet for installation on any rigid horizontal surface

## Specifications

OVERVIEW	
UPC Code	037332121622
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Maximum Input Amps / Watts	DC INPUT: Full continuous load - 72A at 12VDC. AC INPUT: 6.2A at 230VAC with full inverter and charger load (2.2A max charger-only / combined input load to support charger and AC output is automatically controllable to 66%-33%-0% based on AC output loading using the charger limiting set points - see manual for setting instructions)
Recommended Electrical Service	DC INPUT: Requires 12VDC input source capable of delivering 72A for the required duration (when used at full continuous capacity - DC requirements increase during OverPower and DoubleBoost operation). For automotive applications, professional hardwire installation with 100A minimum battery system fusing is recommended. AC INPUT: 230VAC
Input Connection Type	DC INPUT: Set of 2 DC bolt-down terminals. AC INPUT: IEC-320 C14 inlet connection





Powering Business Worldwide



Shipping Dimensions (hwd / in.)	12.40 x 10.50 x 10.70
Shipping Dimensions (hwd / cm)	31.50 x 26.67 x 27.18
Shipping Weight (lbs.)	24.50
Shipping Weight (kg)	11.11
Unit Dimensions (hwd / in.)	7.000 x 8.750 x 9.000
Unit Dimensions (hwd / cm)	17.78 x 22.23 x 22.86
Unit Weight (lbs.)	18.6
Unit Weight (kg)	8.44
<b>ENVIRONMENTAL</b>	
Relative Humidity	0%-95% Non-Condensing
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time (Line Power to Battery Mode)	Transfer time from line power to battery mode: 10 milliseconds (typical - compatible with many computers, servers and networking equipment - verify transfer time compatibility of loads for UPS applications)
Low Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage drops to 144V (user adjustable to 163, 182, 201V - see manual)
High Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage increases to 272V
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.