

## Isobar 10-Outlet A/V Surge Protector, 8-ft. Cord, 3384 Joules, Tel/Coax/Ethernet Protection

MODEL NUMBER: AVBAR10



### Description

Tripp Lite's AVBAR10 Platinum Series Isobar Audio Video Surge / Spike Suppressor provides premium protection (3384 joules) stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for any Audio/Video installations: high-definition video displays, HD Cable / HD satellite sources and A/V receivers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 10 outlets (widely spaced outlets accommodate up to 4 transformers and plug-in safety covers), 3-line HD 2.2 Ghz coaxial protection, 1-Ethernet RJ45 surge protection jack and 1-line tel/modem protection safeguard an entire A/V system. \$500,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). Includes all-metal housing, three diagnostic LEDs (Line OK, Grounded & Protected) and 8-ft. cord with a right-angle plug. Additional accessories include; 8-ft. coaxial cable, 6 ft. network cable and 6-ft. phone cord.

### Features

- 3384 joules surge / spike suppression protection rating
- EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- Isolated Filter Banks eliminate interference between connected components
- All-metal housing safely withstands the strongest surges
- 10 surge-protected NEMA 5-15R AC outlets safeguard an Audio / Video system
- Widely spaced outlets accommodate up to 4 transformers
- Four plug-in safety covers protect against accidental contact
- 3 sets of surge-protected Type F gold HD 2.2 GHZ coaxial connectors (with included 6-ft. coaxial cable) safeguard components on cable, satellite or antenna line
- 1-Ethernet RJ45 surge protection jack (with included 6-ft. network cable) safeguards router and network
- 1-line tel/modem surge protection (with included 6-ft. phone cord) safeguards personal video recorders (Satellite, PVRs) on a single dial-up line.
- 8-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a audio video system

### Highlights

- 10 outlets / 8-ft. cord with space saving right angle plug
- 3384 joule rating
- Isolated Filter Banks
- 3-line High Definition 2.2 GHz (gold) coaxial surge protection
- 1-Ethernet RJ45 surge protection jack
- 1-line tel/modem surge protection
- All-metal housing

### Package Includes

- AVBAR10 Platinum Series Audio Video Surge / Spike Suppressor
- 6 ft. coaxial cable
- 6 ft. network cable
- 6 ft. phone cord
- Instruction manual with warranty information

- 3 diagnostic LEDs alert user to protection, line power and fault status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- All-metal housing (black) stands up to the most demanding environments
- UL and cUL listed, RoHS compliant
- \$500,000 Ultimate Lifetime Insurance (USA, Canada and Puerto Rico only) covers connected components against surge damage...for life!

## Specifications

OVERVIEW	
UPC Code	037332143839
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V, 15A
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	150,000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	12
Transformer Accommodation	(6) Yes
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm line power, protection and ground status
SURGE / NOISE SUPPRESSION	



Powering Business Worldwide



AC Suppression Joule Rating	3384
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	Yes
Network (Ethernet) Protection Details	1 line
Telephone/DSL Protection	Yes
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between horizontal tabs = 355.09mm; Distance between vertical tabs = 58.17mm
Outlets Measurement (Center to Center)	Distance between standard horizontal outlets = 39.45mm; Distance between standard outlet and transformer outlet = 52.42mm; Distance between transformer outlets = 53.01mm; Distance between vertical outlets = 38.76mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	17.25 x 9.25 x 3.25
Shipping Dimensions (hwd / cm)	43.82 x 23.50 x 8.26
Shipping Weight (lbs.)	4.00
Shipping Weight (kg)	1.81
Unit Dimensions (hwd / in.)	2.500 x 14.500 x 3.500
Unit Dimensions (hwd / cm)	36.20 x 5.72 x 8.89
Unit Weight (lbs.)	3.5
Unit Weight (kg)	1.59
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$500,000 &nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &nbsp;

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.