

TAA-Compliant NetDirector 16-Port Cat5 KVM Switch 1U Rack-Mount

MODEL NUMBER: **B064-016**



Description

Tripp Lite's 16-Port NetDirector 1U Rackmount Cat5 KVM Switch, is the next generation of our cost-effective, feature rich, KVM switches. It's sleek, 1U design and compact size, features RJ45 connection ports that utilize inexpensive Cat5 patch cables, reducing the amount of cable clutter normally found with traditional KVM cabling. Easily switch between CPU's with Push Buttons, Hot-Key commands, or built-in On Screen Display (OSD) menu function. Daisy-chaining allows connection to up to 512 computers. Compatible with PS/2 and USB computers, VGA, SVGA, or XGA monitors, as well as the following OS platforms: DOS, Windows (all versions), LINUX, UNIX, HP UX, and SUN. Supports both PS/2 and USB Mouse and Keyboards into the switch. Constructed of heavy-duty steel housing. Server Interface Units required at the server side to convert patch cables back to VGA and USB and/or PS/2 connections.

Features

- Directly connect up to 16 computers; or, expand the number of connected computers to up to 512 by daisy-chaining up to 31 additional levels of B064-016 KVM Switches
- Control multiple computers from a single keyboard, monitor and mouse. Both USB and PS/2 keyboards and mice are supported
- RJ45 connectors and Cat5e/6 cable allow for a more efficient installation
- 1U Rackmountable...Rackmount hardware Included
- Quickly access connected computers via On Screen Display (OSD), Push-button or Hotkey commands
- Firmware upgradeable using the included RJ11 to DB9 firmware upgrade cable
- Multi-language support; OSD can be displayed in English, German, Japanese, Traditional Chinese or Simplified Chinese
- Compatible with Windows, Mac, Linux, UNIX, Novell, Sun and DOS operating systems. Supports video resolutions up to 1600 x 1200 (60Hz) at 131 ft. (40 m.), or up to 1280 x 1024 (75Hz) at 164 ft. (50 m.)

Highlights

- 16 RJ45 Ports utilize inexpensive Cat5 patch cables
- Expandable - control up to 512 servers from a single station
- USB and PS/2 keyboards and mice are supported
- Quickly access connected computers via On Screen Display (OSD), Push-button or Hotkey commands
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Compatible with Windows, Mac, Linux, UNIX, Novell, Sun and DOS operating systems

KVM INPUT

- A monitor with a VGA (HD15) input that is capable of supporting the highest video resolution that you will be using on the connected computers
- A USB or PS/2 mouse
- A USB or PS/2 keyboard

CONNECTED COMPUTERS

- A VGA (HD15) input
- A USB A Female port, or two PS/2 keyboard/mouse ports

Package Includes

- B064-016 KVM Switch
- Rackmount Hardware
- RJ11 to DB9 Firmware Upgrade



- Two-level password security; add up to 1 Administrator and 10 User accounts
- Use Server Interface Units B055-001-PS2 or B055-001-
- 100-240V, 50/60Hz, 1A
- Power Consumption: 120V (6.7W), 230V (7.3W)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Constructed of heavy-duty steel housing

- Cable
- C13 to 5-15P Power Cord
 - Grounding Wire
 - Foot Pads
 - Owner's Manual CD

Specifications

OVERVIEW	
UPC Code	037332159199
Max CPU	512
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 11.68 x 54.61
Shipping Dimensions (hwd / in.)	9.00 x 4.60 x 21.50
Shipping Weight (kg)	3.67
Shipping Weight (lbs.)	8.10
Unit Dimensions (hwd / cm)	4.32 x 43.18 x 15.24
Unit Dimensions (hwd / in.)	1.7 x 17 x 6
Unit Weight (kg)	2.77
Unit Weight (lbs.)	6.1
ENVIRONMENTAL	
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Operating Temperature	0 to 40 C (32 to 104 F)
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	No
CONNECTIONS	
Ports	16
PC/Server Connections	VGA; USB; PS/2
Local Console Ports - Port 3	2 x USB A Female



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FEATURES & SPECIFICATIONS	
Autoscan (Y,N)	Y
Number of Users	1
NIAP-Certified Secure	No
Cat5 KVM Switch	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>