

16-Port Cat5 KVM over IP Switch - 19 in. LCD, 1 Remote or 1 Local User, 1U Rack-Mount, TAA

MODEL NUMBER: B064C-16-1-IP









All-in-one KVM over IP switch with built-in console lets you connect computers and servers via Cat5 cabling.

Features

Control as Many as 16 Computers or Servers from Anywhere in the World

This NetDirector® Cat5 KVM over IP switch provides complete control of up to 16 computers and/or servers located up to 100 feet (30.5 meters) away. The B064C-16-1-IP is a comprehensive network management solution that installs in 1U of space in an EIA-standard 19-inch rack using the included hardware. No server-resident software is required, so server performance and reliability are never compromised. Flash-upgradable firmware over an Ethernet network fine-tunes compatibility with emerging standards.

Simple Network Control That Gives You More Flexibility

This Cat5 switch gives you a rack-mountable keyboard, LCD and touchpad in a single console, designed to ease multi-server management in data centers, server rooms and other high-density environments. Built-in IP capability allows a local or a remote user to access the network independently. You may also select a connected computer using a remote toolbar, OSD (on-screen display), pushbuttons or hot keys. An LED per port indicates which connected computers are online or in use.

High-Resolution On-Screen Display Offers Multi-Language Support

The advanced OSD with high-resolution video up to 1920 x 1200 (at 60 Hz) or 1280 x 1024 (at 75 Hz) provides a GUI with management tools, including auto-scanning and panel array mode. The OSD may be set to display in English, German, Russian, Japanese, traditional Chinese or simplified Chinese.

Allows Connection of Either PS/2 or USB Keyboard and Mouse

PS/2 and USB console ports are included. Only one keyboard/mouse combination may be connected at a time.

Supports Both IPv4 and IPv6 Addresses

The B064C-16-1-IP supports IPv4 and IPv6 protocols. Remote access avoids costly and time-consuming travel to the server room or network closet. You may set the IP address manually or have it automatically assigned via DHCP server (the default method). A non-browser client is available that allows Windows computers to remotely access the KVM without the need for a browser and without the need to install Java.

Heightened Security for Every Connection

Multi-level password protection helps prevent unauthorized persons from gaining access to connected servers/computers. Remote authentication support is provided via RADIUS and LDAP/S. The B064C-16-

Highlights

- Lets you control computers and servers locally or over LAN, WAN or Ethernet
- Remote or local user can control up to 16 computers or servers at the same time
- Daisy-chain up to 128 computers or servers to expand your network
- Built-in sliding console with large 19 in. LCD supports 1920 X 1200 @ 60 Hz
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Windows, Linux, UNIX, Novell, Sun, DOS or macOS operating system
- Internet Explorer (6 and higher), Firefox (1.5 and higher), Mozilla (1.7 and higher), Safari (2.0 and higher), Opera (9.0 and higher) or Netscape (8.1 and higher) web browser

Package Includes

- B064C-16-1-IP NetDirector 16-Port Cat5 KVM over IP Switch
- Detachable C13-to-C14 power cord
- Firmware upgrade cable
- Rail-mounting kit (pre-installed)
- L brackets (pre-installed)
- Installation instructions



1-IP also incorporates advanced encryption technologies: 128-bit RC4, 168-bit 3DES, 256-bit AES and 56-bit DES. You can install SSL certificates to ensure secure transactions between web servers and browsers. An easy-to-access log tracks events on your installation.

TAA-Compliant for GSA Schedule Purchases

The B064C-16-1-IP is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW		
UPC Code	037332284532	
Product Type	Console KVM Switch	
Console	Yes	
Max CPU	128	
Technology	Cat5/5e; PS/2; USB 2.0 (High Speed); VGA/SVGA	
VIDEO		
Number of Monitors Supported	1	
Video Ports	VGA	
Resolutions Supported	1920 x 1200 @ 60Hz	
Max Supported Video Resolution	Local: 1920 X 1200 @ 60Hz Remote: 1920 X 1200 @ 60Hz Resolution: 1280 x 1024 @ 75Hz	
Max Number of Ports (Entire Chain)	128	
HDR Support	No	
3D Video Supported	No	
DISPLAY		
Response Time	5 ms	
Viewing Angle	170° (H), 160° (V)	
INPUT		
AC Power Adapter Plug(s)	IEC-320-C14	
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1A	
AC Power Adapter Cord Length (ft.)	6.6	
AC Power Adapter Cord Length (m)	2	
Nominal Input Voltage Description	100-240VAC, 50-60HZ	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240	
Input Frequency	50/60Hz	
Input Current	1A	



Power Input Receptacle	IEC-320-C14	
POWER		
Power Source Type	Power Cord	
CONNECTIONS		
Number of Ports	16	
Computer/Server Ports	16	
Daisy-Chain Port	Y	
Firmware Upgrade Port	Y	
PC/Server Connections	Serial	
Side A - Connector 1	(16) RJ45 (FEMALE)	
Local Console Ports - Port 3	1	
Console Keyboard and Mouse Interface	PS/2; USB	
Console Monitor Interface	VGA	
Daisy-chainable / Cascadable	Yes	
Daisy-chainable / Cascadable Details	1x DB-25 Male	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	Online: 16 (Green); Selected: 16 (Orange); x1 Power, 1x Num Lock (Green), 1x Caps Lock (Green), 1x Scroll Lock (Green)	
BUNGLOAL		
PHYSICAL		
Primary Form Factor	Rackmount	
Color	Black	
Material of Construction	Metal	
Housing Color	Black	
LCD Monitor (in.)	19	
Rackmountable	Yes 22.07 v. 20.27 v. 5.54	
Shipping Dimensions (hwd / in.)	32.67 x 26.37 x 5.51	
Shipping Weight (lbs.)	40.34	
Shipping Weight (kg)	18.30	
Unit Dimensions (hwd / in.)	26.774 x 17.669 x 1.732	
Unit Dimensions (hwd / cm)	68.01 x 44.88 x 4.40	
Unit Packaging Type	Box	
Unit Weight (lbs.)	31.3	
Unit Weight (kg)	14.20	



Rack Units	1	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Relative Humidity	0% to 80% RH, Non-Condensing	
Operating Humidity Range	5% TO 85% RH, NON-CONDENSING	
Storage Humidity Range	5% TO 85% RH, NON-CONDENSING	
COMMUNICATIONS		
Hotkey	Y	
Port Control	Push Buttons, Hotkeys, OSD	
IP Remote Access	Yes	
EDID Compatible	No	
IR Remote Extension Support	No	
PORT EXPANSION		
Daisy-chainable or Cascadable	128 (via Daisy-chain with B022-U08	
FEATURES & SPECIFICATIONS		
Mounting Accessory Included	Yes	
NIAP-Certified Secure	No	
Number of Users	1	
Autoscan (Y,N)	Y	
On-Screen Display (OSD)	No	
Port Selection	Hotkey; OSD; Pushbutton	
Driver Required	No	
Authentication Supported	LDAP; LDAPS; MS Active Directory; RADIUS	
Autoscan Duration	1-255 Sec	
BUILT-IN CONSOLE		
Console Screen Size (inches)	19	
REMOTE ACCESS		
Modem Port	No	
STANDARDS & COMPLIANCE		
Product Certifications	EN 55032; EN 55035; ICES (Canada); NOM (Mexico); RCM (Australia & New Zealand)	
Product Compliance	CE (Europe); FCC Part 15 Class A (USA); FCC Part 15 Class B (USA); RoHS; Trade Agreements Act (TAA); UKCA	



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.