

2-Port DVI/USB KVM Switch with Audio and Cables

MODEL NUMBER: **B004-DUA2-K-R**



Features

- Fast, easy switching via keyboard hotkeys or pushbuttons
- Plug-and-play setup - no software required
- Hot-swap capability allows easy addition or removal of computers without powering down the switch or other computers
- Speaker and microphone connections allow for the sharing of audio components between systems
- Independent audio/mic and USB peripheral switching function allows for an uninterrupted experience. A computer can be printing on a printer connected to one of the USB 2.0 peripheral ports, while you listen to audio from and access another computer; all at the same time.
- Supports 2-Channel Stereo Audio
- Features two USB 2.0 ports for the sharing of USB peripherals (e.g. flash drives, printers, etc.) between the connected computers
- Uses DVI-I technology, allowing for the transmission of a digital (up to 1920 x 1200) or analog (up to 2048 x 1536) signal. A DVI to VGA adapter, such as Tripp Lite's P126-000, is required for conversion to an analog monitor.
- To connect to a HDMI monitor, a DVI to HDMI adapter such as Tripp Lite's P132-000 is required (Audio is not supported when converting from DVI to HDMI).
- Full time DDC support provides the necessary EDID information for optimal video performance on Windows 7 and other operating systems
- Supports Microsoft® IntelliMouse® and the scrolling wheel on most mice
- (x2) 4-ft. (1.22 m) USB cables and (x2) 4-ft. (1.22 m) DVI + Audio KVM cable kits included
- Compatible with all major operating systems

Specifications

Highlights

- Control 2 computers with a single DVI monitor, USB keyboard and USB mouse
- Switch ports via keyboard hotkeys or pushbuttons
- Allows for the sharing of audio components between systems; listen to music from one computer while accessing another
- Features two USB 2.0 ports for the sharing of USB peripherals between the connected computers
- (x2) 4-ft. (1.22 m) USB cables and (x2) 4-ft. (1.22 m) DVI + Audio KVM cable kits included
- Full time DDC support provides the necessary EDID information for optimal video performance on Windows 7 and other operating systems
- Compatible with all major operating systems

System Requirements

- KVM Console: A DVI monitor, USB keyboard, and USB mouse
- Computers: DVI-I port (P118-000 DVI-I to DVI-D Adapter is required for computers with DVI-D ports), and USB Port
- Audio (Optional): A microphone and speakers with 3.5mm Mini-Stereo connectors and a computer with 3.5mm Mini-Stereo ports
- Compatible with all major operating systems

Package Includes

- B004-DUA2-K-R
- (x2) 4-ft. (1.22 m) DVI-I + 3.5mm Audio Cable kits
- (x2) 4-ft. (1.22 m) USB A-B Device Cables
- Owner's Manual
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.4A Output: 5V, 2A)



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

| OVERVIEW | |
|---|--|
| UPC Code | 037332140036 |
| Max CPU | 2 |
| Technology | USB 2.0 (High Speed); DVI; Stereo Audio |
| VIDEO | |
| Max Supported Video Resolution | 1920 x 1200 (Digital), 2048 x 1536 (Analog) |
| INPUT | |
| AC Power Adapter Plug(s) | NEMA 1-15P North America |
| AC Power Adapter Input Specs (V / Hz / A) | 100-240V / 50/60Hz / 1.0A |
| AC Power Adapter Output Specs (V / A) | 5V / 2.4A |
| AC Power Adapter Cord Length (ft.) | 5 |
| AC Power Adapter Cord Length (m) | 1.5 |
| Voltage Compatibility (VAC) | 100; 110; 120; 127; 200; 208; 220; 230; 240 |
| POWER | |
| Power Source Type | AC Adapter |
| DC Barrel Plug | OD: 5.5 x 2.5 x 9.5mm, Positive Pin, Negative Sleeve |
| Power Consumption (Watts) | 4.7 |
| CONNECTIONS | |
| Number of Ports | 2 |
| PC/Server Connections | DVI; USB |
| Side A - Connector 1 | (2) DVI-I (FEMALE) |
| Side A - Connector 2 | (2) USB B (FEMALE) |
| Side B - Connector 1 | DVI-I (FEMALE) |
| Side B - Connector 2 | (4) USB A (FEMALE) |
| Side B - Connector 3 | (2) 3.5MM (FEMALE) |
| Computer Keyboard and Mouse Interface | USB |
| Computer Monitor Interface | DVI-I Single-Link |
| Console Keyboard and Mouse Interface | USB |
| Console Monitor Interface | DVI-I Single-Link |
| Connector Plating | Nickel |
| USER INTERFACE, ALERTS & CONTROLS | |



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

| | |
|--------------------------------------|-----------------------------|
| LED Indicators | Green (PC 1); Blue (PC 2) |
| PHYSICAL | |
| Color | Silver |
| Material of Construction | ABS |
| Cable Jacket Color | Silver |
| Shipping Dimensions (hwd / in.) | 5.60 x 8.20 x 7.10 |
| Shipping Dimensions (hwd / cm) | 14.22 x 20.83 x 18.03 |
| Shipping Weight (lbs.) | 2.90 |
| Shipping Weight (kg) | 1.32 |
| Unit Dimensions (hwd / in.) | 1.000 x 6.000 x 2.500 |
| Unit Packaging Type | Box |
| Unit Weight (lbs.) | 0.4 |
| Unit Weight (kg) | 0.18 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 104°F (0° to 40°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Relative Humidity | 0%-90% RH, Non-Condensing |
| BTUs | 245.52 |
| COMMUNICATIONS | |
| IP Remote Access | No |
| FEATURES & SPECIFICATIONS | |
| USB Hub Ports | Yes |
| Number of USB Hub Ports | 2 |
| USB Specification | USB 2.0 (up to 480 Mbps) |
| NIAP-Certified Secure | No |
| Number of Users | 1 |
| Port Selection | Pushbutton; Hotkey |
| Driver Required | No |
| STANDARDS & COMPLIANCE | |
| External Power Supply Certifications | FCC; UL; cUL; TUV; CB |
| Product Certifications | ICES (Canada); NOM (Mexico) |
| Product Compliance | FCC (USA); WEEE |

WARRANTY & SUPPORT

| | |
|--|-------------------------|
| Product Warranty Period (Worldwide) | 3-year limited warranty |
|--|-------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.