

2-Port Manual VGA/SVGA Video Switch (3x HD15F)

MODEL NUMBER: **B112-002-R**



Highlights

- 2-port HD15 VGA/SVGA Push-Button Switch
- Rugged Metal Case

System Requirements

- Computer with an HD15 port
- VGA or SVGA monitor with HD15M cable

Package Includes

- B112-002-R Manual VGA/SVGA 2 Position Switch

Description

Tripp Lite's 2-Port Manual VGA/SVGA Switch is the optimal solution for connecting two computers to one monitor or two monitors to one computer. The 2-Port Manual VGA/SVGA Switch features a fully-shielded rugged metal case with front-panel push-button switching. Interior printed circuit board design allows for crystal clear resolutions up to 1600x1280. It does not require any AC power to operate.

Features

- Connects two computers to one monitor or two monitors to one computer
- Fully-shielded rugged metal case with front-panel push button switch
- Does not require external power, software, or complicated set-up procedures

Specifications

OVERVIEW	
UPC Code	037332014269
INPUT	
Bus Powered	Yes
PHYSICAL	
Color	Silver
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	2.54 x 12.45 x 8.89



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	1.00 x 4.90 x 3.50
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
Unit Dimensions (hwd / in.)	0.94 x 4.4 x 2.7
Unit Packaging Type	Box
Unit Weight (kg)	0.15
Unit Weight (lbs.)	0.33
ENVIRONMENTAL	
Operating Temperature Range	14 to 131 F (-10 to 55 C)
Storage Temperature Range	5 to 131 F (-15 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
Power Consumption (Watts)	0.5
CONNECTIONS	
Ports	2
Side A - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton
Max Supported Video Resolution	1920 x 1080 @60Hz
Driver Required	No
EDID Compatible	Yes
Technology	VGA/SVGA
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>