

Most HDMI source devices are able to provide the necessary power for the operation of the switch. If additional power is required, a 5V 2A DC power supply (not included) using a 3.5 x 1.35 mm output plug with a positive tip and negative sleeve can be used.

3-Port HDMI Mini Switch with Remote Control - 4K (HDMI F/3xF), 3D, HDCP 1.4, EDID

MODEL NUMBER: B119-003-UHD-MN



Connect 3 HDMI source devices to a single HDMI monitor and switch back and forth between them.

Description

The B119-003-UHD-MN 3-Port Mini HDMI Switch allows you to connect three HDMI source devices to one port on an HDMI monitor and switch back and forth between them. For instance, you can connect your Blu-ray player, video game system and cable/satellite DVR to one HDMI port on your high-definition television. Or you can connect three computers or media centers to a monitor for displaying digital signage or giving presentations.

Switch between source devices using buttons on the unit or the included remote control. The included IR extender receiver lets you hide the unit out of sight while still being able to switch devices up to 16 feet (5 meters) away using the remote. When the currently used device is powered off, the unit automatically switches to the next powered-on device.

The B119-003-UHD-MN ensures top-quality audio/video applications with Ultra High Definition (UHD) video resolutions up to 4K at 30 Hz (3840 x 2160) and 48-bit True Color (16 bits per channel), as well as DTS-HD, Dolby True-HD and 7.1-channel surround sound audio. It's compatible with 3D, HDCP and EDID. Hassle-free functionality requires no software, drivers or external power supply. Sets up in seconds.

Features

Connects 3 HDMI Devices to 1 HDMI Display Switch between source devices via pushbuttons on unit or included remote control
Ideal for home audio/video applications, presentations and digital signage Included IR extender receiver lets you control devices from a distance using the remote
Automatically switches to next available device when currently used device is powered off

Features Top-of-the-Line Audio and Video Supports Ultra High Definition (UHD) video resolutions up to 4K @ 30 Hz (3840 x 2160)
Supports 48-bit True Color (16 bits per channel)
Supports DTS-HD, Dolby True-HD and 7.1-channel surround sound audio
Compatible with 3D, HDCP 1.4 and EDID

Sets Up in Seconds Plug-and-play operation with no software required for easy, immediate installation

Specifications

Highlights

- Switch source devices using buttons or included remote control
- Switches to next port when current device is powered off
- Supports UHD resolutions up to 4K @ 30 Hz for crystal-clear video
- Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- HDMI-enabled devices and monitor

Package Includes

- B119-003-UHD-MN 3-Port Mini HDMI Switch
- Remote control
- IR extender receiver
- Owner's manual

OVERVIEW	
UPC Code	037332189233
Technology	HDMI; IR
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K @ 30Hz)
Max Supported Color Depth	48-bit Deep Color
3D Video Supported	Yes
AUDIO	
Audio Specification	7.1 Channel Surround Sound, DTS-HD, and Dolby TrueHD
INPUT	
Bus Powered	Yes
POWER	
Power Source Type	USB
Power Consumption (Watts)	1
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (1, 2, 3)
PHYSICAL	
Color	Black
Material of Construction	ABS
Rackmountable	No
Shipping Dimensions (hwd / in.)	5.30 x 2.70 x 1.00
Shipping Dimensions (hwd / cm)	13.46 x 6.86 x 2.54
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
Unit Dimensions (hwd / in.)	0.700 x 3.200 x 2.300
Unit Packaging Type	Box
Unit Weight (lbs.)	0.12
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)

Storage Temperature Range	14 to 176 F (-10 to 80 C)
BTUs	3.4 BTU/Hr
Operating Humidity Range	10% to 85 % RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
IR Remote Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	(3) HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton
HDCP Specification	1.4
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty