

## 8-Port Console Server with Dual GbE NIC, 4Gb Flash and 4 USB Ports

MODEL NUMBER: B093-008-2E4U



Rack console for remotely accessing and controlling serial-based networking equipment through one highly secure gateway.

### Features

**Access All Your Serial and Network Devices from Anywhere in the World**The B093-008-2E4U 8-port console server provides secure in-band (primary network) and out-of-band (alternate channel) remote access to serial- and network-connected routers, network switches, firewalls, PBX systems, UPS systems, PDUs and other devices. It offers reliable network connectivity with dual Gigabit primary and failover Ethernet ports. You can use it in a wide variety of applications, including wiring closets, branch offices, point-of-sale and other remote sites where quick resolution of network issues is imperative.

**Simple and Flexible Accessibility**Eight serial RS-232 console ports are configured to use standard Cat5e/6 patch cable when connecting to Cisco devices. They integrate with industry-standard directory servers using TACACS+, RADIUS, LDAP and Kerberos authentication. Provides 4Gb of internal NAND flash memory.

**Connect an External Modem for Out-of-Band Access**Connect one of the eight RS-232 ports to an external Multitech MT9234MU-CDC-XT or US Robotics USR5637 USB modem (sold separately) to receive out-of-band (alternate channel) access when remote sites experience a network outage.

**Router/Gateway**Each gateway can port forward to an unlimited number of locally networked hosts (computers, routers). This rack console also includes a built-in stateful firewall and embedded DHCP server to host a separate management LAN for critical traffic.

**The Utmost in Security to Keep Your Sensitive Data Private**The B093-008-2E4U supports the following security features and standards: PCI DSS 3.2, FIPS 140-2, SSL and SSH, stateful firewall, OpenVPN and IPSec VPN support. The embedded FIPS 140-2 OpenSSL cryptographic module is validated to meet FIPS 140-2 standards and has received Certificate #2473.

**PowerMan PDU and UPS Support**This 8-port console server uses PowerMan for PDU and RPC management and Network UPS Tools for UPS system monitoring and management. It provides support for a range of power products, so you can remotely manage power to your connected equipment.

**USB Console and Digital I/O (DIO) Ports**Four USB 2.0 console ports allow connection to newer devices with USB console ports, such as a wide variety of PDUs and UPS systems with WEBCARDLX and LX Platform remote management cards. Two DIO ports are included for connecting compatible devices, such as drive relays and alarms.

### Highlights

- Manage routers, UPS systems and other serial-based equipment from anywhere at any time 24/7
- Validated to meet FIPS 140-2 standards to ensure utmost protection of private data
- Dual Gigabit Ethernet ports for primary network connection and automatic failover
- Designed for standard Cat5e/6 patch cable when connecting to Cisco devices
- Easy installation on desktop or 19 in. racks using included mounting hardware

### Applications

- Securely access and control servers, routers, KVM switches and other serial-connected devices in your data center 24/7
- Manage diverse server and device platforms using a network connection
- Oversee IT infrastructure remotely via network
- Troubleshoot equipment issues without spending time/money traveling to remote locations

### Package Includes

- B093-008-2E4U 8-Port Serial Console Server with Dual GbE NIC, 4Gb Flash and 4 USB Ports
- Terminal block
- DB9F to RJ45 crossover serial adapter
- External power supply w/4 ft. cord (Input: 100–240V, 50/60 Hz, 0.4A; Output: 12V 1.25A)
- (4) International plug adapters (North America, Europe, U.K., Australia)
- Rack-mounting hardware
- (4) Rubber feet
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

**Compact Design for Convenient Mounting**The heavy-duty steel housing comes with mounting brackets for easy installation in an EIA-standard 19-inch rack. Its fanless form factor also allows desktop deployment on four included rubber feet that help prevent the unit from sliding.

**TAA-Compliant for GSA Schedule Purchases**This serial console server is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

**4-Year Warranty and Environmentally Responsible Design**The B093-008-2E4U comes with a 4-year warranty. It's manufactured in compliance with strict RoHS specifications.

## Specifications

OVERVIEW	
UPC Code	037332209306
Multi-User	Yes
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.4A
AC Power Adapter Output Specs (V / A)	12V / 1.25A
AC Power Adapter Cord Length (ft.)	4
AC Power Adapter Cord Length (m)	1.2
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Redundancy - Dual Power Inputs	No
Bus Powered	No
POWER	
Power Source Type	AC Adapter
Power Consumption (Watts)	11.5
CONNECTIONS	
Number of Ports	8
Side A - Connector 1	(2) RJ45 (FEMALE)
Side B - Connector 1	(8) RJ45 (FEMALE); (4) USB A (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	7 LED's for Power, Heartbeat-Firmware Running, Serial Connectivity and Network Ports
PHYSICAL	
Color	Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Material of Construction	Metal
Rackmountable	Yes
Shipping Dimensions (hwd / in.)	4.10 x 7.10 x 9.10
Shipping Dimensions (hwd / cm)	10.41 x 18.03 x 23.11
Shipping Weight (lbs.)	2.60
Shipping Weight (kg)	1.18
Unit Dimensions (hwd / in.)	1.400 x 5.100 x 4.700
Unit Dimensions (hwd / cm)	2.86 x 8.89 x 10.16
Unit Packaging Type	Box
Unit Weight (lbs.)	1.3
Unit Weight (kg)	0.59
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-13° to 140°F (-25° to 60°C)
Storage Temperature Range	-40° to 167°F (-40° to 75°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	39.2 BTU/Hr
<b>COMMUNICATIONS</b>	
IP Remote Access	Yes
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3; 802.3ab; 802.3ad
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
IP68 Rated	No
IP20 Rated	No
On-Screen Display (OSD)	No
Port Selection	GUI
Driver Required	No
Authentication Supported	RADIUS; LDAP; TACACS
Common Access Card (CAC) Support	No
<b>REMOTE ACCESS</b>	
Modem Port	No
<b>STANDARDS &amp; COMPLIANCE</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

External Power Supply Certifications	CE; FCC; UL; TUV; PSE; C-Tick; GS; RoHS; CB
Product Certifications	C-Tick (Australia); UL Listed
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	4-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.