

2-Port Manual VGA/SVGA Video Switch (3x HD15F)

MODEL NUMBER: B112-002-R



Highlights

- 2-port HD15 VGA/SVGA Push-Button Switch
- Rugged Metal Case

System Requirements

- Computer with an HD15 port
- VGA or SVGA monitor with HD15M cable

Package Includes

- B112-002-R Manual VGA/SVGA 2 Position Switch

Description

This 2-Port Manual VGA/SVGA Switch is the optimal solution for connecting two computers to one monitor or two monitors to one computer. The 2-Port Manual VGA/SVGA Switch features a fully shielded rugged metal case with front-panel push-button switching. Interior printed circuit board design allows for crystal clear resolutions up to 1600 x 1280. It does not require any AC power to operate.

Features

- Connects two computers to one monitor or two monitors to one computer
- Fully-shielded rugged metal case with front-panel push button switch
- Does not require external power, software, or complicated set-up procedures

Specifications

OVERVIEW	
UPC Code	037332014269
Product Type	Switch
Technology	VGA/SVGA
VIDEO	
Max Supported Video Resolution	1920 x 1080 @ 60Hz
HDR Support	No
INPUT	
Bus Powered	Yes
Product Length (in.)	4.41



Powering Business Worldwide

TRIPP LITE
SERIES

Product Length (ft.)	0.37
POWER	
Power Consumption (Watts)	0.5
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
Input x Output	2 x 1
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Rackmountable	No
Shipping Dimensions (hwd / in.)	4.53 x 1.06 x 3.27
Shipping Dimensions (hwd / cm)	11.51 x 2.69 x 8.31
Shipping Weight (lbs.)	3.53
Shipping Weight (kg)	1.60
Unit Dimensions (hwd / in.)	0.940 x 4.400 x 2.700
Unit Packaging Type	Box
Unit Weight (lbs.)	0.33
Unit Weight (kg)	0.15
ENVIRONMENTAL	
Operating Temperature Range	14° to 131°F (-10° to 55°C)
Storage Temperature Range	5° to 131°F (-15° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
COMMUNICATIONS	
EDID Compatible	Yes
IR Remote Extension Support	No
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton
Driver Required	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.