

2-Port HDMI Splitter - HDCP 2.2, 4K @ 60 Hz, HDR, TAA

MODEL NUMBER: **B118-002-UHD-2**



Transmits Ultra High Definition (UHD) 4K x 2K audio/video (A/V) from an HDMI source to two HDMI displays at the same time. Recommended for digital signage in classrooms, churches, office buildings, restaurants/bars, etc.

Description

The B118-002-UHD-2 2-Port 4K 3D HDMI Splitter transmits a UHD 4K @ 60 Hz (3840 x 2160) audio/video signal from an HDMI source, such as a Blu-ray player or computer, to two HDMI monitors, projectors or televisions at the same time. Ideal for classrooms, churches, offices, restaurants, bars, trade shows and anywhere else featuring 4K x 2K digital signage, the B118-002-UHD-2 is quick and simple to install with no software or drivers necessary.

Using standard 28 AWG HDMI cabling, this splitter can transmit a 4K (3840 x 2160) signal up to 15 feet (4.6 meters). It supports a wide range of audio formats, including DTS-HD, Dolby TrueHD, Dolby Digital Plus, and LPCM 7.1-channel surround sound, as well as 36-bit Deep Color (12 bits per channel). The Full 3D-compliant B118-002-UHD-2 also supports HDCP 2.2 for up-to-date content protection.

Note: The B118-002-UHD-2 sends the same image to all connected displays. If you would like to extend an image over multiple displays, you will need an MST hub, such as the B156-002-HD-V2.

Features

Transmits a 4K HDMI A/V Signal to 2 HDMI Displays Simultaneously

- Recommended for 4K digital signage in classrooms, churches, offices, restaurants, bars, trade shows, etc.
- Distributes A/V signals up to 15 ft. (4.6 m) when used with standard 28 AWG HDMI cable
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Compliant with HDCP 2.2 and EDID to ensure compatibility with latest A/V hardware
- Cascade up to 3 levels of splitters together to increase the number of connected monitors up to 32.

Supports the Most Up-To-Date Features and Formats

- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Full 3D
- DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1-channel surround sound audio

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (3840 x 2160) for crystal-clear video
- Distributes A/V up to 15 ft. when used with 28 AWG HDMI cable
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Expand the number of connected displays, up to 32, by cascading up to 3 levels of splitters together
- Plug-and-play operation with no software required for easy, immediate installation

Package Includes

- B118-002-UHD-2 2-Port 4K 3D HDMI Splitter
- External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A)
- International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual



- 36-bit Deep Color (12 bits per channel)
 - Video amplifier bandwidth of 600 MHz/6 Gbps per channel (18 Gbps total)
 - Lip sync pass-through, xvYCC and x.vColor
- Easy to Use Almost Anywhere**
- Plug-and-play operation with no software required for easy, immediate installation
 - Supports desktop use or wall-mounting using included hardware
 - Power supply includes international plug adapters (North America, Europe, U.K. and Australia)
- TAA-Compliant**
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332200648
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A, 4 ft
Technology	HDMI
VIDEO	
Max Supported Video Resolution	4K @ 60Hz (3840 x 2160)
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
AUDIO	
Audio Specification	DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 5-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
Bus Powered	No
Product Length (in.)	3.61
Product Length (ft.)	0.300
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60HZ, 0.35A
External Power Supply Output Specs (V / A)	5V / 2A



External Power Supply Cord Length (ft.)	4.0
External Power Supply Cord Length (m.)	1.2
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; PSE; C-Tick; GS; RoHS
Power Over Cable (PoC) Support	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x1) Green (Power), (x2) Orange (Signal)
PHYSICAL	
Color	Black
Included Mounting Accessories	Yes
Material of Construction	Metal
Rackmountable	Yes
Shipping Dimensions (hwd / cm)	5.51 x 18.39 x 16.41
Shipping Dimensions (hwd / in.)	2.17 x 7.24 x 6.46
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	0.99
Unit Dimensions (hwd / cm)	5.49 x 16.38 x 18.39
Unit Dimensions (hwd / in.)	2.16 x 6.45 x 7.24
Unit Packaging Type	Box
Unit Weight (kg)	0.08
Unit Weight (lbs.)	0.187
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
CONNECTIONS	
Ports	2



Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH, WEEE, NOM, ISO9001
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>