

## DisplayPort to HDMI over Cat6 Extender Kit, Box Transmitter/Wall Plate Receiver, 4K 60 Hz, 4:4:4, PoC, HDCP 2.2, 230 ft. (70.1 m), TAA

MODEL NUMBER: B127A-1A1-BDFH



Extender kit with transmitter and receiver extends a 4K DisplayPort signal via Cat6 cable to an HDMI display up to 230 ft. away.

### Features

#### Cat6 Extender Kit Ideal for Digital Signage in Schools, Restaurants and Lecture Halls

This complete transmitter and receiver system is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings, hotels and other digital signage applications where the source and display are farther apart than conventional A/V cables allow. The metal transmitter box and the single-gang metal wall plate receiver with metal back cover blend perfectly into the room décor.

#### Extends a 4K A/V Transmission up to 230 ft....or Even Farther

The B127A-1A1-BDFH extends 4K signals from a DisplayPort source device to an HDMI display up to 230 feet (70.1 meters) away via user-supplied Cat6 cabling. By adding a Tripp Lite B127A-010-H HDMI repeater (sold separately) to the application, you can extend the signal up to 400 feet (121.9 meters).

#### Transmits Crystal-Clear 4K Video with Multi-Channel Audio and 4:4:4 Color

The B127A-1A1-BDFH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as specified in HDMI 2.0, with 7.1-channel surround sound. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This extender kit also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

#### Built-In PoC Technology Provides Power to Avoid Bulky External Power Bricks

After you connect the included external power supply to the transmitter, Power over Cable (PoC) technology powers the receiver over Cat6 cable. LEDs on both the transmitter and receiver will light up to indicate the system is receiving power and a signal is being transmitted. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to install the receiver where best needed without worrying about finding a nearby AC outlet.

#### Local HDMI Port on Transmitter Supports 4K @ 60 Hz Resolution

To monitor the video signal being extended to the receiver, connect a 4K display to the transmitter's local HDMI port with a user-supplied HDMI cable. This port does not support multi-resolution capabilities, so the connected monitor must also support 4K/60 Hz to function properly.

### Highlights

- Supports 4K @ 60 Hz video resolutions (4:4:4) as specified in HDMI 2.0
- Power over Cable (PoC) technology provides power to the receiver via Cat6 cable
- Transmitter's local port shows you the 4K image being displayed at the other end
- Stretches 230 ft. signal to 400 ft. with addition of optional B127A-010-H repeater
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Extend video signals from one room to another using Cat6 cable, which can pass through conduit to meet building codes
- Gain flexibility in where the receiver is installed, with the freedom to install it away from an AC outlet
- Improve the line of sight for digital signage in a hotel, restaurant, theater, house of worship, trade show or other location

### System Requirements

- Source device with DisplayPort output (computer, media server, laptop)
- Display device with HDMI input (HDTV, projector, monitor)

### Package Includes

- Box transmitter
- Wall plate receiver
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 24V 1A)
- (4) International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual



#### Plug-and-Play Operation for Quick Setup and Immediate Use

The included transmitter and receiver units work right out of the box with no software required. Connect the transmitter to the source with a user-supplied DisplayPort cable (such as Tripp Lite's P580-Series). Then, connect the receiver to the display with a user-supplied HDMI cable (such as Tripp Lite's P569-XXX-CERT or P568-XXX-2A). Finally, connect the two units with user-supplied Cat6 patch cable (such as Tripp Lite N202-Series). Mounting hardware is included for both units.

#### TAA-Compliant for GSA Schedule Purchases

The B127A-1A1-BDFH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

## Specifications

OVERVIEW	
UPC Code	037332263995
Product Type	Extender Kit
Technology	Cat5/5e; Cat6; DisplayPort; HDMI; POC
VIDEO	
Video Input	DISPLAYPORT (FEMALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	(2) HDMI (FEMALE)
Video Ports Details	DisplayPort 1.2a; HDMI 2.0; HDCP 1.4; HDCP 2.2
Resolutions Supported	3840 x 2160 (4K x 2K) @ 60 Hz (both Local HDMI port and HDMI Output)
Max Supported Video Resolution	3840 x 2160 @ 60 Hz
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230
Transmitter Video Input	DisplayPort
Transmitter - Number of Video Outputs	2
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	230



Signal Range (m)	70
Range Extension using other Tripp Lite product	170 ft or 230 ft
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Extended Mode	Yes
Extended Mode Details	x1 HDMI Port (4K/60 Hz)
Mirror Mode	Yes
Mirror Mode Details	x1 HDMI Port (4K/60 Hz)
Other Tripp Lite product used to extend range	B127A-010-H or B127A-110-BH
Max Supported Color Depth	36-bit Deep Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	230
Maximum Signal Range (m)	70
<b>AUDIO</b>	
Audio Ports	HDMI (FEMALE)
Audio Ports Details	HDMI outputs support passthrough audio formats including LPCM2.0/5.1/7.1
Audio Input	Displayport
Audio Output	HDMI
Audio Specification	Pass-through of Audio format includes LPCM2.0/5.1/7.1
<b>INPUT</b>	
Bus Powered	No
<b>POWER</b>	
Power Source Type	AC Adapter
AC Plug Type	AS/NZS 3112; BS1363; CEE 7/16 Schuko; NEMA 1-15P
Power Source	Transmitter end only (Included)
Power Over Cable (PoC) Support	Yes
Receiver Power Source	AC Adapter (Optional); Power Over Cable
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60 Hz / 0.6A
External Power Supply Output Specs (V / A)	24V / 1A
External Power Supply Cord Length (ft.)	4.53



External Power Supply Cord Length (m.)	1.38
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Transmitter: (1) Power = Green (unit is receiving power); (1) RJ45 Port = Green (power), Orange (data being sent). Receiver: (1) Data = Orange (data being received from transmitter over Cat6 cabling).
<b>PHYSICAL</b>	
Material of Construction	Metal
Color	Black; White
Included Mounting Accessories	(2) Mounting Brackets, (6) Screws
Number of Displays	1
Form Factor/Mounting Options	Wallplate
Rackmountable	Yes
Receiver Unit Dimensions (hwd / cm.)	11.5 x 7 x 3.38
Receiver Unit Dimensions (hwd / in.)	4.528 x 2.756 x 1.331
Receiver Unit Weight (kg)	0.65
Receiver Unit Weight (lbs.)	1
Shipping Dimensions (hwd / cm)	5.51 x 35.20 x 16.41
Shipping Dimensions (hwd / in.)	2.17 x 13.86 x 6.46
Shipping Weight (kg)	1.03
Shipping Weight (lbs.)	2.27
Transmitter Unit Dimensions (hwd / cm.)	2.7 x 11.5 x 6.24
Transmitter Unit Dimensions (hwd / in.)	1.063 x 4.528 x 2.457
Transmitter Unit Weight (kg)	0.65
Transmitter Unit Weight (lbs.)	1
Unit Packaging Type	Box
Unit Weight (lbs.)	1
Unit Weight (kg)	0.45
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104F (0 to 40C)
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	0 to 85% RH, Non Condensing



<b>COMMUNICATIONS</b>	
Signal Range (ft.)	230
Signal Range (m)	70
Transmission Distance	230 ft
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
Latency	0
USB Extension Support	No
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (FEMALE)
Side A - Connector 2	HDMI (FEMALE)
Side A - Connector 3	RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Displayport Specification	1.2a
HDCP Specification	1.4; 2.2
Driver Required	No
Recommended Category Cable	24AWG Cat6
All-in-One Kit	Yes
DIN Mountable	No
Integrated/Removable Cable	No
MST Support	No
Mounting Accessory Included	Yes
Multi-Resolution Support	Yes
Built-In Equalizer	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
External Power Supply Certifications	CCC; CE; FCC; GS; TUV; UL; cUL
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	1-year limited warranty
--	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>