

DVI Extender Equalizer, Single-Link Video Repeater, 1920x1200 at 60Hz / 1080p (DVI F/F), up to 150ft., TAA

MODEL NUMBER: **B120-000-SL**



Description

Tripp Lite's B120-000-SL DVI Single-Link Signal Extender increases the distance a DVI-D signal can be transmitted beyond the recommended 16 ft. (5 m.). Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p, as well as a maximum distance of 150 ft. from the source. Use P561-Series DVI Single-Link cables in most applications. When extending a 1920 x 1200 (or 1080p) video signal more than 75 ft., use cable made with 24Awg wiring. (Available from Tripp Lite as a custom order) Simply connect the longer cable between the source and the B120-000-SL, and the shorter cable (16 ft. or less) between the adapter and the monitor. Software or drivers are not required. Built-in Equalization control to adjust the video image. HDCP and DDC compatible. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Extend a DVI-D Single-Link signal up to 150 ft. from the source
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- Use P561-Series DVI Single-Link cables in most applications
- When extending a 1920 x 1200 (or 1080p) video signal more than 75 ft., use a cable made with 24Awg wiring (Available from Tripp Lite as a custom order)
- Built-in Equalization control to adjust the video image
- HDCP and DDC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- Extend a DVI-D Single-Link signal up to 150 ft. from the source
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- Use P561-Series DVI Single-Link cables in most applications.
- When extending a 1920 x 1200 (or 1080p) video signal more than 75 ft., use cable made with 24Awg wiring
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B120-000-SL DVI Single Link Extender
- External Power Supply with NEMA 1-15P Plug(Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Screwdriver for equalization adjustment
- Owner's Manual



OVERVIEW	
UPC Code	037332167118
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	5.59 x 18.29 x 16.51
Shipping Dimensions (hwd / in.)	2.20 x 7.20 x 6.50
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	150
Max 480P Range (ft)	151
Max 1440 x 900 Range (ft)	150
Max 1080i Range (ft)	150
Max 1080P Range (ft)	150
Max 480i Range (ft)	151
Max 640 x 480 Range (ft)	150
Max 800 x 600 Range (ft)	150
Max 1600 x 1200 Range (ft)	150
Max 720P Range (ft)	150
CONNECTIONS	
Ports	1
Side A - Connector 1	DVI-I (FEMALE)
Side B - Connector 1	DVI-I (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	DVI
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>