

HDMI over Fiber Extender Kit - 4K @ 60 Hz, RS-232, IR, USB, Duplex Multimode LC, 985 ft., TAA

MODEL NUMBER: **B127F-1A1-MM-HH**



Transmitter/receiver kit extends a 4K HDMI signal via multimode fiber cable to a HDMI monitor up to 985 ft. away.

Features

HDMI Extender for Digital Signage or Displaying Video in Schools or Trade Show Booths

This complete transmitter and receiver system is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings and digital signage applications where the source and display are farther apart than conventional A/V cables allow. The B127F-1A1-MM-HH extends 4K video and stereo audio signals from an HDMI source device to an HDMI monitor up to 985 feet (300 meters) away via user-supplied duplex multimode LC fiber cabling.

Transmits Crystal-Clear 4K HDMI Video with Multi-Channel Audio and 4:4:4 Color

The B127F-1A1-MM-HH supports Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with full, rich uncompressed DTS-HD, Dolby TrueHD and uncompressed 7.1-channel digital audio. Built-in equalization automatically fine-tunes the image quality at the remote display with no time-consuming manual fiddling needed. It's compatible with HDCP 2.2, HDMI 2.0 and EDID standards for carrying HDR (high dynamic range) signals. It also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

DIP Switches Extend Your Choice of USB, IR or RS-232 Signals

The DIP switches on both the transmitter and receiver can be adjusted to let you choose from the USB 1.1, bi-directional IR and RS-232 functions. Only one function can be extended at a time.

Plug-and-Play Operation for Quick Setup and Immediate Use

The included transmitter and receiver units work right out of the box with no software required. Mounting hardware is included for installing the units on walls, poles or 19-inch racks. Connect the transmitter to the source and the receiver to the display with HDMI cables (such as Tripp Lite's P569-Series). Then, connect a duplex multimode LC fiber cable (Tripp Lite N820-Series) to the built-in 10G transceivers on the two units. Connect an optional display to the transmitter's local HDMI output to see the image connected to the receiver up to 985 feet away.

TAA-Compliant for GSA Schedule Purchases

The B127F-1A1-MM-HH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports uncompressed DTS-HD, Dolby AC-3 and 7.1-channel digital audio
- Meets HDMI 2.0 standards, including 4:4:4 subsampling for HDR televisions
- Transmitter's local HDMI port allows you to see the Ultra HD image being displayed
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a media server, cable/satellite box, gaming system or other home theater component to a large-screen 4K television or projector
- Upgrade the video quality of your trade show presentation or digital signage installation in a commercial or educational setting to 4K x 2K
- Increase the distance between your video source and video display up to 985 ft.

System Requirements

- Source device with HDMI output (media server, laptop)
- Display device with HDMI input (HDTV, projector, monitor)
- Fiber Patch Cables supporting 10Gb or higher



Package Includes

- Transmitter unit
- Receiver unit
- IR-IN cable
- IR-OUT cable
- (2) RS-232 terminal blocks
- (2) External power supplies with 4.5 ft. cord (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A)
- (8) International plug adapters (North America, Europe, Australia, United Kingdom)
- (2) Sets of mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332239143
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240~50/60Hz, 0.35A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
External Power Supply Certifications	CCC; CE; FCC; GS; TUV; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Tx: x3 ORANGE (Link Indicator, Local, Signal Transmission), x1 Green (Power) RX: x1 Orange (Link Indicator), x1 Green (Power)
PHYSICAL	
Color	Black



Material of Construction	Metal
Rackmountable	Yes
Receiver Unit Dimensions (hwd / in.)	1.06 x 4.53 x 2.46
Receiver Unit Weight (lbs.)	0.5
Transmitter Unit Dimensions (hwd / in.)	1.06 x 4.53 x 2.46
Transmitter Unit Weight (lbs.)	0.5
ENVIRONMENTAL	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	5 to 122°F (-15 to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	985
Signal Range (m)	300
CONNECTIONS	
Side A - Connector 1	(2) 3.5MM (FEMALE); MICRO-USB B (FEMALE)
Side A - Connector 2	(2) HDMI (FEMALE); LC DUPLEX (FEMALE)
Side B - Connector 1	(2) 3.5MM (FEMALE); (2) USB A (FEMALE)
Side B - Connector 2	HDMI (FEMALE); LC DUPLEX (FEMALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	4K x 2K (3840 x 2160) @60Hz
HDMI Specification	2.0
HDCP Specification	2.2
Audio Specification	True uncompressed 8-channel LPCM, AC-3, DTS digital audio
Driver Required	No
EDID Compatible	Yes
Power Over Cable (PoC) Support	No
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
Technology	HDMI; HDR
Wavelength	850nm
Chroma Sub Sampling	4:4:4
Mode Type	Multimode



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SPECIAL FEATURES	
HDR Support	Yes
CERTIFICATIONS	
Certifications	Tested to CE, FCC, REACH, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>