


1-Port HDMI over Cat6 Extender Kit, Pigtail Transmitter/Receiver, 4K 60 Hz, HDR, 4:4:4, 230 ft. (70.1 m), TAA

MODEL NUMBER: **B127U-111-PHPH**



HDMI extender kit with pigtail transmitter and receiver extends a 4K signal via Cat6 cable to an HDMI monitor up to 230 ft. away.

Features

HDMI Extender Kit Ideal for Digital Signage in Schools, Restaurants and Lecture Halls

This complete transmitter and receiver system is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings, hotels and other digital signage applications where the source and display are farther apart than conventional A/V cables allow. The B127U-111-PHPH extends 4K signals from an HDMI source to an HDMI monitor up to 230 feet (70.1 meters) away via user-supplied Cat6 cabling. The one-foot pigtail design of the transmitter and receiver makes the units easy to install, especially in tight spaces.

Transmits Crystal-Clear 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color

The B127U-111-PHPH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with uncompressed DTS-HD, Dolby TrueHD and 7.1-channel digital audio. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K content with no complications. This extender kit also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Create Daisy-Chain Installations with HDMI Outputs, DisplayPort Outputs or Both

The B127U-111-PHPH is compatible with additional HDMI (B127U-110-PH) and DisplayPort (B127U-110-PD) receivers (sold separately) in a four-link daisy-chain installation. Each additional receiver adds up to 230 feet (70.1 meters) to the maximum video transmission distance and up to a total of 920 feet (280 meters) for the entire installation. **Note:** See the installation diagram in the owner's manual for more information.

Multi-Resolution Support Allows Mixing and Matching of Displays of Different Resolutions

Say you have a brand new 4K/60 Hz HDTV in the living room, but want to also connect your Blu-ray player or media server to the older 1080p TV in the kitchen and the 4K/30 Hz monitor in your home office. The B127U-111-PHPH is backward compatible with 4K/30 Hz and 1080p resolutions via automatic switching, allowing each connected television to display video at its maximum resolution without affecting the other outputs.

Local HDMI Port on Transmitter Supports 4K @ 60 Hz Resolution

To monitor the video signal being extended to the transceiver, connect a 4K display to the transmitter's

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Compact transmitter and receiver are USB-powered through display or power adapter
- Supports multi-resolution output to allow for combination of different display types
- Plug-and-play operation with no software required for easy, immediate installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Source device with HDMI output (Blu-ray player, PC, media server)
- Display device(s) with HDMI input (HDTV, projector, monitor)

Package Includes

- Pigtail transmitter
- Pigtail receiver
- Owner's manual

local HDMI port with a user-supplied HDMI cable. This port does not support multi-resolution capabilities, so the connected monitor must also support 4K/60 Hz to function properly.

Plug-and-Play Operation for Quick Setup and Use

The included transmitter and receiver units work right out of the box with no software required. Both feature a one-foot USB-A pigtail connector as the primary power source. Plug the USB connector on the transmitter into a USB-A power adapter (such as U280-W01-QC3-1, sold separately), and plug the receiver into the display's USB-A port. User-supplied 24 AWG Cat6 cabling connects the transmitter and receiver. **Note:** *The transmitter and receiver can also be powered through their Micro-USB ports.*

TAA-Compliant for GSA Schedule Purchases

The B127U-111-PHPH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332281470
Product Type	Pigtail Video Extender Kit
Technology	Cat6; HDMI
Host Connector	HDMI (MALE)
VIDEO	
Video Input	HDMI (MALE)
Video Output	HDMI (MALE)
Number of Monitors Supported	2
Video Ports	HDMI (MALE)
Video Ports Details	HDCP 1.4; HDCP 2.2
Resolutions Supported	Up to 4K (3840 x 2160) @ 60 Hz
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 1920x1200; 2560x1600; 3840x2160 (4K)
Max Supported Video Resolution	4K x 2K @ 60 Hz
Max. Distance (Between any 2 Units)	230 ft.
Max. Distance (Between any 2 Units) (Meters)	70
Max 1080P Range (ft)	230
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230



Powering Business Worldwide



Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	230
Signal Range (m)	70
Range Extension using other Tripp Lite product	N/A
Recommended Cabling	N202-Series Cat6 Gigabit Snagless UTP Ethernet Cabling P568-XXX-CERT Series 4K/60 Hz HDMI Cables
Other Tripp Lite product used to extend range	N/A
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	230
Maximum Signal Range (m)	70
EDID Support	Yes
Signal Transmission	Unidirectional
DisplayPort Alt Mode	No
DSC Support	No
AUDIO	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	Passthrough audio formats including LPCM 2.0/5.1/7.1
INPUT	
Bus Powered	Yes
Power Source	USB
POWER	
Power Source Type	USB
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No
Receiver Power Source	USB

CONNECTIONS	
Number of Ports	6
Ports	3
Ports Detail	Video is carried from the transmitter to the receiver via the RJ45 output ports on each unit. Extend the maximum distance of the installation by daisy-chaining B127U-110-PH units via the second RJ45 port on the receiver unit.
Daisy-Chain Port	RJ45 (Female)
Side A - Connector 1	HDMI (MALE)
Side A - Connector 2	USB A (MALE)
Side A - Connector 3	RJ45 (FEMALE)
Side A - Connector 4	HDMI (FEMALE)
Side A - Connector 5	MICRO-USB B (FEMALE)
Side B - Connector 1	HDMI (MALE)
Side B - Connector 2	USB A (MALE)
Side B - Connector 3	MICRO-USB B (FEMALE)
Side B - Connector 4	(2) RJ45 (FEMALE)
Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Up to 4 Units
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Transmitter: x1 Green (Power); Receiver: x1 Green (Power), x1 Orange (Data)
PHYSICAL	
Color	Gray
Material of Construction	Plastic
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	7.3mm
Wire Gauge (AWG)	28
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Included Mounting Accessories	N/A
Cable Length (cm)	30.5
Total Number of Ports	6
Number of Displays	1
Form Factor/Mounting Options	Pigtail



Powering Business Worldwide



Rackmountable	No
Receiver Unit Dimensions (hwd / cm.)	1.86 x 4.7 x 7.5
Receiver Unit Dimensions (hwd / in.)	0.73 x 1.85 x 2.95
Receiver Unit Weight (kg)	0.25
Receiver Unit Weight (lbs.)	0.55
Shipping Dimensions (hwd / in.)	2.17 x 10.24 x 6.46
Shipping Dimensions (hwd / cm)	5.51 x 26.01 x 16.41
Shipping Weight (lbs.)	1.23
Shipping Weight (kg)	0.56
Transmitter Unit Dimensions (hwd / cm.)	1.86 x 4.7 x 7.5
Transmitter Unit Dimensions (hwd / in.)	0.73 x 1.85 x 2.95
Transmitter Unit Weight (kg)	0.25
Transmitter Unit Weight (lbs.)	0.55
Unit Dimensions (hwd / in.)	0.732 x 1.850 x 2.953
Unit Packaging Type	Box
Unit Weight (lbs.)	1.235
Unit Weight (kg)	0.56
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 85% RH
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	230
Signal Range (ft.)	230
Signal Range (m)	70
Max 480P Range (ft)	230
Transmission Distance	230 ft. (70M)
Max 1440 x 900 Range (ft)	230
Max 1080i Range (ft)	230
Max 1920 x 1440 Range (ft)	230
Max 4K UHD Range (ft)	230
Max 480i Range (ft)	230
Max 640 x 480 Range (ft)	230



Powering Business Worldwide



Max 800 x 600 Range (ft)	230
Max 1600 x 1200 Range (ft)	230
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
Latency	Zero Latency
USB Extension Support	No
PORT EXPANSION	
Daisy-chainable or Cascadable	Y
FEATURES & SPECIFICATIONS	
All-in-One Kit	Yes
10/100 Ethernet Extension Support	No
Integrated/Removable Cable	No
MST Support	No
Mounting Accessory Included	No
Multi-Resolution Support	Yes
Built-In Equalizer	No
HDCP Specification	1.4; 2.2
Driver Required	No
Recommended Category Cable	24 AWG Solid Wire Cat6 Cabling
DIN Mountable	No
STANDARDS & COMPLIANCE	
Product Certifications	ICES (Canada); NOM (Mexico)
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS3; Trade Agreements Act (TAA); UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.