


10 x 1 Wireless HDMI Extender Transmitter - 1080p, 50 ft.

MODEL NUMBER: B126-1D10-TXH



Mini transmitter wirelessly extends an HDMI 1080p audio/video signal to an HDMI display up to 50 ft. away from the source device.

Features

Wireless HDMI Transmitter Ideal for Displaying Video in Boardrooms and Conference Rooms This wireless HDMI transmitter is recommended for video presentations in conference rooms, meeting rooms, trade shows and other locations where connecting long video cables could be a burden. It extends 1080p video and stereo audio signals from an HDMI source device (Blu-ray player, laptop, media server, etc.) to an HDMI display device (television, monitor, projector) up to 15 meters (50 feet) away. No bulky cabling infrastructure is needed.

Wireless Transmission Saves You Money on Cable and Installation Costs The wireless 1080p HDMI transmitter eliminates more than just hassles. You'll save on the costs of cabling infrastructure and the labor to install it. Cable clutter is reduced, and you will enjoy more flexibility in placement of the source and display with no cables to relocate when you want to reconfigure the room. The mini transmitter and receiver units communicate over a 5 GHz wireless frequency that allows fast data transmission and reduced interference from other wireless sources.

Transmits Crystal-Clear 1080p Video for High-Definition Presentations This wireless HDMI transmitter ensures high-definition performance with video resolutions up to 1920 x 1080 (1080p) at 60 Hz with 24-bit Deep Color (8 bits per channel) and stereo audio. It meets HDMI 1.3, HDCP 1.2 and EDID standards. AES 128 encryption protects your wireless transmissions. LEDs indicate when the mini transmitter unit is receiving power, transmitting data and connected to a wireless signal.

Display and Switch Between up to 10 Different HDMI Input Sources Have multiple presenters in a single meeting? Tired of plugging and unplugging your laptop from the presentation screen? The B126-1D10-TXH allows up to 10 different HDMI sources to be connected to one B126-1D10-TXH receiver unit (sold separately). Switch between sources with ease by simply pressing the switch button on the mini transmitter unit.

Plug-and-Play Operation for Quick Setup and Immediate Use The wireless HDMI audio/video transmitter works right out of the box with Tripp Lite's B126-1D10-WHD1 receiver units, with no software or drivers required. The mini transmitter connects directly to the source's HDMI output.

Specifications

Highlights

- Bus-powered TX requires B126-1D10-WHD1 wireless receiver (sold separately)
- Transmits HD picture quality at 1080p @ 60 Hz resolutions up to 50 ft. (15 m)
- Can be used with up to 9 additional transmitters in a single application
- Plug-and-play operation with no existing Wifi network needed for easy installation
- Low-profile design convenient for travel to lectures, trade shows and meetings for work

Applications

- Connect a laptop for a video or PowerPoint presentation in a conference room or meeting room
- Extend HDMI signals in an environment where drilling through walls for cabling is impossible or not practical
- Gain flexibility in where the source and display are placed, with the freedom to move and relocate them without struggling with cables
- Create a cleaner, streamlined installation for a trade show booth
- Improve the line of sight for digital signage in a restaurant, store, school, airport or entertainment venue

System Requirements

- Source device with HDMI output (Blu-ray player, media server, laptop)
- Tripp Lite B126-1D10-WHD1 receiver

Package Includes

- Mini transmitter
- USB-A to USB Micro-B cable, 3 ft.
- Right-angle HDMI adapter (M/F)
- Owner's manual

OVERVIEW	
UPC Code	037332257192
Product Type	Transmitter
Technology	HDMI; Wireless
VIDEO	
Max Supported Video Resolution	1920 x 1080 @60Hz
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	150
Maximum Signal Range (m)	46
AUDIO	
Audio Specification	PCM
INPUT	
Voltage Compatibility (VDC)	5 VDC
Bus Powered	Yes
POWER	
Power Source Type	USB
Power Over Cable (PoC) Support	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Signal (Red), Power (Blue)
PHYSICAL	
Color	Black
Material of Construction	Plastic
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
Unit Dimensions (hwd / in.)	1.530 x 3.490 x 0.600
Unit Packaging Type	Box
Unit Weight (lbs.)	0.04
Unit Weight (kg)	0.02

ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	50
Signal Range (m)	15
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Latency	200ms
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Wireless Transmission Distance	50ft
Integrated/Removable Cable	No
MST Support	No
Mounting Accessory Included	No
Multi-Resolution Support	No
Port Selection	Pushbutton
HDCP Specification	1.2
Driver Required	No
DIN Mountable	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.