

This product supports 4K 60 Hz 4:4:4 subsampling for HDR televisions. To ensure optimal performance, check the factory default settings on your TV.

- Frequency (Hz) should be set to 60 Hz
- HDR feature should be enabled
- HDMI input settings should be set to 2.0
- UHD Deep Color should be set to ON

DisplayPort to HDMI over Cat6 Extender Kit, Transmitter/Receiver, 4K 60 Hz, HDR, PoC, 125 ft., TAA

MODEL NUMBER: **B127-1A1-DH**



Transmitter/receiver kit extends a 4K DisplayPort signal via Cat6 cable to an HDMI projector, monitor or HDTV up to 125 ft. away.

Features

DP to HDMI Extender for Digital Signage or Displaying Video in Schools or Trade Show Booths This complete transmitter and receiver system is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings and digital signage applications where the source and display are farther apart than conventional A/V cables allow. The B127-1A1-DH extends 4K video and stereo audio signals from a DisplayPort (DP) source device to an HDMI display up to 125 feet (38.1 meters) away via user-supplied Cat6 cabling.

Transmits Crystal-Clear 4K HDMI Video with Multi-Channel Audio, HDR and 4:4:4 Color The B127-1A1-DH supports Ultra HD video resolutions up to 4K x 2K (3840 x 2160) at 60 Hz, as specified in HDMI 2.0, with full, rich uncompressed DTS-HD, Dolby AC-3 and 8-channel LPCM digital audio. Built-in equalization automatically fine-tunes the image quality at the remote display with no time-consuming manual fiddling needed. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. This unit also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Built-In PoC Technology Provides Receiver Power to Avoid Bulky External Power Bricks Built-in Power over Cable (PoC) technology powers the low-profile receiver over Cat6 cable. Green and orange LEDs on both the transmitter and receiver will light up to indicate the system is receiving power and a signal is being transmitted.

Plug-and-Play Operation for Quick Setup and Immediate Use The included transmitter and receiver units work right out of the box with no software required. Mounting hardware is included for installing the units on walls, poles or 19-inch racks. Connect the transmitter to the source with a DisplayPort cable

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Power over Cable (PoC) technology provides power to the receiver via Cat6 cable
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Transmitter's local HDMI port allows you to see the Ultra HD image being displayed
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect a media server, cable/satellite box, gaming system or other home theater component to a large-screen 4K television or projector
- Upgrade the video quality of your trade show presentation or digital signage installation in a commercial or educational setting to 4K x 2K

System Requirements

- Source device with DisplayPort output (media server, laptop)
- Display device with HDMI input (HDTV, projector, monitor)

Package Includes

- Transmitter unit
- Receiver unit
- External power supply (Input: 100–240V)
- (4) International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual



(Tripp Lite P580-Series) and the receiver to the display with an HDMI cable (such as Tripp Lite's P568- or P569-Series). Then, connect the two units using Cat6 patch cable (Tripp Lite N202-Series). Connect an optional display to the transmitter's local HDMI output to monitor the image connected to the receiver up to 125 feet away.

TAA-Compliant for GSA Schedule PurchasesThe B127-1A1-DH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332239129
Product Type	Extender Kit
Technology	DisplayPort; HDMI; Cat5/5e; Cat6; POC
VIDEO	
Video Input	DISPLAYPORT (FEMALE)
Video Output	HDMI (FEMALE)
Max Supported Video Resolution	3840x2160 (4K @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	200
Max 1920 x 1080 (1080p) Range (ft)	200
Max 1920 x 1200 Range (ft)	150
Max 2560 x 1600 Range (ft)	150
Max 3840 x 2160 (4K@30Hz) Range (ft)	150
Max 3840 x 2160 (4K@60Hz) Range (ft)	125
Transmitter Video Input	DisplayPort
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Max Supported Color Depth	24-bit True Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	125



Maximum Signal Range (m)	38
AUDIO	
Audio Input	Displayport
Audio Output	HDMI
Audio Specification	7.1 Channel Surround Sound, DTS-HD and Dolby TrueHD
INPUT	
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
Power Source	Transmitter end only (Included)
Power Over Cable (PoC) Support	Yes
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.6A
External Power Supply Output Specs (V / A)	24V/1A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Tx: x1 Green (Power), x2 Orange (Local, Output); Tx RJ45 port: Green (Connected), Orange (Activity) Rx: x1 Green (Power); Rx RJ45 port: Green (Connected), Orange (Activity)
PHYSICAL	
Material of Construction	Metal
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	1
Form Factor/Mounting Options	Box; Wall-mount
Rackmountable	Yes
Receiver Unit Dimensions (hwd / in.)	1.06 x 4.53 x 2.46
Receiver Unit Weight (lbs.)	0.45
Transmitter Unit Dimensions (hwd / in.)	1.06 x 4.53 x 2.46
Transmitter Unit Weight (lbs.)	0.45



Unit Packaging Type	Box
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	5 to 122°F (-15 to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	125
Signal Range (m)	38
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (FEMALE)
Side A - Connector 2	HDMI (FEMALE)
Side A - Connector 3	RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2a
HDCP Specification	1.4; 2.2
Driver Required	No
Recommended Category Cable	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
10/100 Ethernet Extension Support	No
Built-In Equalizer	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, REACH, RoHS
External Power Supply Certifications	CCC; CE; FCC; GS; PSE; TUV; UL; cUL
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	1-year limited warranty
--	-------------------------

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>