

DVI over Cat5/Cat6 Passive Extender, Wallplate Video Receiver, 1920x1080 at 60Hz, Up to 100-ft.

MODEL NUMBER: **B140-1P0-WP-1**



Transmit a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable

Description

The B140-1P0-WP-1 is a receiver wallplate that is used with the B140-002, B140-002-DD, and B140-004 extender/splitter transmitter units, transmitting a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable. To achieve maximum distance and resolution, use 24AWG Solid Wire Cat5e/6 cable (Tripp Lite's N202-Series). The B140-1P0-WP-1 is compatible with all operating systems, and is plug and play, with no external power, software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Installation is simple. Connect a B140-002, B140-002-DD, or B140-004 transmitter (not included) to a DVI source using a Tripp Lite P561-Series DVI cable (not included). Connect the B140-1P0-WP-1 to a display using a Tripp Lite P561-Series DVI cable (not included). Finally, the receiver unit is connected to an RJ45 port on the transmitter unit using a single Cat5e/6 cable. A 1920 x 1080 @ 60Hz signal can be extended up to 50 ft. from the source, or a 1024 x 768 @ 60Hz signal up to 100 ft..

Features

- Transmit a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable
- For use with B140-002, B140-002-DD, or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50 ft., or a 1024 x 768 @ 60Hz signal up to 100 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- HDCP compatible
- Compatible with all operating systems
- Plug and play; no external power, software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- For use with B140-002, B140-002-DD, or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50 ft., or a 1024 x 768 @ 60Hz signal up to 100 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Compatible with all operating systems
- Plug and play, no external power, software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B140-1P0-WP-1 DVI Over Cat5 Passive Extender/ Receiver Remote Wallplate
- Wallplate screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332163042
Product Type	Cat5/Cat6 Receiver
Technology	DVI
VIDEO	
Max 720P Range (ft)	100
Max 1080P Range (ft)	50
Maximum Signal Range (ft)	100
Maximum Signal Range (m)	30
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
PHYSICAL	
Color	White
Included Mounting Accessories	Yes
Shipping Dimensions (hwd / in.)	2.20 x 7.20 x 6.50
Shipping Dimensions (hwd / cm)	5.59 x 18.29 x 16.51
Shipping Weight (lbs.)	0.55
Shipping Weight (kg)	0.25
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	11.43 x 6.99 x 2.54
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	100
Max 480P Range (ft)	100
Max 1440 x 900 Range (ft)	100
Max 1080i Range (ft)	50
Max 480i Range (ft)	100
Max 640 x 480 Range (ft)	100
Max 800 x 600 Range (ft)	100
Max 1600 x 1200 Range (ft)	100



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.