

# HDMI over Cat6 Extender Kit, Transmitter and Pigtail Receiver, 4K 60Hz, 4:4:4, PoC, HDR, HDCP 2.2, 230 ft., TAA

MODEL NUMBER: B127A-1A1-BHPH



HDMI extender kit with transmitter and pigtail receiver extends a 4K signal via Cat6 cable to an HDMI display up to 230 ft. away.

## Features

### HDMI Extender Kit Ideal for Digital Signage in Schools, Restaurants and Lecture Halls

This complete transmitter and receiver system is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings, hotels and other digital signage applications where the source and display are farther apart than conventional A/V cables allow. The low-profile pigtail-type receiver is ideal for applications in which space around the display is restricted and a larger box-style receiver will not fit.

### Extends a 4K A/V Transmission up to 230 ft....or More

The B127A-1A1-BHPH extends 4K signals from an HDMI source device to an HDMI display up to 230 feet away via user-supplied Cat6 cabling. By adding a Tripp Lite B127A-010-H HDMI repeater or B127A-110-BH Transceiver (sold separately) to the application, you can extend the signal up to 400 or 460 feet, respectively.

### Transmits Crystal-Clear 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color

The B127A-1A1-BHPH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as specified by HDMI 2.0, with full, rich uncompressed DTS-HD, Dolby TrueHD and 7.1-channel digital audio. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This extender kit also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. Built-in equalization allows you to fine-tune the image quality at the remote display.

### Local HDMI Port on Transmitter Supports 4K @ 60 Hz Resolution

To monitor the video signal being extended to the receiver, connect a 4K display to the transmitter's local HDMI port with a user-supplied HDMI cable. This port does not support multi-resolution capabilities, so the connected monitor must also support 4K/60 Hz to function properly.

### Built-In PoC Technology Provides Receiver Power to Avoid Bulky External Power Bricks

Power over Cable (PoC) technology powers the receiver over Cat6 cable. LEDs on both the transmitter and receiver will light up to indicate the system is receiving power and a signal is being transmitted. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to place the receiver where needed without worrying about finding a nearby AC outlet.

### Plug-and-Play Operation for Quick Setup and Immediate Use

The included transmitter and receiver units work right out of the box with no software required. Mounting hardware is included for installing the transmitter on a wall, pole or 19-inch rack. Connect the transmitter to the source with a user-supplied HDMI cable (such as Tripp Lite's P568- or P569-Series). Then, connect the pigtail receiver to the display with its built-in HDMI cable. Finally, connect the two units with user-

## Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Power over Cable (PoC) technology provides power to the receiver via Cat6 cable
- Transmitter's local port shows you the 4K image being displayed at the other end
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Applications

- Connect a laptop for a video or PowerPoint presentation in an auditorium or lecture hall, where the source device changes frequently
- Extend video signals from one room to another using Cat6 cable, which can pass through conduit to meet building codes
- Gain flexibility in where the units are placed, with the freedom to move and relocate one away from an AC outlet
- Improve the line of sight for digital signage in a hotel, restaurant, theater, house of worship, trade show or other location

## System Requirements

- Source device with HDMI output



supplied Cat6 patch cable (such as Tripp Lite N202-Series).

**TAA-Compliant for GSA Schedule Purchases**

The B127A-1A1-BPH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

(Blu-ray player, cable box, laptop)

- Display device with HDMI input (HDTV, projector, monitor)

**Package Includes**

- Transmitter
- Receiver
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 24V 1A)
- (4) International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332258632
Product Type	Extender Kit
Technology	HDMI; HDR; Cat5/5e; Cat6; POC
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (FEMALE)
Max Supported Video Resolution	3840x2160 (4K @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230
Transmitter Video Input	HDMI



Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Range Extension using other Tripp Lite product	170ft or 230ft
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Other Tripp Lite product used to extend range	B127A-010-H or B127A-110-BH
Max Supported Color Depth	36-bit True Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	230
Maximum Signal Range (m)	70
<b>AUDIO</b>	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	Pass-through audio (LPCM 2.0/5.1/7.1)
<b>POWER</b>	
Power Source	Transmitter end only (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.6A
External Power Supply Output Specs (V / A)	24V/1A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
External Power Supply Certifications	CE; FCC; CCC; GS; TUV; UL; cUL
Power Over Cable (PoC) Support	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	TX: Green (Power); RJ45 Port: Green (Connection), Orange (Activity); RX: RJ45 Port: Green (Connection), Orange (Activity)



<b>PHYSICAL</b>	
Included Mounting Accessories	Wallmount
Material of Construction	Metal (Transmitter), Plastic (Receiver)
Number of Displays	1
Optional Mounting Accessory Notes	TX can only be wallmounted
Form Factor/Mounting Options	Box; Pigtail
Rackmountable	Yes
Receiver Unit Dimensions (hwd / cm.)	1.86 x 4.7 x 7.5
Transmitter Unit Dimensions (hwd / cm.)	2.7 x 11.5 x 6.24
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	5 to 122°F (-15 to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	230
Signal Range (m)	70
Transmission Distance	230 ft.
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
Latency	Zero-Latency
USB Extension Support	No
<b>CONNECTIONS</b>	
Side A - Connector 1	(2) HDMI (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	(2) 3.5MM (FEMALE)
Side B - Connector 1	HDMI (MALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Recommended Category Cable	Cat6
Built-In Equalizer	No
<b>SPECIAL FEATURES</b>	
DIN Mountable	No
Integrated/Removable Cable	No
MST Support	No
Included Mounting Accessory	No
Multi-Resolution Support	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, REACH, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>