


## Component Video (RCA) over IP Extender Transmitter over Cat5/Cat6, RS-232 and IR Control, 1080i, 328.08 ft. (100 m), TAA

MODEL NUMBER: **B160-001-CSI**



Converts component video and stereo audio to an IP-based signal that is transmitted point-to-point to a receiver 328 ft. away via Cat5e/6 cable or through a dedicated Ethernet network switch.

### Features

#### Distributes Component Video, Stereo Audio, Serial and IR Control Signals over Cat5/6 Cabling

- Converts audio and video to an IP-based signal that is transmitted point-to-point to a display 328 ft. away
- Add low-cost network switches between transmitter and receiver to continue extending distance up to 328 ft. per switch
- HDMI output for connecting a local display

#### Create a Multi-In, Multi-Out Installation Using B160-Series Transmitters and Receivers

- Connect up to 64 transmitters and 255 receivers through multiple dedicated managed network switches
- IGMP-enabled switches allow centralized control over which sources show on which displays
- Video source can be sent to any analog or digital display, so you can mix and match technologies and use existing monitors

### Enhanced Technical Features

- Supports video resolutions up to 1080i
- Uses H.264 video compression standard
- Transmits on 20–60 kHz IR frequency
- Sends IR control signals that control a source from a remote display
- Supports RS-232 serial baud rates up to 57600 Bps
- HDCP and 3D compatible

### Highlights

- Compatible with Tripp Lite B160-Series A/V over IP receivers
- Video source can be sent to any analog or digital display
- Supports video resolutions up to 1080i
- HDMI output on transmitter for connecting local display
- Plug and play—no software or drivers required

### Package Includes

- Transmitter unit
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 2A)
- Plug adapters for North America, U.K., Europe and Australia
- IR-Out cable
- 3.5 mm to DB9 adapter cable (M/F)
- Mounting hardware
- Owner's manual



#### Plug-and-Play Functionality

- Plug and play—no software or drivers required
- Hardware included for mounting on wall, rack or pole
- Compatible with all Tripp Lite B160-Series A/V over IP receivers

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332196705
Technology	A/V over IP; Component; IR; Serial (RS232)
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	BSMI; CB; CE; FCC; GS; PSE; RCM; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45 Output (Green / Power, Orange / Signal), Channel Signal (Red), Power (Green)
PHYSICAL	
Color	Black
Material of Construction	Steel
Rackmountable	Yes
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 10.10



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Weight (lbs.)	1.80
Unit Dimensions (hwd / in.)	1.2 x 5 x 3.9
Unit Weight (kg)	0.09
Unit Weight (lbs.)	0.2
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 167 F (-10 to 75 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 85%, Non-Condensing
BTUs	24.6 BTU/Hr
Power Consumption (Watts)	7.2
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	328
Signal Range (m)	100
Latency	2-3 seconds
<b>CONNECTIONS</b>	
Ports	9
Side A - Connector 1	(5) RCA (FEMALE)
Side B - Connector 1	(2) 3.5MM (FEMALE); HDMI (FEMALE); RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	1080i @60Hz
Audio Specification	2 Channel Surround Sound
Driver Required	No
Recommended Category Cable	N202-Series Cat6 Patch Cable
Max Supported Color Depth	24-bit True Color
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
3D Video Supported	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>