

VGA over IP Extender Transmitter over Cat5/Cat6, RS-232 Serial and IR Control, 1920 x 1440 (1080p), 328 ft. (100 m), TAA

MODEL NUMBER: B160-001-VSI



Converts VGA video + audio to an IP-based signal that is transmitted point-to-point to a receiver 328 ft. away via Cat5e/6 cable or through a dedicated Ethernet network switch.

Features

Distributes VGA A/V, Serial and IR Control Signals over Cat5/6 Cabling

- Converts audio/video to an IP-based signal that is transmitted point-to-point to a display 328 ft. away
- Add low-cost network switches between transmitter and receiver to continue extending distance up to 328 ft. per switch
- HDMI output for connecting a local display

Create a Multi-In, Multi-Out Installation Using B160-Series Transmitters and Receivers

- Connect up to 64 transmitters and 255 receivers through multiple dedicated managed network switches
- IGMP-enabled switches allow centralized control over which sources show on which displays
- Video source can be sent to any analog or digital display, so you can mix and match technologies and use existing monitors

Enhanced Technical Features

- Supports video resolutions up to 1920 x 1440, including 1080p (limited to receiver's max resolution)
- Uses H.264 video compression standard
- Transmits on 20–60 kHz IR frequency
- Extends IR control signals that control a source from a remote display
- Supports RS-232 serial baud rates up to 57600 Bps
- HDCP and 3D compatible

Plug-and-Play Functionality

- No software or drivers required
- Hardware included for mounting on wall, rack or pole

Highlights

- Compatible with Tripp Lite B160-Series A/V over IP receivers
- Video source can be sent to any analog or digital display
- Supports video resolutions up to 1920 x 1440, including 1080p*
- HDMI output on transmitter for connecting local display
- Plug and play—no software or drivers required

Package Includes

- Transmitter unit
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 2A)
- Plug adapters for U.S., U.K., Europe and Australia
- IR-Out cable
- 3.5 mm to DB9 adapter cable (M/F)
- Mounting hardware
- Owner's manual

- Compatible with all Tripp Lite B160-Series A/V over IP receivers

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332196682
Product Type	Transceiver
Technology	IR; VGA/SVGA; A/V over IP; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920 x 1440 @ 60Hz
Max 720P Range (ft)	328
Max 1080P Range (ft)	328
Max 1280 x 720 (720p) Range (ft)	328
Max 1920 x 1080 (1080p) Range (ft)	328
Max 1920 x 1200 Range (ft)	328
Transmitter Video Input	VGA
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Range Extension using other Tripp Lite product	328ft
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	network switch
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	No
Maximum Signal Range (ft)	328
Maximum Signal Range (m)	100
Maximum Signal Range Details	328 ft via Cat6/275 ft via Cat5e
AUDIO	
Audio Input	3.5mm
Audio Specification	Stereo Audio

INPUT	
Bus Powered	No
POWER	
Power Source Type	AC Adapter
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45 Output (Green / Power, Orange / Signal), Channel Signal (Red), Power (Green)
PHYSICAL	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-02
Form Factor/Mounting Options	Box; Wall-mount
Shipping Dimensions (hwd / in.)	2.00 x 6.40 x 10.20
Shipping Dimensions (hwd / cm)	5.08 x 16.26 x 25.91
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2
Unit Weight (kg)	0.09
Housing	Metal

ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Relative Humidity	0% to 85%, Non-Condensing
BTUs	18.1 BTU/Hr
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	328
Max 480P Range (ft)	328
Max 1440 x 900 Range (ft)	328
Max 1080i Range (ft)	328
Max 1920 x 1440 Range (ft)	328
Max 480i Range (ft)	328
Max 640 x 480 Range (ft)	328
Max 800 x 600 Range (ft)	328
Max 1600 x 1200 Range (ft)	328
EDID Compatible	No
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
Consumer Electronics Control (CEC) Supported	No
USB Extension Support	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	3.5MM (FEMALE); HD15 (FEMALE)
Side B - Connector 1	HDMI (FEMALE); RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
Built-In Equalizer	No
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	BSMI; CB; CCC; CE; FCC; GS; PSE; RCM; TUV; UL; cUL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	1-year limited warranty
--	-------------------------