

DisplayPort over IP Extender Receiver over Cat5/Cat6, RS-232 Serial and IR Control, 1080p 60 Hz, 328 ft. (100 m), TAA

MODEL NUMBER: **B160-100-DPSI**



Receives IP-based audio + video signal transmitted point-to-point from a source 328 ft. away via Cat5e/6 cable or through a dedicated Ethernet network switch.

Features

DisplayPort A/V, Serial and IR Control Signals over Cat5/6 Cabling

- Receives IP-based audio/video transmitted point-to-point from a source 328 ft. away
- Add low-cost network switches between transmitter and receiver to continue extending distance up to 328 ft. per switch

Create a Multi-In, Multi-Out Installation Using B160-Series Transmitters and Receivers

- Connect up to 64 transmitters and 255 receivers through multiple dedicated managed network switches
- IGMP-enabled switches allow centralized control over which sources show on which displays
- Displays video from any analog or digital source, so you can mix and match technologies and use existing sources and monitors

Enhanced Technical Features

- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Uses H.264 video compression standard
- Transmits on 20–60 kHz IR frequency
- Extends IR control signals that control a source from a remote display
- Supports RS-232 serial baud rates up to 57600 Bps
- HDCP and 3D compatible when used with a DisplayPort or HDMI transmitter

Plug-and-Play Functionality

- No software or drivers required
- Hardware included for mounting on wall, rack or pole
- Compatible with all B160-Series A/V over IP transmitters

Highlights

- Compatible with B160-Series A/V over IP transmitters
- Display video from any source, analog or digital
- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Scales up to multi-in, multi-out installation with network switch
- Plug and play—no software or drivers required

Package Includes

- Receiver unit
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 2A)
- Plug adapters for U.S., U.K., Europe and Australia
- IR-In cable
- 3.5 mm to DB9 adapter cable (M/M)
- Mounting hardware
- Owner's manual

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332196729
Product Type	Receiver
Technology	DisplayPort; IR; A/V over IP; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	328
Max 1920 x 1080 (1080p) Range (ft)	328
Receiver/Transceiver Video Output	DisplayPort
Receiver - Number of Video Outputs	1
Range Extension using other Tripp Lite product	328 ft.
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	network switch
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	328
Maximum Signal Range (m)	100
Maximum Signal Range Details	328 ft via Cat6/275 ft via Cat5e
AUDIO	
Audio Output	Displayport
Audio Specification	Stereo Audio
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
AC Power Adapter Output Specs (V / A)	5V / 2A

AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.4
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	6
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45 Output (Green / Power, Orange / Signal), Channel Signal (Red), Power (Green)
PHYSICAL	
Color	Black
Material of Construction	Steel
Included Mounting Accessories	Wallmount
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-02
Form Factor/Mounting Options	Box; Wall-mount
Rackmountable	Yes
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 10.20
Shipping Weight (lbs.)	1.70
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2
Unit Weight (kg)	0.09
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0% to 85%, Non-Condensing
BTUs	20.5 BTU/Hr

COMMUNICATIONS	
Signal Range (ft.)	328
Signal Range (m)	100
EDID Compatible	Yes
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
Latency	2-3 seconds
USB Extension Support	No
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	DISPLAYPORT (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
Daisy-chainable / Cascadable	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
Built-In Equalizer	No
Displayport Specification	1.2
HDCP Specification	1.4
Driver Required	No
Recommended Category Cable	N202-Series Cat6 Patch Cable
STANDARDS & COMPLIANCE	
External Power Supply Certifications	BSMI; CB; CCC; CE; FCC; GS; PSE; RCM; TUV; UL; cUL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.