

# HDMI over Cat6 Pigtail Receiver with Repeater, 4K 60 Hz, 4:4:4, Transceiver, HDCP 2.2, 230 ft. (70.1 m), TAA

## MODEL NUMBER: B127U-110-PH

Works with a B127U-Series transmitter or splitter to extend 4K video via Cat6 cable to an HDMI monitor up to 230 ft. away.

### Features

#### HDMI Extender Receiver Recommended for Digital Signage in Schools and Businesses

This 4K receiver is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings, hotels and other digital signage applications where the source and display are farther apart than conventional A/V cables allow. When connected to a B127U-Series transmitter, the B127U-110-PH helps extend 4K signals from an HDMI or DisplayPort source to an HDMI monitor up to 230 feet (70.1 meters) away with zero latency via user-supplied Cat6 cabling. The one-foot pigtail design makes the receiver easy to install, especially in a tight space.

#### Transmits 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color

The B127U-110-PH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with uncompressed DTS-HD, Dolby TrueHD and 7.1-channel digital audio. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K content with no complications. This receiver also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

#### Create Daisy-Chain Installations with HDMI Outputs, DisplayPort Outputs or Both

The B127U-110-PH can be connected to additional B127U-110-PH HDMI receivers or B127U-110-PD DisplayPort receivers (sold separately) in a four-link daisy-chain installation. Each additional receiver adds up to 230 feet (70.1 meters) to the maximum video transmission distance and up to a total of 920 feet (280 meters) for the entire installation. **Note:** See the installation diagram in the owner's manual for more information.

#### Multi-Resolution Support Allows Mixing and Matching of Displays of Different Resolutions

The B127U-110-PH is backward compatible with 4K/30 Hz and 1080p resolutions via automatic switching, allowing each connected monitor to display video at its maximum resolution without affecting the other outputs.

#### Plug-and-Play Operation for Quick Setup and Immediate Use

The receiver works right out of the box with no software required. A one-foot USB-A pigtail connector is the primary power source. Plug the USB connector on the receiver into a USB-A power adapter (such as U280-W01-QC3-1, sold separately) or USB-A port on the connected display. User-supplied 24 AWG Cat6 cabling connects the transmitter and receivers. **Note:** The receiver can also be powered through its Micro-USB port.

#### TAA-Compliant for GSA Schedule Purchases

The B127U-110-PH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) with High Dynamic Range (HDR)
- Lightweight pigtail receiver is USB-powered through display or power adapter
- Can be daisy-chained up to 4 times (920 ft. total) via additional receivers
- Plug-and-play operation with no software required for easy, immediate installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- Source device with HDMI or DisplayPort output (computer, laptop, media server)
- Display device with HDMI input (HDTV, projector, monitor)
- B127U-Series transmitter or splitter

### Package Includes

- B127U-110-PH HDMI over Cat6 Receiver
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332281463
Product Type	HDMI Over Cat6 Pigtail Receiver with Repeater
Technology	Cat6; HDMI; USB

Host Connector	HDMI (MALE)
<b>VIDEO</b>	
Video Input	RJ45 (FEMALE)
Video Output	HDMI (MALE)
Number of Monitors Supported	1
Video Ports	HDMI (MALE)
Video Ports Details	HDMI 2.0; HDCP 2.2
Resolutions Supported	Up to 4K (3840 x 2160) @ 60 Hz
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 1920x1200; 2560x1600; 3840x2160 (4K)
Max Supported Video Resolution	4K x 60 Hz
Max. Distance (Between any 2 Units)	230 ft.
Max. Distance (Between any 2 Units) (Meters)	70
Max 1080P Range (ft)	230
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	230
Signal Range (m)	70
Range Extension using other Tripp Lite product	N/A
Recommended Cabling	<a href="#">N202-Series Cat6 Gigabit Snagless UTP Ethernet Cabling</a>
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4
Maximum Signal Range (ft)	230
Maximum Signal Range (m)	70
EDID Support	Yes
Signal Transmission	Unidirectional

DisplayPort Alt Mode	No
DSC Support	No
<b>AUDIO</b>	
Audio Output	HDMI
Audio Specification	Supports passthrough audio formats including LPCM 2.0/5.1/7.1
<b>INPUT</b>	
Bus Powered	Yes
Power Source	USB
<b>POWER</b>	
Power Source Type	USB
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No
Receiver Power Source	USB
<b>CONNECTIONS</b>	
Number of Ports	3
Ports	2
Ports Detail	Video is carried from the transmitter to the receiver via the RJ45 portExtend the maximum distance of the installation by daisy chaining B127U-110-PH units via the second RJ45 port on the receiver unit.
Daisy-Chain Port	RJ45 (Female)
Side A - Connector 1	HDMI (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
Side B - Connector 2	(2) RJ45 (FEMALE)
Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Up to 4 Units
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	x1 Green (Power), x1 Orange (Data)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Plastic
Cable Jacket Color	Black
Cable Jacket Material	PVC



Powering Business Worldwide



Cable Outer Diameter (OD)	7.3mm
Wire Gauge (AWG)	28
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Included Mounting Accessories	N/A
Cable Length (cm)	30.5
Total Number of Ports	3
Number of Displays	1
Form Factor/Mounting Options	Pigtail
Rackmountable	No
Receiver Unit Dimensions (hwd / cm.)	1.86 x 4.7 x 7.5
Receiver Unit Dimensions (hwd / in.)	0.73 x 1.85 x 2.95
Receiver Unit Weight (kg)	0.25
Receiver Unit Weight (lbs.)	0.55
Shipping Dimensions (hwd / in.)	2.17 x 10.24 x 6.46
Shipping Dimensions (hwd / cm)	5.51 x 26.01 x 16.41
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
Unit Dimensions (hwd / in.)	0.732 x 1.850 x 2.953
Unit Dimensions (hwd / cm)	1.85 x 4.7 x 7.5
Unit Dimensions (hwd / mm)	18.5 x 47 x 75
Unit Packaging Type	Box
Unit Weight (lbs.)	0.176
Unit Weight (kg)	0.08
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 85% RH
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	230
Signal Range (ft.)	230
Signal Range (m)	70
Max 480P Range (ft)	230



Powering Business Worldwide



Transmission Distance	230 ft. (70m)
Max 1440 x 900 Range (ft)	230
Max 1080i Range (ft)	230
Max 1920 x 1440 Range (ft)	230
Max 4K UHD Range (ft)	230
Max 480i Range (ft)	230
Max 640 x 480 Range (ft)	230
Max 800 x 600 Range (ft)	230
Max 1600 x 1200 Range (ft)	230
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
Latency	Zero Latency
USB Extension Support	No
<b>PORT EXPANSION</b>	
Daisy-chainable or Cascadable	Up to 4 layers
<b>FEATURES &amp; SPECIFICATIONS</b>	
All-in-One Kit	No
10/100 Ethernet Extension Support	No
Integrated/Removable Cable	No
MST Support	No
Mounting Accessory Included	No
Multi-Resolution Support	Yes
Built-In Equalizer	No
HDCP Specification	2.2
Driver Required	No
Recommended Category Cable	24 AWG Cat6
DIN Mountable	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	ICES (Canada); NOM (Mexico)
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS3; Trade Agreements Act (TAA); UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide



Product Warranty Period (Worldwide)	1-year limited warranty
----------------------------------------	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.