

VGA with Audio over Cat5/Cat6 Extender, Receiver, USB-Powered, 1440x900 60 Hz, Up to 300 ft. (90 m), TAA

MODEL NUMBER: **B132-100A-SR**



Extends a VGA video and audio signal up to 300-ft. (91M) from the source

Features

- Works with a B13 or B13 Transmitter Unit to extend a VGA video and audio signal up to 300-ft. from the source
- Extends a 1440 x 900 video and audio signal up to 150-ft, or a 1024 x 768 video and audio signal up to 300-ft.
- 24AWG, Solid Wire Cat5e/6 cable (such as Tripp Lite's N20 Cat6 cables) is required to achieve maximum distance and resolution
- Power is supplied via the included USB Micro-B cable; no external power supply required
- Features built-in equalization and gain controls to adjust the video image
- All operating systems supported
- Plug and play; no software or drivers required
- HDCP and EDID compliant
- Ideal for digital signage installations for retail, schools, churches, etc.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Works with a B132-002A-2 or B132-004A-2 Transmitter Unit to extend a VGA video and audio signal up to 300-ft. from the source
- Extends a 1440 x 900 video and audio signal up to 150-ft, or a 1024 x 768 video and audio signal up to 300-ft.
- Power is supplied via the included USB Micro-B cable; no external power supplies required
- Plug and play, no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Package Includes

- B132-100A-SR
- USB Micro-B cable
- Screwdriver for EQ/Gain adjustment
- Owner's Manual

Specifications

| OVERVIEW | |
|--------------|---------------------------------------|
| UPC Code | 037332185563 |
| Product Type | Receiver |
| Technology | VGA/SVGA; Stereo Audio; Cat5/5e; Cat6 |
| VIDEO | |



Powering Business Worldwide



| | |
|---------------------------------|-----------------------|
| Max 720P Range (ft) | 150 |
| HDR Support | No |
| 3D Video Supported | No |
| Maximum Signal Range (ft) | 300 |
| Maximum Signal Range (m) | 91 |
| INPUT | |
| Bus Powered | No |
| POWER | |
| Power Over Cable (PoC) Support | No |
| CONNECTIONS | |
| Number of Ports | 1 |
| Side A - Connector 1 | RJ45 (FEMALE) |
| Side B - Connector 1 | HD15 (FEMALE) |
| Side B - Connector 2 | 3.5MM (FEMALE) |
| PHYSICAL | |
| Color | White |
| Number of Displays | 1 |
| Shipping Dimensions (hwd / in.) | 6.14 x 4.80 x 1.30 |
| Shipping Dimensions (hwd / cm) | 15.60 x 12.19 x 3.30 |
| Shipping Weight (lbs.) | 0.37 |
| Shipping Weight (kg) | 0.17 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| COMMUNICATIONS | |
| Max 1024 x 768 Range (ft) | 300 |
| Max 480P Range (ft) | 300 |
| Max 1440 x 900 Range (ft) | 150 |
| Max 480i Range (ft) | 300 |
| Max 640 x 480 Range (ft) | 300 |
| Max 800 x 600 Range (ft) | 300 |
| EDID Compatible | No |
| IR Remote Extension Support | No |
| RS-232 Serial Extension Support | No |



Powering Business Worldwide



| | |
|--|-------------------------|
| Consumer Electronics Control (CEC) Supported | No |
| USB Extension Support | No |
| FEATURES & SPECIFICATIONS | |
| 10/100 Ethernet Extension Support | No |
| Built-In Equalizer | No |
| Driver Required | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.