

2-Port DVI over Cat5/6 Splitter/Extender, Box-Style Transmitter for Video, DVI-D Single Link, 200 ft., TAA

MODEL NUMBER: **B140-002**



Transmitter/splitter extends a DVI video signal via Cat6 cable to 2 projectors, monitors or HDTVs up to 200 ft. away.

Features

Splitter Ideal for Digital Signage or Displaying DVI Video in Schools or Trade Show BoothsThis two-port transmitter/splitter allows you to split a DVI-D single-link signal and extend it to two monitors beyond the normal 16-foot DVI limitation using inexpensive Cat5/6 cabling. The B140-002 is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings and other digital signage applications where the source and display are farther apart than conventional A/V cables allow.

Extend a DVI Video Signal up to 200 ft. from the Source DeviceThe B140-002 extends video from a DVI source device to two DVI displays up to 200 feet away via user-supplied Cat5/Cat6 cabling (such as Tripp Lite's N202-Series 24 AWG cables, sold separately). Specifically, it can extend a 1024 x 768 (@ 60 Hz) resolution up to 200 feet and a 1920 x 1080 (@ 60 Hz) resolution up to 150 feet when used with an active remote unit (Tripp Lite B140-1A0 or B140-1A0-WP, sold separately). When used with a passive remote unit (Tripp Lite B140-1P0, sold separately), it can extend a 1024 x 768 (@ 60 Hz) resolution up to 100 feet and a 1920 x 1080 (@ 60 Hz) resolution up to 50 feet.

Include a Tripp Lite Repeater to Expand the Range and Add More DisplaysConnect a B140-110 repeater unit (sold separately) to add up to four remote units (three repeaters and one active receiver) to each channel for a total of four displays per channel. An active receiver should be the last unit in a channel. A 1920 x 1080 (@ 60 Hz) signal can be extended up to 125 feet from each repeater to the next unit in the channel, while a 1024 x 768 (@ 60 Hz) can be extended up to 175 feet.

Plug-and-Play Operation for Quick Setup and Immediate UseThe included transmitter works right out of the box with no software required. Mounting hardware is included for installing the unit on a wall, pole or 19-inch rack. Its durable metal housing is designed to last a long time and fit seamlessly into any home or office application. The B140-002 is compatible with HDCP standards, all DVI video sources and all operating systems.

TAA-Compliant for GSA Schedule PurchasesThe B140-002 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Transmits up to 200 ft. for digital signage in bars, offices, classrooms, trade shows, etc.
- Supports HD resolutions up to 1920 x 1080 (@ 60 Hz) for crystal-clear 1080p video
- Works in tandem with Tripp Lite B140-1A0 or B140-1P0 remote receiver
- Plug-and-play operation with no software required for easy, immediate installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Displaying a digital menu from a PC on monitors in a restaurant or bar
- Connecting 2 HDTVs to the same cable box, media server or DVD player for sports or movies
- Giving a presentation on large projectors or monitors in a lecture hall
- Creating digital signage for an office lobby, healthcare waiting room, church, school, trade show, conference room, retail display or airport

System Requirements

- Works in tandem with Tripp Lite B140-1A0 or B140-1P0 extender remote receiver or B140-1A0-WP-1 extender wall



plate

Package Includes

- B140-002 DVI over Cat5/Cat6 Splitter/Extender
- External power supply with 5 ft. cord and NEMA 1-15P plug (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 2A)
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332156709
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
PHYSICAL	
Color	Black
Included Mounting Accessories	Yes
Shipping Dimensions (hwd / cm)	5.59 x 17.53 x 16.26
Shipping Dimensions (hwd / in.)	2.20 x 6.90 x 6.40
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	1.00
Unit Dimensions (hwd / cm)	2.54 x 6.35 x 9.14
Unit Dimensions (hwd / in.)	1 x 2.5 x 3.6
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	200
Max 480P Range (ft)	200
Max 1440 x 900 Range (ft)	150
Max 1080i Range (ft)	150
Max 1080P Range (ft)	150
Max 480i Range (ft)	200
Max 640 x 480 Range (ft)	200



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Max 800 x 600 Range (ft)	200
Max 1600 x 1200 Range (ft)	150
Max 720P Range (ft)	150
CONNECTIONS	
Ports	2
Side A - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 1	(2) RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	DVI
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>