

## BC Pro 120V 600VA 345W Standby UPS, Tower, USB port, 6 Outlets

MODEL NUMBER: BCPRO600



### Highlights

- 600VA tower 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL/ethernet protection, 97% efficient
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- BCPRO600 Standby UPS System
- USB cable
- Phone cable
- Instruction manual

### Description

Tripp Lite's BCPRO600 standby UPS offers complete power protection for desktop PCs, network workstations and a wide variety of consumer and professional electronics. Uninterruptible Power Supply / UPS circuits switch to battery backup mode within milliseconds to keep connected equipment running without interruption or data loss during power failures. Surge-only outlets offer convenient protection for printers and other desktop accessories not requiring battery support. AC and dataline surge suppression prevents connected equipment damage. USB communications port supports built-in power management and auto-shutdown features of Windows and Mac OS X or full featured monitoring and data-saving auto-shutdown options using Tripp Lite's free PowerAlert monitoring software.

### Features

- BCPRO600 tower 120V standby UPS offers AC power protection from blackouts, brownouts, overvoltages and transient surges
- 600VA / 345 watt UPS output capacity
- Uninterruptible Power Supply / UPS operation maintains battery-derived AC output during blackouts, brownouts and overvoltages to prevent data loss and system downtime for connected equipment
- Built-in USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [tripplite.eaton.com/products/power-alert](http://tripplite.eaton.com/products/power-alert)
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- 5.7 minutes runtime at 100% load (345 watts), 14.5 minutes runtime at 50% load (175 watts)
- 42 minutes runtime for a desktop computer system consuming 80 watts continuous
- 6 built-in total NEMA 5-15R outlets
- 3 UPS battery backup outlets, plus 3 additional surge-only outlets
- Right angle NEMA 5-15P input connection with 6ft / 1.8m line cord
- Network grade AC surge protection is available from all outlets
- Built-in data line surge suppression protects a single dialup, DSL or ethernet line
- 97% line mode efficiency rating uses less energy and BTU emissions
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft



Powering Business Worldwide



reboot of application/OS or hard power off/on reboot of connected equipment, ideal for unattended kiosk applications

- Front panel LEDs indicate line / battery mode and battery replace status; Audible alarm with alarm cancel / self-test button
- Hot swappable user battery replacement
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Small tower housing supports desk or floor placement

## Specifications

OVERVIEW	
UPC Code	037332033277
UPS Type	Standby
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
OUTPUT	
Output Capacity (VA)	600
Output Capacity (Watts)	345
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	No

BATTERY	
Runtime Full Load (min.)	5.7 min. (345w)
Runtime Half Load (min.)	14.5 min. (175w)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	3 LEDs indicate line power, battery power and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	510
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (&nbsp;<a class="productLink" href="//tripplite.eaton.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems~UPSWM">UPSWM</a>&nbsp; - tower mounting kit)
Primary UPS Depth (mm)	191
Primary UPS Height (mm)	274
Primary UPS Width (mm)	132
Shipping Dimensions (hwd / in.)	13.90 x 8.00 x 10.20
Shipping Dimensions (hwd / cm)	35.31 x 20.32 x 25.91
Shipping Weight (lbs.)	15.90
Shipping Weight (kg)	7.21
UPS Housing Material	PVC



Powering Business Worldwide

**TRIPP-LITE**  
by **EATON**

UPS Power Module Dimensions (hwd, cm)	27.43 x 13.21 x 19.05
UPS Power Module Dimensions (hwd, in.)	10.8 x 5.2 x 7.5
UPS Power Module Weight (kg)	6.89
UPS Power Module Weight (lbs.)	15.2
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	14
AC Mode Efficiency Rating (100% Load)	97%
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools (NUT) Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="https://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp+Lite">https://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite</a>
Communications Interface	USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99 (adjustable to 83 via back panel potentiometer)
High Voltage Transfer to Battery Power (Setpoint)	139
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>APPLICATIONS</b>	
UPS Applications	Computer/Peripherals
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



Powering Business Worldwide



Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000&nbsp;<a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;
---	---

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.