

External UPS Battery Pack, 80 10Ah for S3M40KX or 80 9Ah for S3M30KX , No Batteries Included - S3M30KX or S3M40KX 3-Phase UPS System

MODEL NUMBER: BP480V10-NIB



Includes internal battery wiring and accessories for 80 user-supplied 9Ah or 10Ah batteries to extend runtime of a compatible UPS.

Description

The BP480V10-NIB External Battery Cabinet does not include batteries. The cabinet is designed for 9Ah or 80 10Ah batteries. This cabinet offers extended battery runtime when used in conjunction with compatible UPS systems. Includes internal disconnect for battery isolation.

Compatible UPS Systems: S3M30KX when using 80 9Ah, and S3M40KX when using 80 10Ah batteries. The external battery cabinet battery Ah capacity must match the internal UPS battery Ah capacity.

Features

+/-240VDC Backup Battery Pack — You Provide the Batteries This special configuration includes the steel enclosure and all required internal wiring and accessories for a quantity of 80 user-supplied 9Ah or 10Ah internal batteries (batteries not included). With 9Ah batteries installed, the UPS battery pack cabinet is compatible with 3-phase S3M30KX UPS system. With 10Ah batteries, it's compatible with the S3M40KX. For the same battery pack with internal batteries included, see BP480V09 (9Ah) or BP480V10 (10Ah).

Gives Your Compatible UPS System Extended Runtime After you buy and install your own batteries, the BP480V10-NIB not only provides extended runtime, but it can also be daisy-chained to as many as seven additional external battery packs for even longer extended-run operation. Hardwire installation is safe and simple. Circuit breakers provide overcurrent protection. Internal disconnect for battery isolation is included.

One-Year Warranty The BP480V10-NIB is backed by a one-year warranty, ensuring reliability and performance.

Highlights

- Extends runtime of compatible UPS systems using special +/- 240VDC configuration
- Requires 80 user-supplied 9Ah or 10Ah sealed lead acid batteries for operation
- Black steel cabinet matches UPS systems to give your server room a consistent look
- Requires hardwire installation; circuit breakers provide overcurrent protection
- Multiple UPS battery pack cabinets may be connected in parallel to increase runtime

Applications

- Extend the runtime of your compatible Tripp Lite UPS system to maintain operation during all power conditions
- Daisy-chain as many as 7 additional battery packs to provide even longer extended-run operation for backing up essential equipment in your server room or data center

System Requirements

- S3M30KX, S3M40KX or other UPS system specifying compatibility with this external battery pack
- 80 user-supplied 9Ah or 10Ah sealed lead acid batteries

Package Includes

- BP480V10-NIB External Battery Pack for S3M30KX or S3M40KX UPS System – Batteries Not Included
- Cable for jack, 32 in. (81.3 cm), 1/0 AWG
- Attachment hardware for battery cable
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332231062



Powering Business Worldwide



INPUT	
Input Phase	3-Phase
BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	+/- 240VDC
UPS Connection	Hardwire (contractor supplies wiring - see Owner's Manual for gauge recommendations)
Typical Battery Lifespan	10 year design lifespan
PHYSICAL	
Material of Construction	Steel
External Battery Pack Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Shipping Dimensions (hwd / in.)	40.10 x 14.96 x 36.20
Shipping Dimensions (hwd / cm)	101.85 x 38.00 x 91.95
Shipping Weight (lbs.)	179.90
Shipping Weight (kg)	81.60
Unit Dimensions (hwd / in.)	32.900 x 9.850 x 30.700
Unit Dimensions (hwd / cm)	83,57 x 25,02 x 77,98
Unit Weight (lbs.)	120.4
Unit Weight (kg)	54.61
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.