

10-Device Desktop AC Charging Station with Surge Protector for Tablets, Laptops and E-Readers

MODEL NUMBER: **CSD1006AC**



Highlights

- 1.25 in. wide slots hold devices up to 10.5 in.
- 6-ft. (1.83 m) AC input cord with right-angle NEMA 5-15P plug
- 2,880 joules of surge suppression
- Locking lid helps prevent device theft, damage or tampering
- Separate cable with combination lock for added security

Package Includes

- CSD1006AC 10-Device Desktop AC Charging Station
- Enclosure unit with locking lid
- Combination cable lock
- (2) Keys
- Owner's manual

Locking enclosure provides AC charging, secure storage and cord management for up to 10 tablets, laptops and e-readers. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSD1006AC 10-Device Desktop AC Charging Station provides AC charging, secure storage and cord management for up to 10 tablets, laptops and e-readers up to 10.5 inches. Each slot is 1 1/4" wide. It's recommended for schools, offices, warehouses, retail outlets, worksites, healthcare facilities and anywhere else multiple mobile devices are used.

Devices fit into slots 1.25 inches wide. Their AC adapters plug into the 10 widely spaced NEMA 5-15R outlets as needed for proficient charging. The devices are protected by 2,880 joules of surge suppression and EMI/RFI noise filtering that protect against potentially harmful bursts in voltage. Diagnostic LEDs let you know that the charging station is grounded and the connected devices protected. An auto-shutoff feature cuts off power to the outlets in case of a power spike.

The CSD1006AC locks with the included keys to help prevent theft, damage or tampering. A cable with combination lock is also included to secure the charging station to a desk, table, cart or other flat surface. The 6-ft. (1.83 m) AC input cord with NEMA 5-15P plug helps you place the charging station in a convenient location. Storage shelf dividers are easily removed to accommodate thicker devices. Cabling is secured beneath the shelf tray to alleviate clutter.

The CSD1006AC comes with a 1-year lifetime warranty. The included Surge Suppressor comes with a lifetime limited warranty and \$100,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only).

Features

Convenient AC Charging

- 10 NEMA 5-15R outlets for charging tablets, laptops and e-readers up to 10.5 in.
- Devices fit into slots 1.25 in. wide
- 6-ft. (1.83 m) AC input cord with right-angle NEMA 5-15P plug reaches convenient outlets
- Recommended wherever multiple mobile devices are used—schools, offices, warehouses, etc.

Comprehensive Protection

- 2,880 joules of surge suppression

- EMI/RFI noise filtering
- Diagnostic LEDs indicate grounded connection and protected outlets
- Automatically shuts down outlets in case of power surge

Complete Security

- Locks with included keys to help prevent device theft, damage or tampering
- Included combination cable lock secures the unit to a desk or cart

Clutter-Reducing Organization

- AC outlets, power adapters and cords store out of sight
- Staggered outlets fit power adapters without blocking adjacent outlets
- Storage shelf dividers can be removed to accommodate thicker devices

Included Surge Suppressor Protected by Lifetime Limited Warranty and Insurance

- \$100,000 of Ultimate Lifetime Insurance for any connected equipment damaged by a power surge (U.S., Canada and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332193469
Product Type	Multi-Device Charger
Charging Form Factor	Desktop Cabinet
Functions	Charge; Secure
Device Compatibility	Laptop; Tablet
Device Slots	10
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Plug Features	120V/15A
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	

Frequency Compatibility	60 Hz
Circuit Breaker (amps)	15
CHARGING	
Number of Charging Ports	10
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(10) 15A
Overcharge Protection	Yes
Charging Amps per Port	15A
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2880
AC Suppression Response Time	<1ns
Automatic Shut-Off	Yes
PHYSICAL	
Color	Black; Gray
Material of Construction	Plastic
Charging Station Form Factor	Desktop Cabinet
Shipping Dimensions (hwd / in.)	10.50 x 16.40 x 17.70
Shipping Dimensions (hwd / cm)	26.67 x 41.66 x 44.96
Shipping Weight (lbs.)	13.65
Shipping Weight (kg)	6.19
Unit Dimensions (hwd / in.)	8.940 x 16.540 x 13.540
Unit Dimensions (hwd / cm)	42.01 x 34.39 x 22.71
Number of Shelves	1
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	No
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
IP68 Rated	No

IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key; Combination Cable Lock
STANDARDS & COMPLIANCE	
Product Certifications	UL 1449
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Warranty Details	Included Surge Suppressor comes with a lifetime limited warranty and \$100,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only). Charging Station has a 1-year limited warranty.
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No