

3-Port Mini DisplayPort to HDMI Multi-Monitor Splitter, MST Hub, 4K 60Hz UHD, DP1.2, TAA

MODEL NUMBER: **B155-003-HD-V2**



Displays the same image on 3 HDMI monitors, extends the desktop across all three, or combines all into one large monitor. Ideal for digital signage in schools, churches, conference rooms, trade shows and retail outlets.

Description

The B155-003-HD-V2 3-Port Mini DisplayPort 1.2 to HDMI MST Hub connects up to three HDMI monitors to the Mini DisplayPort (MDP) output on your computer. Ideal for digital signage in schools, churches, conference rooms, trade shows, hotels and retail outlets, this hub allows you to display the same image on all three monitors, extend the desktop across them, or combine all three as one large monitor in video wall mode.

The B155-003-HD-V2 is compliant with DisplayPort 1.2 and backward compatible with versions 1.1 and 1.1a with the feature set being limited to that of your equipment. It supports Ultra High Definition (UHD) video resolutions up to 4K @ 60 Hz (3840 x 2160). In video wall mode, it supports expanded resolutions, such as 5760 x 1080 in a horizontal 1 x 3 monitor configuration or 1920 x 3240 in a vertical 3 x 1 configuration.

This MST hub also supports HDCP, EDID, DDC and 48-bit Deep Color (16 bits per channel), as well as DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio. It works with all operating systems. Plug-and-play convenience means no software or drivers are needed. A built-in six-inch cable connects directly to a MDP source. LEDs indicate when the monitors are receiving a signal. The B155-003-HD-V2 complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

Connects Up to 3 HDMI Monitors to Your Computer's Mini DisplayPort Output

- Ideal for digital signs in schools, churches, conference rooms, trade shows and retail settings
- Displays same image on 3 monitors simultaneously in mirror mode
- Extends desktop across 3 monitors in extended mode
- Combines 3 monitors into one large monitor in video wall mode
- Built-in 6 in. cable connects directly to MDP source
- LEDs indicate when monitors are receiving a signal

Meets the Latest Performance Standards

- Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160)
- Supports expanded resolutions in video wall mode, such as 5760 x 1080 in horizontal 1 x 3 configuration
- Supports HDCP, EDID and DDC
- Supports 48-bit Deep Color (16 bits per channel)

Highlights

- Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160)
- Built-in 6 in. cable connects directly to Mini DisplayPort source
- Supports up to 48-bit Deep Color (16 bits per channel)
- Works with all operating systems
- Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound

System Requirements

- Computer with DisplayPort 1.2-compatible graphics card (e.g. AMD Radeon with AMD Eyefinity) required for video wall mode.
- Backward compatible with most DisplayPort 1.1a equipment running current graphics drivers with feature set limited to that of your equipment. Compatibility with older graphics cards not guaranteed.
- Mac OS X does not support MST for NVIDIA and Intel Graphics Processor Units, limiting video display on connected monitors to mirror mode.
- Maximum supported video resolutions and number of monitors depend on your graphics card. Check graphics card specifications to determine its capabilities.
- Monitor(s) with HDMI input.

Package Includes

- B155-003-HD-V2 3-Port Mini DisplayPort 1.2 to HDMI MST Hub
- External power supply w/NEMA 1-15P plug and 5 ft. cord (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- Owner's manual



Powering Business Worldwide



- Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio

Easy to Use Almost Anywhere

- Works with all operating systems
- Plug and play—no software or drivers required

TAA Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332192998
Technology	HDMI; DisplayPort
Host Connector	MINI DISPLAYPORT (MALE)
VIDEO	
Max Supported Video Resolution	4K @ 60 Hz (3840 x 2160)
Max Supported Color Depth	48-bit Deep Color
3D Video Supported	Yes
AUDIO	
Audio Specification	DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V, 50/60Hz, 0.5A
AC Power Adapter Output Specs (V / A)	5V, 2A
AC Power Adapter Cord Length (ft.)	4.5
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
DC Barrel Plug	OD: 5.5 x 2.1 x 9.5mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	6.1
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	(3) HDMI (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold



Powering Business Worldwide



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x3) Orange (Monitor Signal)
PHYSICAL	
Color	Black
Material of Construction	Plastic
Rackmountable	No
Shipping Dimensions (hwd / in.)	8.30 x 2.17 x 6.50
Shipping Dimensions (hwd / cm)	21.08 x 5.51 x 16.51
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.4 x 10.8 x 7.5
Unit Dimensions (hwd / mm)	108 x 74 x 25
Unit Packaging Type	Box
Unit Weight (lbs.)	0.20
Unit Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	14 to 167 °F (-10 to 75 °C)
Storage Temperature Range	-4 to 176 °F (-20 to 80 °C)
Relative Humidity	0% to 85%, Non-Condensing
BTUs	20.8 BTU/Hr
COMMUNICATIONS	
EDID Compatible	Yes
FEATURES & SPECIFICATIONS	
MST Support	Yes
Displayport Specification	1.2
HDCP Specification	1.3
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; UL; cUL
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.