

Computer with DisplayPort 1.2-compatible graphics card (e.g. AMD Radeon with AMD Eyefinity) required for video wall mode. Backward compatible with most DisplayPort 1.1a equipment running current graphics drivers with feature set limited to that of your equipment. Compatibility with older graphics cards not guaranteed. MST compliant DisplayPort 1.2 graphics cards are limited to a bandwidth of 21.6 Gbps amongst all monitors, with higher resolution monitors using up more bandwidth. 1080p monitors will use up approximately 22% of bandwidth, whereas 4K monitors will use 40% or more. As each monitor will be different, it is necessary to verify the percentage of bandwidth being used by each monitor in the display settings interface for your graphics card. If the total percentage of bandwidth taken up by all of the connected monitors exceeds 100%, an image will not display on one or more of them. Maximum supported video resolutions and number of monitors depend on your graphics card. Check graphics card specifications to determine its capabilities.

4-Port Mini DisplayPort to DisplayPort Multi-Monitor Splitter, MST Hub, 4K 60 Hz UHD, DP1.2, TAA

MODEL NUMBER: **B155-004-DP-V2**



Displays the same image on 4 DisplayPort monitors, extends the desktop across them, or combines all into one large monitor. Ideal for digital signage in schools, churches, conference rooms, trade shows and retail outlets.

Description

The B155-004-DP-V2 4-Port Mini DisplayPort 1.2 to DisplayPort MST Hub connects four DisplayPort monitors to the Mini DisplayPort output on your computer. Ideal for digital signage in schools, churches, conference rooms, trade shows, hotels and retail outlets, this hub allows you to display the same image on all four monitors, extend the desktop across them, or combine all four into one large monitor in video wall mode.

The B155-004-DP-V2 is compliant with DisplayPort 1.2 and backward compatible with versions 1.1 and 1.1a with the feature set being limited to that of your equipment. It supports high-definition video resolutions up to 1920 x 1080 (1080p) per monitor. In video wall mode, this hub supports expanded video resolutions, such as 4K @ 60Hz (3840 x 2160) in a 2 x 2 monitor configuration or 7680 x 1080 in a vertical 4 x 1 configuration.

This MST hub also supports HDCP, EDID, DDC and 48-bit Deep Color (16 bits per channel), as well as DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio. It works with all operating systems. Plug-and-play convenience means no software or drivers are needed. A built-in six-inch cable connects directly

Highlights

- Supports HD video resolutions up to 4K @ 60Hz (3840 x 2160)
- Built-in 6 in. cable connects directly to Mini DisplayPort source
- Supports up to 48-bit Deep Color (16 bits per channel)
- Works with all operating systems
- Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound

System Requirements

- Computer with DisplayPort 1.2-compatible graphics card (e.g. AMD Radeon with AMD Eyefinity) required for video wall mode.
- Backward compatible with most DisplayPort 1.1a equipment running current graphics drivers with feature set limited to that of your equipment. Compatibility with older graphics cards not guaranteed.
- Mac OS X does not support MST for NVIDIA and Intel Graphics Processor Units, limiting video display on connected monitors to mirror mode.
- Maximum supported video resolutions and number of monitors depend on your graphics card. Check graphics card specifications to determine its capabilities.



to a Mini DisplayPort source. LEDs indicate when the monitors are receiving a signal. The B155-004-DP-V2 complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

Connects Up to 4 DisplayPort Monitors to Your Computer's Mini DisplayPort

- Ideal for digital signs in schools, churches, conference rooms, trade shows and retail settings
- Displays same image on 4 monitors simultaneously in mirror mode
- Extends desktop across 4 monitors in extended mode
- Combines 4 monitors into one large monitor in video wall mode
- Built-in 6 in. cable connects directly to Mini DisplayPort source

- LEDs indicate when monitors are receiving a signal

Meets the Latest Performance Standards

- Supports HD video resolutions up to 1920 x 1080 per monitor
- Supports expanded resolutions in video wall mode, such as 4K @ 60Hz (3840 x 2160) in a 2 x 2 monitor configuration or 7680 x 1080 in a vertical 4 x 1 configuration
- Supports HDCP, EDID and DDC
- Supports 48-bit Deep Color (16 bits per channel)
- Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio

- Backward compatible with DisplayPort 1.1 and 1.1a

Easy to Use Almost Anywhere

- Works with all operating systems
- Plug and play—no software or drivers required

TAA Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

- Monitor(s) with DisplayPort input.

Package Includes

- B155-004-DP-V2 4-Port Mini DisplayPort 1.2 to DisplayPort MST Hub
- External power supply with NEMA 1-15P plug and 5 ft. cord (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332193407
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
Technology	DisplayPort
Host Connector	MINI DISPLAYPORT (MALE)
VIDEO	
Max Supported Video Resolution	4K @ 60Hz (3840 x 2160)
Max Supported Color Depth	48-bit Deep Color
3D Video Supported	Yes
AUDIO	
Audio Specification	DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio



INPUT	
External Power Supply Plug(s)	NEMA 1-15P North America
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60Hz, 0.5A
External Power Supply Output Specs (V / A)	5V, 2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 9.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x4) Orange (Monitor Signal)
PHYSICAL	
Color	Black
Material of Construction	Plastic
Rackmountable	No
Shipping Dimensions (hwd / cm)	21.08 x 5.51 x 16.26
Shipping Dimensions (hwd / in.)	8.30 x 2.17 x 6.40
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Unit Dimensions (hwd / cm)	10.8 x 7.5 x 2.4
Unit Dimensions (hwd / in.)	4.3 x 3.0 x 0.9
Unit Dimensions (hwd / mm)	108 x 75 x 24
Unit Packaging Type	Box
Unit Weight (kg)	0.09
Unit Weight (lbs.)	0.2
ENVIRONMENTAL	
Operating Temperature Range	14 to 167 °F (-10 to 75 °C)
Storage Temperature Range	-4 to 176 °F (-20 to 80 °C)
Relative Humidity	0% to 85%, Non-Condensing
BTUs	13.65 BTU/Hr
Power Consumption (Watts)	4



COMMUNICATIONS	
EDID Compatible	Yes
CONNECTIONS	
Ports	4
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	(4) DISPLAYPORT (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
HDCP Specification	1.3
Driver Required	No
SPECIAL FEATURES	
MST Support	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS and REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>