

Dual-Display Flex-Arm Mount for 13” to 34” Monitors - Clamp or Grommet, USB, Audio Ports

MODEL NUMBER: DDR1732DAL



Aluminum desk clamp mounts most 13- to 34-inch monitors at a comfortable height to free up valuable space on your desk or work area.

Features

Rugged Aluminum Desk Clamp Lifts Your Monitors Above Your Work Area’s Surface

This VESA-compliant desktop clamp mounts two flat- or curved-screen displays above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDR1732DAL will fit most flat- and curved-panel monitors from 13 to 34 inches. The durable aluminum frame tolerates frequent adjustments, and the two swiveling aluminum arms support up to 19.8 pounds (8.9 kg) apiece. Instead of clamping the unit to your desktop, you may install it using the included grommet. All hardware is included.

Swivel, Tilt and Rotate the Dual Screens to Find the Most Comfortable Viewing Angles

The flex arms adjust independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -90° to +90° tilt, -90° to +90° swivel and 90° rotation for positioning your screens. Easy screen adjustment lets you quickly find just the right angles without interrupting your workday.

Connect Your Favorite Devices to Help You Get Through the Workday

The base of the DDR1732DAL features a USB 3.0 port for connecting a smartphone or other USB device. Two 3.5 mm audio jacks allow connection of a microphone and speakers.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100.

Highlights

- Sturdy aluminum frame clamps securely to your desk for mounting twin displays
- -90° to +90° tilt, -90° to +90° swivel and 90° rotation help you find the perfect angle
- Base includes a USB 3.0 port and dual 3.5 mm audio ports for connecting peripherals
- Durable aluminum flex arms blend into any décor and support up to 19.8 lb. each
- VESA compliance ensures compatibility with 75 x 75 and 100 x 100 mounting patterns

Applications

- Lift 2 monitors above your standing desk or workstation to free up valuable surface space
- Swivel, tilt and/or rotate your screens for the most comfortable viewing angle

System Requirements

Flat- and curved-screen monitors from 13 to 34 in.

Package Includes

- DDR1732DAL Dual-Display Flex-Arm Desktop Clamp
- Mounting hardware
- Owner’s manual

Specifications

OVERVIEW	
UPC Code	037332262509



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desk Clamp; Grommet
Degrees of Motion	-90/+90 for Tilt, Swivel and Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	34
Maximum Screen Size (cm)	86.4
Maximum Weight Capacity (lbs.)	19.8
Maximum Weight Capacity (kg)	9
Number of Displays	2
Unit Dimensions (hwd / in.)	12.8 x 22.1 x 4.9
Unit Dimensions (hwd / cm)	32.5 x 56.1 x 12.4
Unit Weight (lbs.)	19.8
Unit Weight (kg)	8.98
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Antimicrobial	No
Tools Necessary	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>