



Powering Business Worldwide

## Waber-by-Tripp Lite Surge Suppressor with heavy-duty metal housing

MODEL NUMBER: DG115-SR



### Highlights

- 6 outlets/6 ft. cord
- 600 joule rating
- Audible surge indication
- Remote switch included

### Package Includes

- DG115-SR Power Strip
- Warranty information
- Instruction manual

### Description

The Waber-by-Tripp Lite DG115-SR Power Strip offers a convenient method of power distribution and surge suppression in workbench, wallmount or floor mount applications. Unique design includes remote power switch at the end of a 6 foot cord allows remote power control of connected equipment. Includes 6 NEMA 5-15R output receptacles, 6 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built in surge suppression rated at 600 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15 amp resettable circuit breaker and attractive gray color scheme. Lifetime warranty.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip with remote power switch on a 6 ft. cord

SUPPRESSION - 600 joules AC suppression

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Mountable remote power switch at the end of a 6 foot cord allows remote power control of connected equipment.
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs support permanent installation on a wide variety of surfaces
- UL1449 (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6 foot AC line cord
- Lifetime warranty

## Specifications

OVERVIEW



Powering Business Worldwide

UPC Code	037332115621
<b>INPUT</b>	
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Lighted two position mountable remote power switch at the end of a dedicated 6 ft. cord controls power to all outlets
Diagnostic LED Details	Protection present (green)
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	600
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Up to 20 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Color	Light Gray
Material of Construction	Metal



Powering Business Worldwide

Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	2.16 x 15.00 x 6.00
Shipping Dimensions (hwd / cm)	5.50 x 38.10 x 15.24
Shipping Weight (lbs.)	2.12
Shipping Weight (kg)	0.96
Unit Dimensions (hwd / in.)	1.500 x 12.594 x 2.500
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.