

Heavy-Duty Rolling TV Stand, Height Adjustable, 60" - 100" Screens

MODEL NUMBER: DMCS60100XX



Portable floor stand accommodates a heavy flat or curved television, monitor or interactive display/whiteboard.

Features

Bring the Presentation to Your AudienceThe DMCS60100XX combines the strength of a height-adjustable TV floor stand with the convenience of a portable cart. Mount a flat or curved panel television, monitor or interactive whiteboard on this movable TV stand and bring it to your audience in a classroom, lecture hall, office, conference room or other location where audio/video resources are shared. The DMCS60100XX accommodates most flat-panel displays from 60 to 100 inches, including Promethean whiteboards. Its heavy-duty aluminum frame supports up to 220 pounds (99.8 kilograms)

Effectively Share Audio/Video ResourcesAn alternative to purchasing multiple displays, the DMCS60100XX allows a large screen and its peripherals to be easily shared within a facility and stored in a secure area. The heavy-duty TV stand has four sturdy wheels that move smoothly through doorways and over thresholds. The wheels lock to keep the stand in position while at rest. Each column has a handle to help you guide the cart's movement.

Easily Adjust the Height and Viewing Angle of Your 60" to 100" DisplayThe columns telescope in two-inch increments, so you can adjust the height of the display mounting bracket from 47 to 65 inches above the floor. The display angle can be adjusted from +5° to -10° for optimal viewing.

VESA-Compliant Mounting Ensures Display CompatibilityVESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing mounting standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 200 x 500, 300 x 200, 300 x 300, 300 x 400, 300 x 500, 300 x 600, 400 x 200, 400 x 300, 400 x 400, 400 x 500, 400 x 600, 500 x 200, 500 x 300, 500 x 400, 500 x 500, 500 x 600, 600 x 300, 600 x 400, 600 x 500, 600 x 600, 700 x 300, 700 x 400, 700 x 500, 700 x 600, 800 x 300, 800 x 400, 800 x 500, 800 x 600, 900 x 400, 900 x 500, 1000 x 400, 1000 x 500 and 1000 x 600.

Conveniently Place Peripherals and Manage CablesThe upper shelf holds a webcam or small projector. The lower shelf holds a laptop or an audio/video component, such as a Blu-ray player. Add a clamp-on surge protector to the lower shelf to provide power protection for devices. The height of both shelves is adjustable. Cable management openings in the columns allow you to route power and connection cords, reducing clutter for a clean, professional look.

Highlights

- Holds most flat or curved 60-100 in. displays up to 220 lb. (99.8 kg)
- Accommodates interactive whiteboards, including Promethean models
- Height adjustable from 47 to 65 in. for best viewing
- Locking swivel casters easily roll over carpet
- Shelves hold a webcam and a Blu-ray player or laptop

Applications

- View video in a multipurpose area where a permanent installation is not practical
- Move a display and webcam into a meeting room for web conferencing
- Create a temporary digital signage display in an auditorium
- Roll an interactive whiteboard between classrooms
- Easily move a flat- or curved-panel television for storage in a secure area

Package Includes

- All DMCS60100XX components (assembly required)
- Assembly fasteners
- Display mounting fasteners
- Hex key
- Wrench
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Specifications

OVERVIEW	
UPC Code	037332224620
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black; Silver
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	1000x400; 1000x500; 1000x600; 200x200; 200x300; 200x400; 200x500; 300x200; 300x300; 300x400; 300x500; 300x600; 400x200; 400x300; 400x400; 400x500; 400x600; 500x200; 500x300; 500x400; 500x500; 500x600; 600x300; 600x400; 600x500; 600x600; 600x900; 700x300; 700x400; 700x500; 700x600; 800x300; 800x400; 800x500; 800x600; 900x400; 900x500
Motion	Tilt
Mounting Location	Floor
Degrees of Motion	+5° to -10°
Minimum Screen Size (in.)	60
Minimum Screen Size (cm)	152.4
Maximum Screen Size (in.)	100
Maximum Screen Size (cm)	254
Maximum Weight Capacity (lbs.)	220
Maximum Weight Capacity (kg)	100
Number of Displays	1
Shipping Dimensions (hwd / in.)	9.80 x 25.80 x 47.50
Shipping Dimensions (hwd / cm)	24.89 x 65.53 x 120.65
Shipping Weight (lbs.)	100.00
Shipping Weight (kg)	45.36
Unit Dimensions (hwd / in.)	46.200 x 44.000 x 27.600
Unit Weight (lbs.)	61
Unit Weight (kg)	27.67
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No



Powering Business Worldwide

TRIPP LITE
SERIES

Pre-Installed Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.