

Heavy-Duty Streamline Landscape Mobile Cart for 60" to 105" Flat-Panel Displays

MODEL NUMBER: DMCS60105HDS



Secure digital signage stand delivers your message to a classroom, lobby, trade show or other location with heavy foot traffic.

Features

Set Up Your Digital Signage Wherever Your Audience Is

This streamline mobile TV stand fits most flat-panel displays, whiteboards and interactive displays from 60 to 105 inches (152 to 267 centimeters) in landscape mode. It's easy to assemble with for convenient setup wherever foot traffic flows, such as classrooms, trade shows, lecture halls, offices, auditoriums, restaurants, bars and hotels. It's ideal for setting up a digital whiteboard or interactive display for a virtual meeting or brainstorming session or showing videos in a multipurpose area where a permanent display is not feasible.

Heavy-Duty Frame Designed to Last

The aluminum and steel frame withstands the stress of repeated adjustments and supports up to 220 pounds (100 kilograms). Leveling feet at the bottom let you adapt your display to uneven floors. Heavy-duty locking casters are also included for rolling your display from one room to the next.

Includes Combo Lock to Keep Your Display Secure

The DMCS60105HDS features an anti-theft locking hole complete with a four-position combination lock to protect your display in heavy traffic areas.

Conveniently Place Peripherals and Manage Cables

An adjustable shelf below the display holds audio/video and other components, such as surge protectors, laptops, projectors, webcams and Blu-ray players, up to 55 pounds (25 kilograms). Equipment cables route through clips on the stand's legs to keep them organized and avoid excessive clutter.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 400 x 400, 600 x 400, 800 x 400, 800 x 600 and 1000 x 600. All hardware is included.

Specifications

Highlights

- Supports most monitors, whiteboards and interactive displays from 60 to 105 in.
- Durable aluminum and steel frame blends into any decor and supports up to 220 lb.
- Anti-theft locking hole with included 4-position combination lock keeps display secure
- Height-adjustable shelf accommodates laptops, webcams, Blu-ray players, etc.
- Cable management clips keep cords organized and prevent cable clutter

Package Includes

- DMCS60105HDS Streamline Landscape Mobile Cart
- Assembly hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332272126
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	400x400; 600x400; 800x400; 800x600; 1000x600
Mounting Location	Floor
Minimum Screen Size (in.)	60
Minimum Screen Size (cm)	152.40
Maximum Screen Size (in.)	105
Maximum Screen Size (cm)	266.7
Maximum Weight Capacity (lbs.)	220
Maximum Weight Capacity (kg)	100
Number of Displays	1
Unit Dimensions (hwd / in.)	67.560 x 43.100 x 26.900
Unit Dimensions (hwd / cm)	171.60 x 109.47 x 68.33
Unit Weight (lbs.)	52
Unit Weight (kg)	23.59
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	Yes
Built-in Cable Management	No
Leveling Feet	Yes
Pre-Installed Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.