

Heavy-Duty Rolling TV Cart for 60" to 105" Flat-Screen Displays, Locking Casters, Black

MODEL NUMBER: DMCS60105XXDD



Height-adjustable mobile cart lets you move your flat-panel display smoothly and safely from one room to another on heavy-duty casters.

Features

Move Your Flat-Panel Display or Interactive Whiteboard Wherever Your Audience Is

This rugged rolling TV cart combines a height-adjustable display mount with the convenience of a mobile cart. This DMCS60105XXDD lets you deliver your message to conference rooms, classrooms, lobbies, lecture halls, hospitals and anywhere else requiring flexibility in a screen's location. Mount your flat-panel television, whiteboard or touchscreen monitor to this mobile cart, and then roll it safely and smoothly from room to room. The scratch-resistant powder-coated finish tolerates frequent handling and blends easily into any décor.

Raise and Lower the Screen to Find the Most Comfortable Viewing Angle

The height-adjustable TV floor stand fits most flat-panel displays, whiteboards and monitors from 60 to 105 inches. Its durable steel frame withstands the stress of repeated adjustments and supports up to 330 pounds. You can raise or lower the height of the display from 66.8 to 72.6 inches above the floor.

Rolls Easily from Place to Place on Sturdy Locking Metal Casters

The DMCS60105XXDD rolls almost effortlessly to the proper viewing location and angle on sturdy swivel casters with rubber wheels that move smoothly in any direction through doorways, over thresholds and even on carpet. The casters lock into place to keep the stand securely in position while at rest.

Conveniently Place Peripherals and Manage Cables

Two durable shelves hold audio/video and other components, such as computers, UPS systems, printers, projectors, webcams and Blu-ray players. Each shelf supports up to 44 pounds.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400, 600 x 400, 800 x 400, 800 x 600, 900 x 600 and 1000 x 600. Mounting hardware is included.

Specifications

Highlights

- Ideal for rolling your flat-panel TV through offices, classrooms and conference rooms
- Raise and lower the height of the display from 66.8 to 72.6 in. for comfortable viewing
- Durable steel frame blends into any room decor and supports up to 330 lb.
- Heavy-duty swivel casters enable smooth rolling and lock to secure the cart at rest
- Built-in shelves accommodate computers, projectors, printers, Blu-ray players, etc.

Applications

- Move a flat-panel display into a lobby, hallway or trade show booth to create temporary digital signage
- Show videos in a multipurpose area, such as a hotel lobby or lecture hall, where a permanent display is impractical
- Roll your television into a secure area for storage when not in use
- Bring a digital whiteboard or interactive display into a conference room or classroom for a virtual meeting or brainstorming session

System Requirements

Flat-screen television, monitor, digital whiteboard or interactive display from 60 to 105 in.

Package Includes

- DMCS60105XXDD Heavy-Duty Rolling TV Cart
- Assembly and mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332260338
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 300x200; 300x300; 400x200; 400x300; 400x400; 600x400; 800x400; 800x600; 900x600; 1000x600
Motion	Fixed
Mounting Location	Floor
Minimum Screen Size (in.)	60
Minimum Screen Size (cm)	152.4
Maximum Screen Size (in.)	105
Maximum Screen Size (cm)	266.7
Maximum Weight Capacity (lbs.)	330
Maximum Weight Capacity (kg)	150
Number of Displays	1
Shipping Dimensions (hwd / in.)	9.00 x 31.00 x 62.00
Shipping Dimensions (hwd / cm)	22.86 x 78.74 x 157.48
Shipping Weight (lbs.)	128.00
Shipping Weight (kg)	58.06
Unit Dimensions (hwd / in.)	72.600 x 46.200 x 26.600
Unit Weight (lbs.)	330
Unit Weight (kg)	149.69
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No
Pre-Installed Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.