


## Safe-IT Heavy-Duty Rolling Cart for 70" to 120" Displays, UL Certified, Antimicrobial Protection

MODEL NUMBER: DMCS70120AMUL



UL-certified rolling cart with antimicrobial protection lets you move your 70 to 120 in. television or monitor from one room to another.

### Features

#### Move Your Television or Interactive Whiteboard to Your Audience

This Safe-IT™ rolling TV cart combines a height-adjustable display mount with the convenience of a mobile cart. Mount your television, monitor, digital whiteboard or interactive touchscreen to the all-metal unit, and then roll it safely and smoothly from room to room. The DMCS70120AMUL lets you deliver your message in corporate, education, healthcare, transportation, hospitality, retail, government and other settings requiring flexibility in a screen's location.

#### Heavy-Duty Metal Casters Take Your Message Wherever It Needs to Go

A mobile stand with three-inch swivel casters allows you to roll the DMCS70120AMUL into any office, conference room, huddle space or classroom best suited for cost-efficient resource sharing. Ease of movement allows collaborative workflow to happen in any location and maximizes usage to increase engagement, creativity and productivity. Antimicrobial handles help you guide the cart's movement. The casters lock into place to keep the stand securely in position while at rest.

#### UL Certified for an Enhanced Sense of Safety

The DMCS70120AMUL is certified to meet UL/cUL 1678 safety standards.

#### Raise and Lower the Screen to Find the Most Comfortable Viewing Angle

The height-adjustable rolling cart fits most flat-panel displays, whiteboards and monitors from 70 to 120 inches in landscape mode. Its durable steel frame withstands the stress of repeated adjustments and supports up to 264 pounds (120 kilograms). Raise or lower the height of the display during assembly anywhere from 49.2 to 63 inches. You can also tilt the screen to achieve the most comfortable viewing angle.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The handles feature antimicrobial properties that help resist the growth of bacteria, viruses, fungi, mold and mildew.

#### Conveniently Place Peripherals and Manage Cables

Adjustable shelves hold audio/video and other components, such as surge protectors, laptops, projectors, webcams and Blu-ray players. Each shelf holds up to 11 pounds (4.9 kg). Cables can be routed through the columns to keep them hidden and avoid excessive clutter.

### Highlights

- Ideal for rolling your TV or whiteboard into offices, classrooms and conference rooms
- Durable steel frame blends into any room decor and supports up to 264 lb. (120 kg.)
- 3 in. swivel casters enable smooth rolling and lock to secure the cart at rest
- Certified to meet UL/cUL 1678 safety standards for education and medical facilities
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

### System Requirements

- Flat-screen television, monitor, digital whiteboard or interactive touchscreen from 70 to 120 in.
- Supports the following VESA patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400, 600 x 400, 800 x 400, 800 x 600 and 1000 x 600

### Package Includes

- DMCS70120AMUL Heavy-Duty Rolling Cart
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

**VESA-Compliant Mounting Ensures Display Compatibility**

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400, 600 x 400, 800 x 400, 800 x 600 and 1000 x 600. Hardware for assembly and mounting is included.

## Specifications

OVERVIEW	
UPC Code	037332275370
Device Compatibility	Monitor/HDTV; Projector
PHYSICAL	
Color	Black
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	200x200; 300x200; 300x300; 400x200; 400x300; 400x400; 600x400; 800x400; 800x600; 1000x600
Motion	Full
Mounting Location	Floor
Degrees of Motion	360° Rotate
Minimum Screen Size (in.)	70
Minimum Screen Size (cm)	177.8
Maximum Screen Size (in.)	120
Maximum Screen Size (cm)	266.7
Maximum Weight Capacity (lbs.)	265
Maximum Weight Capacity (kg)	120
Number of Displays	1
Unit Dimensions (hwd / in.)	91.900 x 49.300 x 29.900
Unit Dimensions (hwd / cm)	233 x 125 x 76
Unit Weight (lbs.)	81.3
Unit Weight (kg)	36.88
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Pre-Installed Casters	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA C22.2; UL 1678; UL Listed; cUL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.