

Rolling Dual-Screen TV/Monitor Cart - For Two 35" to 45" TVs and Monitors, Side-by-Side Mounting

MODEL NUMBER: **DMCSD3545M**



Dual-screen mobile TV cart supports side-by-side mounting of two flat-panel televisions or monitors.

Features

Bring the Message to Your AudienceThe DMCSD3545M combines a height-adjustable TV stand with the convenience of a rolling cart. Mount two flat-panel televisions or monitors on this mobile TV cart and bring your message to your audience in a classroom, lecture hall, office, conference room or other location where audio/video resources are shared. This cart has a steel frame and accommodates most flat-panel displays from 35 to 45 inches. Maximum weight supported is 88 lbs (39.9 kgs) per display.

Effectively Share Audio/Video ResourcesFour sturdy swivel casters provide smooth rolling through doorways and over thresholds, making it possible to share dual screens within a facility instead of purchasing multiple setups. When not in use, the cart can be rolled into a secure area for storage. The casters lock to keep the cart in position while at rest.

Easily Mount Two 35" to 45" Displays and Adjust the Viewing AngleThe columns telescope, so you can adjust the viewing height of the displays from 50 to 62.5 inches above the floor. For hassle-free display compatibility, this rolling TV cart supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300 and 400 x 400. The display angle can be adjusted from +10° to -10° for optimal viewing.

Conveniently Place Peripherals and Manage CablesThis cart has two height-adjustable shelves that each support 11 lbs (4.9 kgs). The upper shelf holds a webcam or small projector. The lower shelf holds a laptop or other video source, such as a Blu-ray player. Add a clamp-on surge protector (sold separately) to the lower shelf to protect devices from power surges and help prevent line noise interference. Cable management openings in the columns allow you to route power and audio/video cords, reducing clutter for a clean, professional look.

Highlights

- Holds most flat-panel displays from 35 to 45 in. and up to 88 lb.
- Display height adjusts from 50 to 62.5 in. for best viewing
- Locking swivel casters move easily over thresholds
- Adjustable shelves for a webcam and a video source support 11 lbs (4.9 kgs) each
- Cable management reduces cord clutter

Applications

- View video in a multipurpose area where a permanent installation is not practical
- Move displays and a webcam into a meeting room for web conferencing
- Create a temporary digital signage display in an auditorium
- Easily move displays and a video source to a secure area for storage

Package Includes

- All DMCSD3545M components (assembly required)
- Assembly fasteners
- Display mounting fasteners
- Hex key
- Wrench
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332239433



Powering Business Worldwide

TRIPP LITE
SERIES

Device Compatibility	Monitor/HDTV; Projector
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400
Motion	Fixed
Mounting Location	Floor
Minimum Screen Size (in.)	35
Minimum Screen Size (cm)	88.9
Maximum Screen Size (in.)	45
Maximum Screen Size (cm)	114.3
Maximum Weight Capacity (lbs.)	176
Maximum Weight Capacity (kg)	80
Number of Displays	2
Shipping Dimensions (hwd / in.)	14.00 x 20.00 x 62.00
Shipping Dimensions (hwd / cm)	35.56 x 50.80 x 157.48
Shipping Weight (lbs.)	87.30
Shipping Weight (kg)	39.60
Unit Dimensions (hwd / in.)	59.300 x 26.900 x 85.000
Unit Dimensions (hwd / cm)	150.6 x 68.33 x 215.9
Unit Weight (lbs.)	79.1
Unit Weight (kg)	35.88
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No
Pre-Installed Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.