


## Tilt Wall Mount for 32" to 70" TVs and Monitors

MODEL NUMBER: DWT3270X



Low-profile mount hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Tilts to provide optimal viewing angles.

### Description

The VESA-compliant DWT3270X Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 32 to 70 inches. A -10° to 0° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

- Low-profile mount is concealed behind the display to give a sleek, professional appearance. Frame is open for easy wall access. Mounting rails adjust horizontally to compensate for off-center wall studs. Built-in bubble level allows accurate display leveling. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 165 lbs (74.8 kgs). Mounting hardware included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 200 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm and 600 x 400 mm

### Features

**Mounts Your TV or Monitor to the Wall** Fits most flat-panel televisions, monitors and other displays from 32 to 70 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Mounts out of sight behind display for sleek, professional appearance. Mounting hardware included.

**Convenient One-Touch Adjustment** -10° to 0° tilt capability provides comfortable viewing from multiple angles. Improves viewing angles in applications where audience is below the display.

**Durable Metal Construction** Supports up to 165 lbs (74.8 kgs). Open frame allows easy wall access. Adjustable mounting rails compensate for off-center wall studs. Built-in bubble level for accurate display leveling. Scratch-resistant powder-coated finish.

**VESA Compliance** Supports the following VESA mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 200 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm and 600 x 400 mm.

## Specifications

### Highlights

- Fits most flat-panel displays from 32 to 70 in.
- Hangs out of sight for a sleek, professional appearance
- -10° to 0° tilt capability for comfortable viewing
- Supports up to 165 lbs (74.8 kgs).

### Package Includes

- DWT3270X Tilt Wall Mount for 32" to 70" TVs and Monitors
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

|                                      |   |
|--------------------------------------|---|
| UPC Code                             | 037332183606  |
| Device Compatibility                 | Monitor/HDTV  |
| <b>PHYSICAL</b>                      |   |
| Color                                | Black   |
| Material of Construction             | Steel   |
| VESA Pattern (mm)                    | 100x100; 100x200; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400 |
| Motion                               | Tilt  |
| Mounting Location                    | Wall  |
| Degrees of Motion                    | -10/+0 Tilt   |
| Distance from Wall (in.)             | 1.77  |
| Distance from Wall (cm)              | 5   |
| Distance from Wall (mm)              | 45  |
| Minimum Screen Size (in.)            | 32  |
| Minimum Screen Size (cm)             | 81.28   |
| Maximum Screen Size (in.)            | 70  |
| Maximum Screen Size (cm)             | 177.8   |
| Maximum Weight Capacity (lbs.)       | 165   |
| Maximum Weight Capacity (kg)         | 75  |
| Number of Displays                   | 1   |
| Shipping Dimensions (hwd / in.)      | 2.00 x 8.50 x 27.00   |
| Shipping Dimensions (hwd / cm)       | 5.08 x 21.59 x 68.58  |
| Shipping Weight (lbs.)               | 6.20  |
| Shipping Weight (kg)                 | 2.81  |
| Unit Dimensions (hwd / in.)          | 17.320 x 26.140 x 1.800   |
| Unit Dimensions (hwd / cm)           | 20.3 x 66.4 x 4.77  |
| Unit Weight (lbs.)                   | 5.94  |
| Unit Weight (kg)                     | 2.69  |
| Assembly Required                    | Yes   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |   |
| Antimicrobial                        | No  |
| Cord Management                      | No  |
| Tools Necessary                      | Yes   |
| Security Lock                        | No  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |   |

|                                     |                         |
|-------------------------------------|-------------------------|
| Product Compliance                  | RoHS; RoHS3; REACH      |
| WARRANTY & SUPPORT                  |                         |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.