


UPS Battery Pack for SV-Series 3-Phase UPS, +/-120VDC, 3 Cabinets - Tower, TAA, Batteries Included

MODEL NUMBER: **EBP240V6003**



External backup battery pack provides extended runtime for compatible Tripp Lite SV-Series 3-phase UPS systems.

Features

UPS Battery Pack Extends the Runtime of Your SV-Series 3-Phase UPS System This external backup battery pack consists of three battery cabinets containing sealed lead acid batteries designed to give your Tripp Lite SV-Series UPS system more runtime. It uses a +/-120VDC configuration and must be hardwired to a compatible UPS system. You can also connect more battery packs in parallel to increase runtime even longer. A UL-listed DC circuit breaker protects against too much current. The EBP240V6003 is compatible with all Tripp Lite UPS models that begin with SV20, SV40, SV60, SV80, SV100, SV120 and SV140.

Designed and Constructed to Ensure Consistent Power for a Long Time This 120V UPS battery pack is made from heavy-gauge welded steel with a baked powder-coated finish that protects the cabinets from chipping and corrosion. The hinged cabinet door locks to prevent tampering and to facilitate easy access to the internal batteries. User-supplied power output cables feed into the cabinets through conduit knockouts built into the cabinets' exterior. Front and rear vents allow the free flow of warm air out of the cabinets to maintain cool internal temperatures. Sturdy metal casters allow you to smoothly roll the backup battery pack into position.

TAA-Compliant for GSA Schedule Purchases The EBP240V6003 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332225351
INPUT	

Highlights

- Extends runtime of Tripp Lite SV-Series UPS systems using a +/-120VDC configuration
- Sealed lead acid batteries offer safety, little maintenance and high power density
- Hardwired installation with circuit breakers providing overcurrent protection
- Multiple battery cabinets may be connected in parallel to increase runtime
- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Extend the runtime of your compatible Tripp Lite UPS system in a data center or telecom network
- Connect multiple battery packs in parallel to further extend runtime for mission-critical equipment

System Requirements

- Any Tripp Lite UPS model that begins with SV20, SV40, SV60, SV80, SV100, SV120 or SV140

Package Includes

- EBP240V6003 UPS Battery Pack for SV-Series 3-Phase UPS w/Batteries, 3 Cabinets
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Input Phase	3-Phase
BATTERY	
Expandable Runtime	No
DC System Voltage (VDC)	+/- 120VDC
UPS Connection	Hardwire (contractor supplies wiring - see Owner's Manual for requirements and installation information)
PHYSICAL	
Material of Construction	Steel
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / in.)	64.50 x 87.00 x 31.50
Shipping Weight (lbs.)	6583.00
Shipping Weight (kg)	2,986.00
Unit Dimensions (hwd / in.)	59 x 87 x 31.5
Unit Dimensions (hwd / cm)	149.86 x 220.98 x 80.01
Unit Weight (lbs.)	6503
Unit Weight (kg)	2,949.71
STANDARDS & COMPLIANCE	
Product Certifications	EN 60950-1; CSA (Canada); CAN/CSA-C22.2 No. 107.1 (Canada); IEC/EN 62040; UL 1778
Product Compliance	RoHS; UKCA
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>